# XS218BLPAM12

inductive sensor XS2 M18 - L64mm - brass - Sn8mm - 12..24VDC - M12





#### Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Sensor name	XS2
Sensor design	Cylindrical M18
Size	64 mm
Body type	Fixed
Enclosure material	Nickel plated brass
Type of output signal	Discrete
Wiring technique	3-wire
[Sn] nominal sensing distance	8 mm
Discrete output function	1 NO
Discrete output type	PNP
Electrical connection	4 pins M12 male connector
[Us] rated supply voltage	1224 V DC with reverse polarity protection
Switching capacity in mA	<= 200 mA with overload and short-circuit protection
IP degree of protection	IP67 conforming to IEC 60529

### Complementary

•		
ISO thread	M18 x 1	
Detection face	Frontal	
Detector flush mounting acceptance	Non flush mountable	
Material	Metal	
Front material	PBT	
Operating zone	06.4 mm	
Differential travel	115% of Sr	
Output circuit type	DC	
Status LED	1 LED yellow for output state	
Supply voltage limits	1036 V DC	
Switching frequency	<= 500 Hz	
Voltage drop	<= 2 V at closed state	
Current consumption	<= 10 mA at no-load	
Delay first up	<= 15 ms	
Delay response	<= 0.1 ms	
Delay recovery	<= 1 ms	
Marking	CE	
Threaded length	35 mm	
Height	18 mm	
Length	64 mm	
Product weight	0.035 kg	

### **Environment**


CSA UL	
	UL

ambient air temperature for operation	-2570 °C
ambient air temperature for storage	-4085 °C
vibration resistance	25 gn amplitude = +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6
shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0903 - Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available


### **Dimensions**



(1) LED


## **Minimum Mounting Distances**

Side by side



e (1) 32 mm/1.26 in.


≥



e (2) 96 mm/3.78 in.

≥


Facing a metal object



e (3) 24 mm/0.94 in.

>

Mounted in a metal support




**d** ≥ 56 mm/2.20 in.

**h** ≥ 16 mm/0.63 in.

# **Wiring Schemes**

M12 connector





1: (+)


2: Not connected

3: (-)

4: NO Output

### **Performance Curves**

Standard Steel Target : 24x24x1 mm



- (1) Pick-up points
- (2) Drop-out points (object approaching from the side)
- (y) Sensing distance in mm