Product data sheet Characteristics

XS508B1PAL2

inductive sensor XS5 M8 - L33mm - stainless - Sn1.5mm - 12..24VDC - cable 2m





Main

Range of product	OsiSense XS	
Series name	General purpose	
Sensor type	Inductive proximity sensor	
Device application	-	
Sensor name	XS5	
Sensor design	Cylindrical M8	
Size	33 mm	
Body type	Fixed	
Detector flush mounting acceptance	Flush mountable	
Material	Metal	
Type of output signal	Discrete	
Wiring technique	3-wire	
[Sn] nominal sensing distance	1.5 mm	
Discrete output function	1 NO	
Output circuit type	DC	
Discrete output type	PNP	
Electrical connection	Cable	
Cable length	2 m	
[Us] rated supply voltage	1224 V DC with reverse polarity protection	
Switching capacity in mA	<= 200 mA DC with overload and short-circuit protection	
IP degree of protection	IP67 conforming to IEC 60529	
		

Complementary

Thread type	M8 x 1	
Detection face	Frontal	
Front material	PPS	
Enclosure material	Nickel plated brass	

Operating zone	01.2 mm
Differential travel	115% of Sr
Cable composition	3 x 0.11 mm ²
Wire insulation material	PvR
Status LED	1 LED (yellow) for output state
Supply voltage limits	1036 V DC
Switching frequency	<= 5000 Hz
Voltage drop	<= 2 V, closed state
Current consumption	<= 10 mA (no-load)
Delay first up	<= 10 ms
Delay response	<= 0.1 ms
Delay recovery	<= 0.1 ms
Marking	CE
Threaded length	25 mm
Height	8 mm
Length	33 mm
Product weight	0.035 kg

Environment

Product certifications	UL CSA
Ambient air temperature for operation	-2570 °C
Ambient air temperature for storage	-4085 °C
Vibration resistance	25 gn, amplitude: +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn (duration = 11 ms) conforming to IEC 60068-2-27

Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0953 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold	
Product environmental profile	Available End of Life Information	
Product end of life instructions	Available	


Contractual warranty

Warranty period	18 months

Product data sheet Dimensions Drawings

XS508B1PAL2

Dimensions




Product data sheet Mounting and Clearance

XS508B1PAL2


Minimum Mounting Distances

Side by side




e (1) ≥ 3 mm/0.12 in.

Face to face



e (2) ≥ 18 mm/0.71 in. Facing a metal object




e $(3) \ge 4.5 \text{ mm/0.18 in.}$

Product data sheet Mounting and Clearance

XS508B1PAL2

Mounting




(1) Bending cable: 4 x external cable diameter

Product data sheet Connections and Schema

XS508B1PAL2

Wiring Schemes




BU: Blue BN: Brown BK: Black

XS508B1PAL2

Performance Curves

Standard Steel Target: 8x8x1 mm



- (1) Pick-up points
- (2) (y) Drop-out points (object approaching from the side)
- Sensing distance in mm