ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

XS708T, XS716T, XS728T, XS748T





Leading the industry with the 2nd generation of 10-Gigabit Smart Managed Switches, Purposely Designed for SMB with Cost-Effective 10GBASE-T Connectivity and Advanced L2+/ Layer 3 Lite Features

As a leading provider of network equipment for SMBs, NETGEAR® understands the importance of reliable and high performance networks. With the growth of virtualization, cloud-based services and applications like VoIP, video streaming and IP surveillance, SMB networks need to extend beyond simple reliability to higher speed and performance. The 10-Gigabit Smart Managed Switch series from NETGEAR presents the right solution for this requirement; delivering unprecedented non-blocking 10-Gigabit bandwidth at an affordable cost.

The NETGEAR ProSAFE® XS708T, XS716T, XS728T, and XS748T are powerful Smart Managed Switches that come with 8, 16, 24, or 44 10-Gigabit Copper ports and either 2 Shared (Combo) Copper/SFP+ ports (XS708T/XS716T) or 4 additional Dedicated SFP+ ports (XS728T/XS748T) for 10G Fiber links. The NETGEAR 10-Gigabit Smart Managed Switches are purposely designed as a cost-effective way to provide 10G connections to 10G-capable servers and NAS (Network Attached Storage) systems. They can be used at the "center of a small business network" or as an aggregation / access switch in a larger organization including workgroup access, connecting to a 10-Gigabit NETGEAR ProSAFE Fully Managed Switch on one end and extending the 10G connections to the edge. The XS708T and XS716T are also ideal for smaller workgroups that need high bandwidth for sharing, collaborating, editing, and publishing high-density content like video or animation.

Highlights

The ProSAFE 10G Smart Managed Switches provide comprehensive L2+/Layer 3 Lite features in order to meet current and future needs on virtualization, converged networking and mobility. Some of the main features include:

- Advanced VLAN features such as Protocolbased VLAN, MAC-based (Media Access Control) VLAN and 802.1x Guest VLAN
- Advanced QoS (Quality of Service) with L2/ L3/L4 awareness and 8 priority queues
- \cdot IPv4 and IPv6 static routing
- · Private VLAN
- · Dynamic VLAN assignment
- · IGMP and MLD snooping
- Advanced Security
- IPv6 for management, QoS and ACL

10-Gigabit Transition with BASE-T

- 10GBASE-T, like other BASE-T technologies, uses the standard RJ45 Ethernet jack
- It is backward compatible, auto-negotiating between higher and lower speeds – thereby not forcing an all-at-once network equipment upgrade
- Cat5/Cat5e are supported for Gigabit speeds up to 100 meters

- Cat6 twisted pair copper cabling supports
 10-Gigabit speeds up to 45 meters
- Cat6a or newer Cat7 cabling will allow for up to 100 meter 10GBASE-T connections

Designed as Core Switch for SMB Network

- 10G connection to 10G-capable servers and network storage
- Powerful L2+/Layer 3 Lite features make them the most cost-effective core switches for SMB and virtualization environment
- Future-proof your network with 10G bandwidth, advanced traffic management and comprehensive IPv6 support
- Static routing helps to route internal traffic for more efficient use of network resources
- IGMP and MLD snooping provide advanced multicast filtering

Act as Aggregation Switch for Medium Sized Networks

- 10-Gigabit switches help to resolve the congestion issue between network edge and core, which is caused by the broader adoption of Gigabit-to-the-desktop
- 10-Gigabit Ethernet provides greater scalability than multiple Gigabit Ethernet links, resulting in a simplified and highly efficient network infrastructure

- Up to eight 10-Gigabit Ethernet links can be aggregated into a virtual 80-Gbps connection
- 10-Gigabit Ethernet reduces cabling complexity and uses existing cabling efficiently

Smart IT, not Big IT

- Easy-to-use Web browser-based management GUI makes setup and management simple
- Standards-based technology ensures interoperability with any standards-based devices in the existing network
- Dual firmware images improve reliability and uptime to your network
- Worry-free with NETGEAR ProSAFE LIFETIME Hardware Warranty*
- Minimal down-time with NETGEAR ProSAFE LIFETIME Next-Business-Day Replacement Warranty
- Get deployment assistance with 90-days Free 24x7 Advanced Technical Phone Support**
- LIFETIME Online Chat Technical Support







ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

XS708T, XS716T, XS728T, XS748T

Hardware at a Glance

			F	REAR			
Model Name	Form-Factor	100M/1G/10G Copper Ports	1G/10G Copper Ports	1G/10G SFP+ Ports	Firmware/ Config Access	Power Supply	Fans
XS708T	Rackmount	8		2 shared (combo)	1 x USB	1 internal PSU, fixed	1 internal, fixed fan
XS716T	Rackmount	16		2 shared (combo)	1 x USB	1 internal PSU, fixed	2 internal, fixed fans
XS728T	Rackmount		24	4 dedicated	1 x USB	1 internal PSU, fixed	4 internal, fixed fans
XS748T	Rackmount		44	4 dedicated	1 x USB	1 internal PSU, fixed	4 internal, fixed fans





XS708T: 8-port 10-Gigabit Smart Managed Switch

- 8 x 10GBASE-T copper ports supporting 10G/1G/100M speeds
- 2 x Shared (combo) 10GBASE-T copper/10GBASE-X SFP+ ports supporting 10G/1G speeds

XS728T: 28-port 10-Gigabit Smart Managed Switch

- 24 x Dedicated 10GBASE-T copper ports supporting 10G/1G speeds
- 4 x Dedicated 10GBASE-X SFP+ 10G ports supporting 10G/1G speeds





XS716T: 16-port 10-Gigabit Smart Managed Switch

- 16 x 10GBASE-T copper ports supporting 10G/1G/100M speeds
- 2 x Shared (combo) 10GBASE-T copper/10GBASE-X SFP+ ports supporting 10G/1G speeds

XS748T: 48-port 10-Gigabit Smart Managed Switch

- 44 x Dedicated 10GBASE-T copper ports supporting 10G/1G speeds
- 4 x Dedicated 10GBASE-X SFP+ 10G ports supporting 10G/1G speeds

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

XS708T, XS716T, XS728T, XS748T

Software at a Glance

	LAYER 2+ / LAYER 3 LITE FEATURES						
Management	IPv4/IPv6 ACL and QoS	IPv4/IPv6 Multicast filtering	Auto-VoIP, Auto-Video	IEEE (802.3az) Energy Effiecient Ethernet	VLANs	Convergence	IPv4 & IPv6 Static Routing
Web Browser-based GUI (HTTP/HTTPS), PC-Based Smart Control Center Utility (SCC) RMON, SNMP	L2, L3, L4 Ingress	IGMP and MLD Snooping	Yes	Yes	Static, Dynamic, Voice, MAC, Protocol-based, and Private	LLDP-MED, RADIUS, 802.1X	Yes

Performance at a Glance

Model Name	Packet buffer	CPU	ACLs	MAC Address Table RP/NDP Table VLANs	Fabric	Latency (Max Connection Speed)	Static Routes (IPv4 & IPv6)	Multicast IGMP Group
XS708T	2 MB	600 MHz Cortex-A9 Single Core, 512MB RAM 8MB SPI + 256 NAND FLASH	100 shared	16K MAC 738 ARP/NDP 256 VLANs	160Gbps line-rate	10GBASE-T: <3.012 μs 10GBASE- X SFP+: <2.466 μs	IPv4: 32 IPv6: 32	512
XS716T	2 MB	600 MHz Cortex-A9 Single Core, 512MB RAM 8MB SPI + 256 NAND FLASH	100 shared	16K MAC 738 ARP/NDP 256 VLANs	320Gbps line-rate	10GBASE-T: <2.624 μs 10GBASE-X SFP+: <2.128 μs	IPv4: 32 IPv6: 32	512
XS728T	3 MB	800 MHz Dual Core, 512MB RAM 8MB SPI + 256MB NAND Flash	164 shared	16K MAC 1K ARP/NDP 512 VLANs	560Gbps line-rate	10GBASE-T: <11.649 μs 10GBASE-X SFP+: <2.619 μs	IPv4: 64 IPv6: 64	512
XS748T	3 MB	800 MHz Dual Core, 512MB RAM 8MB SPI + 256MB NAND Flash	164 shared	16K MAC 1K ARP/NDP 512 VLANs	960Gbps line-rate	10GBASE-T: <3.674 μs 10GBASE-X SFP+: < 3.693 μs	IPv4: 64 IPv6: 64	512

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

XS708T, XS716T, XS728T, XS748T

Features at a glance

HARDWARE FEATURES	BENEFITS
10GBASE-T Copper Ethernet connections	Support low-latency, line-rate 10G Copper "BASE-T" technology with backward compatibility to Fast Ethernet and Gigabit Ethernet. Cost-effectively migrate current network to 10G capacity by utilizing the existing Cat6 RJ45 short connections (up to 30m) and Cat6a/Cat7 connections up to 100m.
10GBASE-X SFP+ ports	Providing flexibility to uplink to 10G-capable core or aggregation switches that support fiber links. Backward compatible to Gigabit fiber. Support copper or fiber modules.
USB Configuration Port	Quickly and conveniently upgrade or restore firmware, load or backup configuration files, or download system log files for troubleshooting.
Energy Efficient Ethernet (IEEE 802.3az)	Maximum power reduction for ongoing operation cost savings.
SOFTWARE FEATURES	BENEFITS
Comprehensive IPv6 Support for Management, ACL and QoS	Build current network with future in mind. Ensure investment protection and a smooth migration to an IPv6-based network without switch replacement.
IPv4 & IPv6 Static Routing	A simple way to provide segmentation of the network with internal routing through the switch – reserving the router for external traffic routing only, making the entire network more efficient.
Robust security features: • 802.1x authentication (EAP) • Port-based security by locked MAC • ACL filtering to permit or deny traffic based on MAC and IP addresses	Build a secured, converged network with all types of traffic by preventing external attacks and blocking malware while allowing secure access for authorized users.
Comprehensive QoS features: Port-based or 802.1p-based prioritization Layer 3-based (DSCP) prioritization Port-based ingress and egress rate limiting	Advanced controls for optimized network performance and better delivery of mission-critical traffic such as voice and video.
Auto-VoIP, Auto-Voice VLAN, and Auto-Video VLAN	Automatic Voice over IP prioritization (Auto-VoIP) simplifies most complex multi-vendor IP telephone deployments either based on protocols (SIP, H.323 and SCCP) or on OUI bytes (default database and user-based OUIs) in the phone source MAC address, providing the best class of service to VoIP streams (both data and signaling) over other ordinary traffic by classifying traffic, and enabling correct egress queue configuration. Similarly, Auto-Video VLAN enables IGMP snooping to minimize broadcast streams.
IGMP Snooping and MLD Snooping	Facilitate fast receiver joins and leaves for multicast streams. Save cost and improve network efficiency by ensuring multicast traffic only reaches designated receivers without the need of an extra multicast router.
Protected Ports	Ensure no exchange of unicast, broadcast, or multicast traffic between the protected ports on the switch, thereby improving the security of your converged network. This allows your sensitive phone phone conversations to stay private and your surveillance video clips can be forwarded to their designated storage device without leakage or alteration.
DHCP Snooping	Ensure IP address allocation integrity by only allowing DHCP messages from trusted DHCP servers and dropping malformed DHCP messages with a port or MAC address mismatch.
Dynamic VLAN Assignment (RADIUS)	IP phones and PCs can authenticate on the same port but under different VLAN assignment policies. Users are free to move around and enjoy the same level of network access regardless of their physical location on the network.
Private VLAN	Private VLANs help reduce broadcast with added security.
Dual Firmware Images and Configuration Files	Dual firmware images and dual configuration files for transparent firmware updates/configuration changes with minimum service interruption.


ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet


XS708T, XS716T, XS728T, XS748T

Target Application

XS708T in SMB Network



XS728T in Medium-sized Network



— 10GE link — GE link ···· Wireless link

Why 10-Gigabit Switches and Why from NETGEAR?

NETGEAR introduced the industry's first cost-effective 10-Gigabit Switches for SMBs in 2013 and is the leading provider for 10G solutions at affordable price points:

- · Ideal for SMBs to use as the core switch, connecting to 10G-capable Servers and network storage.
- Expand network capacity, remove performance bottlenecks and/or support premise expansion needs.
- Cost-effectively expand 10G bandwidth from core switch in medium-sized networks to access switches which are equipped with 10G uplinks.
- Powerful feature sets with advanced L2+/Layer 3 Lite functions, enhanced security measures, static routing, dynamic VLAN assignment and IPv6 management and support.
- · Improved usability for easier and smoother deployment of voice, video, and WLAN on the same converged platform.
- LIFETIME warranty on hardware, LIFETIME Next-Business-Day (NBD) replacement, LIFETIME tech support online chat, and 90-days Free Advanced Tech Phone Support** for peace-of-mind.

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

Technical Specifications

PRODUCT	XS708T	XS716T	XS728T	XS748T	
100M/1G/10G RJ-45 copper ports	8	16	n/a	n/a	
1G/10G copper ports	n/a	n/a	24	44	
1G/10G SFP+ (fiber) ports	2 shared (combo)	2 shared (combo)	4 (dedicated)	4 (dedicated)	
USB port (for config file upload/backup & firmware updates)		Υ	es		
PERFORMANCE SPECIFICATION					
Packet buffer memory (Dynamically shared across only used ports)	21	МВ	31	МВ	
Forwarding modes		Store-and	d-forward		
Bandwidth	160Gbps	320Gbps	560Gbps	960Gbps	
Priority queues		-	3		
Priority queuing		Weighted Round Robin ((WRR) and Strict Priority		
MAC Address database size (48-bit MAC addresses)		1	5K		
Multicast groups		5	12		
Number of IPv4 static routes	3	2	64		
Number of IPv6 static routes	3	2	64		
Number of VLANs	25	56	512		
Number of ARP cache entries	73	38	10	24	
Number of DHCP snooping bindings	8	K	1K		
Access Control Lists (ACLs)	100 shared for MA	C, IP and IPv6 ACLs	164 shared for MAC, IP and IPv6 ACLs		
Packet forwarding rate (64 byte packet size) (Mfps or Mpps)	119.0	238.0	416.6	714.2	
Jumbo frame support	Up to 9K p	packet size	Up to 10K	packet size	
Acoustic noise level @ 25°C (dBA) (ANSI-S10.12)	27.4 dBA	29.1 dBA	41.6 dBA	47.8 dBA	
Mean Time Between Failures (MTBF) @ 25°C	276,197 hours	276,832 hours	514,977 hours	483,808 hours	
L2 SERVICES - VLANS					
IEEE 802.1Q VLAN tagging		Υ	es		
IP-based VLANs		Y	es		
MAC-based VLANs	Yes				
Auto-VoIP VLAN / Auto-Voice VLAN	ves, based on Our bytes (default database and user		Yes, based on OUI bytes (default database and user-based OUIs) in the phone source MAC address, voice packets must have 802.1Q VLAN tag		
Auto-VoIP	Yes, based on protocols (SIP, H.323 and SCCP). Prioritzes traffic to a higher queue			nigher queue	
Voice VLAN	Yes, based on either VL packets are passed onto t using LLI		N	lo	
Auto-Video VLAN	Yes				
Private VLAN		Y	es		

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

PRODUCT	XS708T	XS716T	XS728T	XS748T		
L2 SERVICES - AVAILABILITY	'					
Broadcast, multicast, unknown unicast storm control		Υ	es			
IEEE 802.3ad – LAGs (LACP)		Υ	es			
IEEE 802.3x (full duplex and flow control)		Υ	es			
IEEE 802.1D Spanning Tree Protocol		Υ	es			
IEEE 802.1w Rapid Spanning Tree Protocol		Υ	es			
IEEE 802.1s Multiple Spanning Tree Protocol		Y	es			
L2 SERVICES - MULTICAST FILTERING						
IGMP snooping (v1, v2 and v3)		Υ	es			
MLD snooping support (v1 and v2)		Υ	es			
IGMP snooping queries		Υ	es			
Block unknown multicast		Υ	es			
Multicast VLAN Registration (MVR)	Ye	S	N	10		
L3 SERVICES - DHCP						
DHCP client		Υ	es			
DHCP snooping		Y	es			
L3 SERVICES - ROUTING						
IPv4 static routing	32)	64			
IPv6 static routing	32	2	6	64		
VLAN routing		Y	es			
Host ARP table (number of entries)	73	8	1024			
ICMP Router Discovery Protocol (IRDP)	Ye	S	No			
Number of IP VLAN interfaces (routed VLANs)	15		32			
LINK AGGREGATION						
IEEE 802.3ad - LAGs (LACP)		Yes				
Manual Static LAG		Υ	es			
# of Static or LACP LAGs # of members in each LAG	8 LAGs with max 8 m	embers in each LAG	12 LAGs with max 8 members in each LAG	24 LAGs with max 8 members in each LAG		
NETWORK MONITORING AND DISCOVERY SER	VICES					
802.1ab LLDP		Υ	es			
SNMP		v1, v	2c, v3			
RMON group 1,2,3,9		Υ	es			
NETWORK SECURITY						
IEEE 802.1x	Yes					
Guest VLAN		Υ	es			
RADIUS-based VLAN assignment via .1x	Yes					
MAC-based .1x	Yes					
RADIUS accounting	Yes					
Access Control Lists (ACLs)						
IP-based ACLs (IPv4 and IPv6)	Yes					
MAC-based ACLs		Y	es			

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

XS708T, XS716T, XS728T, XS748T

PRODUCT	XS708T	XS716T	XS728T	XS748T	
TCP/UPD-based ACLs	Yes				
MAC lockdown		Y	es		
MAC lockdown by the number of MACs		Y	es		
Control MAC # Dynamic learned entries		60	00		
Control MAC # static entries	2	0	6	00	
IEEE 802.1x RADIUS port access authentication		Y	es		
Port-based security by locked MAC addresses		Y	es		
Dynamic ARP inspection	Ye	25	1	No	
Broadcast, multicast, unknown unicast storm control		Y	es		
DoS attacks prevention	Ye	25	1	No	
QUALITY OF SERVICE (QOS)					
Port-based rate limiting	Egres	s only	Ingress and egress		
Port-based QoS		Υ	s		
Support for IPv6 fields		Y	es		
DiffServ QoS		Υ	es		
IEEE 802.1p COS		Υ	es		
Destination MAC and IP		Υ	es		
IPv4 and v6 DSCP		Υ	es		
IPv4 and IPv6 ToS		Y	es		
TCP/UDP-based		Y	es		
Weighted Round Robin (WRR)		Υ	es		
Strict priority queue technology		Υ	es		
Auto-VoIP VLAN / Auto-Voice VLAN	Yes, based on OUI byte: user-based OUIs) in the pl		based OUIs) in the phone	default database and user- source MAC address, voice e 802.1Q VLAN tag	
Auto-VoIP	Yes, based on protocols (SIP, H.323 and SCCP). Prioritzes traffic to a higher queue			higher queue	
Voice VLAN	Yes, based on either VLAN ID or 802.1p priority, packets are passed onto the connecting VoIP phone using LLDP-MED		1	No	
Auto-Video VLAN	Yes				

IEEE NETWORK PROTOCOLS

- IEEE 802.3 Ethernet
- IEEE 802.3u 100BASE-T (XS708T/XS716T only)
- IEEE 802.3ab 1000BASE-T
- IEEE 802.3an 10GBASE-T 10Gbps Ethernet Over Copper Twisted Pair Cable
- IEEE 802.3ae 10-Gigabit Ethernet Over Fiber (10GBASE-LRM) XS708T/ XS716T only
- IEEE 802.3ae 10-Gigabit Ethernet Over Fiber (10GBASE-SR, 10GBASE-LR, 10GBASE-ER, 10GBASE-LX4) All models
- IEEE 802.3z Gigabit Ethernet 1000BASE-SX/LX
- IEEE 802.3x Full-Duplex Flow Control

- IEEE 802.1Q VLAN Tagging
- IEEE 802.3ad Trunking (LACP)
- IEEE 802.1AB LLDP with ANSI/TIA-1057 (LLDP-MED)
- IEEE 802.1p Class of Service
- IEEE 802.1D Spanning Tree (STP)
- IEEE 802.1s Multiple Spanning Tree (MSTP)
- IEEE 802.1w Rapid Spanning Tree (RSTP)
- IEEE 802.1x RADIUS Network Access Control
- IEEE 802.3az Energy Efficient Ethernet (EEE)

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

PRODUCT	XS708T	XS716T	XS728T	XS748T	
MANAGEMENT					
Password management		Υ	es		
Configurable management VLAN		Υ	es		
Admin access control via RADIUS and TACACS+	Yes				
IPv6 management		Υ	es		
SNTP client over UDP port 123		Υ	es		
SNMP v1/v2c		Υ	es		
SNMP v3 with multiple IP addresses		Υ	es		
RMON group 1,2,3,9		Υ	es		
Port mirroring		Υ	es		
Many-to-one port mirroring	8	16	8	8	
Web browser-based graphical user interface (GUI)		Υ	es		
Smart Control Center (SCC) for multi-switch management		Υ	es		
Dual software (firmware) image		Y	es		
Dual configuration file		Y	es		
Cable test utility		Y	es		
SSL/HTTPS Web-based access (version)	Yes	(v3)	Yes	(v2)	
TLS Web-based access (version)	Yes (v1.0) Yes (v1.0 ~ v1.2)				
File transfers (uploads, downloads)	TFTP / HTTP				
HTTP upload/download (firmware)		Y	es		
Syslog (RFC 3164)		Y	es		
USB port for firmware and config upload / download		Υ	es		
LEDS					
Per port		Speed, Lir	nk, Activity		
Per device		Power	and Fan		
PHYSICAL SPECIFICATIONS					
Dimensions (W x D x H)	440 x 204 x 43 mm (17.3 x 8 x 1.7 in)	440 x 204 x 43 mm (17.3 x 8 x 1.7 in)	440 x 310 x 43 mm (17.3 x 12.2 x 1.7 in)	440 x 310 x 43 mm (17.3 x 12.2 x 1.7 in)	
Weight	2.61 kg (5.76 lb)	2.98 kg (6.57 lb)	5.04 kg (11.11 lb)	6.25 kg (13.78 lb)	
POWER CONSUMPTION					
Max power (worst case, all ports used, line-rate traffic) (Watts)	49.5 W	96.0 W	134.9 W	262.8 W	
Min power (link-down standby) (Watts)	26.3 W	45.3 W	67. 8W	97.6 W	
Heat Dissipation (max and min) (BTU/hr)	Max: 169.00 BTU Min:: 89.79 BTU	Max: 327.74 BTU Min: 154.65 BTU	Max: 460.55 BTU Min: 231.57 BTU	Max: 897.17 BTU Min: 333.14 BTU	
Energy Efficient Ethernet (EEE) IEEE 802.3az		Yes (deactiva	ted by default)		
Power back-off	N	0	Drops power consumption by 15% to 20% when short copper cables are detected		
Fan	1	2	4	4	

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

PRODUCT	XS708T	XS716T	XS728T	XS748T		
ENVIRONMENTAL SPECIFICATIONS	7,37001	7.57 101	737201	737401		
Operating						
Operating temperature	-5° to 55°C	(23° to 131°F)	0° to 50°C (32° to 122°F)		
Humidity (relative)	90% maximum relative humidity (RH), non-condensing					
Altitude			OOm) maximum			
Storage		.,				
Storage temperature	-10° to 70°C	(– 14° to 158°F)	-20° to 70°C	(– 4° to 158°F)		
Humidity (relative)			numidity, non-condensing			
Altitude			OOm) maximum			
ELECTROMAGNETIC EMISSIONS AND IMMU	JNITY					
Certifications		CE mark, o	commercial			
		FCC Part 15 Clas	ss A, VCCI Class A			
		Class A EN 55022	(CISPR 22) Class A			
	Class A C-Tick					
	EN 55024					
	CCC					
	47 CFR FCC Part 15, SubpartB, Class A					
	ICES-003: 2016 Issue 6, Class A					
	ANSI C63.4:2014					
	IEC 60950-1:2005 (ed.2)+A1:2009+A2:2013					
	AN/NZS CISPR 22:2009+A1:2010 CLASS A					
SAFETY	'					
Certifications	CB mark, commercial					
	CSA certified (CSA 22.2 #950)					
	UL listed (UL 1950)/cUL IEC 950/EN 60950					
	EN 60950-1: 2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013					
	IEC 60950-1:2005 (ed.2)+A1:2009+A2:2013					
	AN/NZS 60950.1:2015					
	CCC (China Compulsory Certificate)					
WARRANTY AND SUPPORT						
ProSAFE Lifetime Warranty		Included	Lifetime*			
Lifetime 24x7 Online Technical Support*		Included,	Lifetime*			
Lifetime Next-Business-Day (NBD) Replacement		Included,	Lifetime*			
ProSUPPORT OnCall 24x7, Category 2**	Category 1:	Category 2:	Category 3:	Category 4:		
Service Packs	PMB0311 (1 yr.) PMB0331 (3 yrs.) PMB0351 (5 yrs.)	PMB0312 (1 yr.) PMB0332 (3 yrs.) PMB0352 (5 yrs.)	PMB0313 (1 yr.) PMB0333 (3 yrs.) PMB0353 (5 yrs.)	PMB0314 (1 yr.) PMB0334 (3 yrs.) PMB0354 (5 yrs.)		

ProSAFE® 10-Gigabit Ethernet Smart Managed Switches

Data Sheet

XS708T, XS716T, XS728T, XS748T

Ordering Information

PACKAGE CONTENT	
All Models	ProSAFE® 10-Gigabit Ethernet Smart Managed Switch
	Power cord (localized to country of sale)
	Rack-mounting kit
	Rubber footpads for tabletop installation
	Quick install guide
	Resource CD with installation guides, Smart Control Center utility software, MIB files, and links to additional online documentation including the Web browser-based management GUI User Manual and datasheet.
ORDERING INFORMATION	
XS708T-100NES	North America, Latin America and Europe
XS708T-100AJS	Asia Pacific and Australia
XS708T-100PRS	China
XS708T-100INS	India
XS716T-100NES	North America, Latin America and Europe
XS716T-100AJS	Asia Pacific and Australia
XS716T-100PRS	China
XS716T-100INS	India
XS728T-100NES	North America, Latin America and Europe
XS728T-100AJS	Asia Pacific and Australia
XS728T-100PRS	China
XS728T-100INS	India
XS748T-100NES	North America, Latin America and Europe
XS748T-100AJS	Asia Pacific and Australia
OPTIONAL MODULES AND ACCESSORIES	
AXM761-10000S	SFP+ Transceiver 10GBASE-SR (Short range, multimode)
AXM762-10000S	SFP+ Transceiver 10GBASE-LR (Long range, single mode)
AXM763-10000S	SFP+ Transceiver 10GBASE-LRM (Long range, multimode) - XS708T/XS716T only
AXM764-10000S	SFP+ Transceiver 10GBASE-LR Lite (Long range lite, single mode)
AGM731F-10000S	SFP Transceiver 1000BASE-SX (Short range, multimode)
AGM732F-10000S	SFP Transceiver 1000BASE-LX (Long range, single mode)
AGM734-10000S	SFP Transceiver 1000BASE-T Copper RJ45 GBIC
AXC761-10000S	SFP+ DAC CABLE (1m)
AXC763-10000S	SFP+ DAC CABLE (3m)

^{*} This product comes with a limited warranty that is valid only if purchased from a NETGEAR authorized reseller, and modifications to product may void the warranty; covers hardware, fans, and internal power supplies – not software or external power supplies; see http://www.netgear.com/about/warranty/ for details. Lifetime technical support includes basic phone support for 90 days from purchase date and lifetime online chat support when purchased from a NETGEAR authorized reseller.

NETGEAR, the NETGEAR Logo, ProSUPPORT and ProSAFE are trademarks of NETGEAR, Inc. in the United States and/or other countries. Other brand names mentioned herein are for identification purposes only and may be trademarks of their respective holder(s). Information is subject to change without notice. © 2016 NETGEAR, Inc. All rights reserved.

^{**} The NETGEAR OnCall 24x7 contract provides unlimited phone and email technical support for your networking product. For ProSAFE products purchased prior to 06/2014, also includes next business-day hardware replacement.

[†] NETGEAR #1 in Fixed Web(Smart)-Managed Worldwide Market Share according to IHS Infonetics Ethernet Switches Market Share and Forecast, 1Q15 Edition, June 2015.