Product data sheet Characteristics

ZB4BZ101

single contact block with body/fixing collar 1NO screw clamp terminal



Range of product	Harmony XB4
Product or component type	Complete body/contact assembly
Device short name	ZB4
Fixing collar material	Zamak
Sale per indivisible quantity	1
Head type	Standard
Contacts type and composition	1 NO
Contact operation	Slow-break
Contact block type	Single
Device composition	Fixing collar Body
Connections - terminals	Screw clamp terminals : $<= 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN 60947-1 Screw clamp terminals : $>= 1 \times 0.22 \text{ mm}^2$ without cable end conforming to EN 60947-1

Complementary

Range of product	Harmony XB4	
Product or component type	Complete body/contact assembly	
Device short name	ZB4	
Fixing collar material	Zamak	
Sale per indivisible quantity	1	
Head type	Standard	
Contacts type and composition	1 NO	
Contact operation	Slow-break	
Contact block type	Single	
Device composition	Fixing collar Body	
Connections - terminals	Screw clamp terminals : $<= 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN 60947-1 Screw clamp terminals : $>= 1 \times 0.22 \text{ mm}^2$ without cable end conforming to EN 60947-1	
Complementary CAD overall width	30 mm	
CAD overall height	47 mm	
040 # # #	-	
CAD overall depth	37 mm	
Terminals description ISO n°1	3/ mm (13-14)NO	
<u> </u>		
Terminals description ISO n°1	(13-14)NO	
Terminals description ISO n°1 Product weight	(13-14)NO 0.053 kg	
Terminals description ISO n°1 Product weight Contacts usage	(13-14)NO 0.053 kg Standard contacts	
Terminals description ISO n°1 Product weight Contacts usage Positive opening	(13-14)NO 0.053 kg Standard contacts Without positive opening 2.6 mm (NO changing electrical state)	
Terminals description ISO n°1 Product weight Contacts usage Positive opening Operating travel	(13-14)NO 0.053 kg Standard contacts Without positive opening 2.6 mm (NO changing electrical state) 4.3 mm (total travel)	
Terminals description ISO n°1 Product weight Contacts usage Positive opening Operating travel Operating force	(13-14)NO 0.053 kg Standard contacts Without positive opening 2.6 mm (NO changing electrical state) 4.3 mm (total travel) 2.3 N (NO changing electrical state)	
Terminals description ISO n°1 Product weight Contacts usage Positive opening Operating travel Operating force Operating torque	(13-14)NO 0.053 kg Standard contacts Without positive opening 2.6 mm (NO changing electrical state) 4.3 mm (total travel) 2.3 N (NO changing electrical state) 0.05 N.m (NO changing electrical state)	
Terminals description ISO n°1 Product weight Contacts usage Positive opening Operating travel Operating force Operating torque Mechanical durability	(13-14)NO 0.053 kg Standard contacts Without positive opening 2.6 mm (NO changing electrical state) 4.3 mm (total travel) 2.3 N (NO changing electrical state) 0.05 N.m (NO changing electrical state) 5000000 cycles	

Short-circuit protection	10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1	
[lth] conventional free air thermal current	10 A conforming to EN/IEC 60947-5-1	
[Ui] rated insulation voltage	600 V (degree of pollution: 3) conforming to EN 60947-1	
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 60947-1	
[le] rated operational current	3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1	
Electrical durability	10000000 cycles, AC-15, 2 A at 230 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 10000000 cycles, AC-15, 3 A at 120 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 10000000 cycles, AC-15, 4 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 10000000 cycles, DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 10000000 cycles, DC-13, 0.5 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C	
Electrical reliability	Λ < 10exp(-6) at 5 V, 1 mA in clean environment conforming to EN/IEC 60947-5-4 Λ < 10exp(-8) at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4	
Compatibility code	ZB4	

Environment

Protective treatment	TH
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-4070 °C
IP degree of protection	IP20 conforming to IEC 60529
Standards	EN/IEC 60947-5-1 EN/IEC 60947-1 EN/IEC 60947-5-5 UL 508 JIS C 4520 EN/IEC 60947-5-4 CSA C22.2 No 14
Product certifications	LROS (Lloyds register of shipping) RINA GL CSA DNV BV UL
Vibration resistance	5 gn (f = 2500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27


Contractual warranty

Warranty period	18 months	

Product data sheet Dimensions Drawings

ZB4BZ101

Dimensions



ZB4BZ101

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board	Connection by Faston Connectors
(2)	(5)

- Diameter on finished panel or support
- 40 mm min. / 1.57 in. min.
- 30 mm min. / 1.18 in. min.
- (1) (2) (3) (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0$ $^{+0.4}$ / 0.88 in. $_0$ $^{+0.016})$
- (5) (6) 45 mm min. / 1.78 in. min.
- 32 mm min. / 1.26 in. min.