

Xmore[®] quality USB Stick 3.0

Product description




Xmore [®] Partnumber	USB016GXQC8B017R	USB064GXQC8B017R
	USB032GXQC8B017R	
Flash Type	Toshiba 15nm MLC	
Capacity	16GB / 32GB / 64GB	
Power Consumption	Normal:	< 82 mA
	Standby:	< 2.5mA
	Read:	< 220 mA
	Write:	< 225 mA
Performance	Read:	Up to 140 MB/s
	Write:	Up to 80 MB/s
Temperature Range	Storage:	-25°C to 85°C
	Operation:	0°C to 70°C
Advance Flash Management	Static and Dynamic wear-leveling	
	Bad Block management	
USB Mode	USB 3.0 (backward compatible to USB2.0/1.1)	

RoHS compliant	USB-IF compliant
EMI compliant	ESD compliant



Technical draw



Version 1.0, short spec., February 2017

A brand of Glyn GmbH & Co. KG All Information according to latest Manufacturer data. Errors and omissions excepted.