



Main

Range of product	Harmony XB5 Harmony XB4
Product or component type	Contact block
Device short name	ZBE
Sale per indivisible quantity	4
IP degree of protection	IP20 IEC 60529
Contacts type and composition	1 NC
Contact operation	Slow-break
Contact block type	Single
Contacts usage	Standard contacts
Connections - terminals	Spring clamp terminals

Complementary

Product weight	0.011 kg
Positive opening	With EN/IEC 60947-5-1 appendix K
Operating travel	1.5 mm NC changing electrical state 4.3 mm total travel
Operating force	2 N NC changing electrical state
Mechanical durability	10000000 cycles
Contacts material	Silver alloy (Ag/Ni)
Electrical reliability	$\Lambda < 10\exp(-7)$ 1 mA in clean environment EN/IEC 60947-5-4 $\Lambda < 10\exp(-8)$ 5 mA in clean environment EN/IEC 60947-5-4
Mounting of block	Front mounting
Condition of use	Mounting on push-button collar
Electrical composition code	C11 \leq 3 C14 \leq 2 M10 \leq 2
Compatibility code	ZBE

Environment

Protective treatment	TH
Ambient air temperature for storage	-40...70 °C

Ambient air temperature for operation	-40...70 °C
Standards	EN/IEC 60947-5-1 UL 508 EN/IEC 60947-1 CSA C22.2 No 14 JIS C 4520 EN/IEC 60947-5-4
Product certifications	CCC DNV LROS (Lloyds register of shipping) UL BV GL RINA CSA GOST
Vibration resistance	5 gn 2...500 Hz IEC 60068-2-6
Shock resistance	30 gn 18 ms half sine wave acceleration IEC 60068-2-27 50 gn 11 ms half sine wave acceleration IEC 60068-2-27

Contractual warranty

Warranty period	18 months
-----------------	-----------