# Product data sheet Characteristics

# ZB5AZ103

single contact block with body/fixing collar 2NO screw clamp terminal



#### Main

Main		ە 
Range of product	Harmony XB5	
Product or component type	Complete body/contact assembly	
Device short name	ZB5	a
Fixing collar material	Plastic	
Sale per indivisible quantity	1	
Head type	Standard	÷
Contacts type and composition	2 NO	
Contact operation	Slow-break	
Contact block type	Single	
Connections - terminals	Screw clamp terminals <= $2 \times 1.5 \text{ mm}^2$ with cable end EN 60947-1 Screw clamp terminals >= $1 \times 0.22 \text{ mm}^2$ without cable end EN 60947-1	v or relia Militic

#### Complementary

Complementary			
CAD overall width	30 mm		
CAD overall height	42 mm		
CAD overall depth	32 mm		
Terminals description ISO n°1	(13-14)NO		
Device composition	Body Fixing collar		
Contacts usage	Standard contacts		
Positive opening	Without positive opening		
Operating travel	2.6 mm (NO changing electrical state) 4.3 mm (total travel)		
Mechanical durability	1000000 cycles		
Tightening torque	0.81.2 N.m conforming to EN 60947-1		
Shape of screw head	Cross head compatible with Philips no 1 screwdriver Cross head compatible with pozidriv No 1 screwdriver Slotted head compatible with flat $\emptyset$ 4 mm screwdriver Slotted head compatible with flat $\emptyset$ 5.5 mm screwdriver		
Contacts material	Silver alloy (Ag/Ni)		
Short-circuit protection	10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1		
[Ith] conventional free air thermal current	10 A conforming to EN/IEC 60947-5-1		
No. 40 0040			

[Ui] rated insulation voltage	600 V (degree of pollution: 3) conforming to EN 60947-1			
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 60947-1			
[le] rated operational current	3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1			
Electrical durability	1000000 cycles, AC-15, 2 A at 230 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 3 A at 120 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 4 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.5 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/ IEC 60947-5-1 appendix C			
Electrical reliability	$\Lambda$ < 10exp(-6) at 5 V, 1 mA in clean environment conforming to EN/IEC 60947-5-4 $\Lambda$ < 10exp(-8) at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4			
Compatibility code	ZB5			

### Environment


Protective treatment	TH
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-4070 °C
IP degree of protection	IP20 conforming to IEC 60529
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 UL 508 CSA C22.2 No 14
Product certifications	BV CSA DNV GL LROS (Lloyds register of shipping) RINA UL
Vibration resistance	5 gn (f = 2500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27

### Contractual warranty

Warranty period

18 months


Dimensions



# **ZB5AZ103**

#### Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) (3) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.  $\emptyset$ 22.5 mm recommended ( $\emptyset$ 22.3  $_0^{+0.4}$ ) /  $\emptyset$ 0.89 in. recommended ( $\emptyset$ 0.88 in.  $_0^{+0.016}$ )

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

## **Detail of Lug Recess**



- Diameter on finished panel or support
- (1) (2) (3) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.  $\emptyset$ 22.5 mm recommended ( $\emptyset$ 22.3  $_0^{+0.4}$ ) /  $\emptyset$ 0.89 in. recommended ( $\emptyset$ 0.88 in.  $_0^{+0.016}$ )