


Secvest Wireless Retrofit Kit for FTS 96 (white)

Art. no. FUFT50008W

Page 1 of 2



- Double your protection by combining mechanical security with electronic monitoring
- Active intrusion protection, thanks to simple upgrading of the mechanical system with electronics
- Even detects intrusion attempts
- Connection points for passive glass break detectors

Connecting mechanical security and electronic monitoring

At first glance, it is difficult to tell the difference between the FTS 96 window lock, which is purely mechanical, and the FTS 96 E wireless window lock, which is electronic. You can use the wireless upgrade kit to prepare the FTS 96 mechanical window lock for use with the Secvest wireless alarm system.

The wireless upgrade kit contains: Electronic unit with circuit board, batteries, rotary knob cover, dust cover for lock and lock casing. Upgrading FTS 96 window locks that have already been installed is simple and uncomplicated and can be done at any time.

Note: We recommend the ABUS wireless test box for optimum detection of the wireless range of the mechatronic products on site.

Secvest Wireless Retrofit Kit for FTS 96 (white)

Art. no. FUFT50008W

Page 2 of 2

Technical Data:

Dimensions	(WxHxD) 78x125x55 mm
Connections	Clamping terminal
Battery type	2 x 1.5 V LR03 AAA alkaline batteries
Width	78 mm
Type of detection	Magnetic field measurement
Radio frequency	868,6625 MHz
Transmission power	10 mW
Housing material	ABS
Height	125 mm
Length	55 mm
Max. battery life	2 year(s)
Max. operating temperature	55 °C

Max. receiving range (outdoors)	100 m
Max. sending range (building)	30 m
Min. operating temperature	-10 °C
Modulation	FM
Installation location	Windows and doors
Tamper monitoring	Yes
Sensor type	Reed contact, magnetic field sensor system
Voltage monitoring	Yes
DC voltage supply	3 V
Environmental class	II