Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com

6724 Joy Road

JUMO Process Control, Inc.



Data Sheet 408401

Page 1/13

JUMO ZELOS C01 LS

Capacitive level switch

Areas of application

- · Food and beverage industry
- Railway applications, according to DIN EN 50155
- · Shipbuilding
- · Mechanical and plant engineering
- · Water and wastewater engineering

Special features

- · Suitable for CIP and SIP processes
- · High pressure resistance and medium temperature
- · Minimization of downtimes due to firmware update profile
- · Standard torque wrench SW22 usable

Description

The capacitive level switch measures the point level of solid and liquid media in applications with requirements for overfill and dry run protection and can also be used for media detection, e.g. in separation and cleaning processes.

The device is suitable for installation in pressurized tanks, pipelines, containers, in hygienic areas and as part of overfill protection systems according to WHG and can be used in explosion-proof areas.



Type 408401



Type 408401



Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road
East Syracuse, NY 13057, USA
Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net

Internet: www.jumousa.com



Data Sheet 408401

Page 2/13

Technical data

Electrical data

Voltage supply	DC 24 V SELV
PNP, NPN, push-pull	DC 9.6 to 36 V
IO-Link	DC 18 to 32 V
Explosion protection Ex i	DC 9.6 to 30 V
Current consumption ^a	
Idle mode	0.45 W
Switch operation with 2 outputs	15 W
IO-Link operation	0.5 W
Protection class	3
Overvoltage category	II
Pollution degree	2
Electrical connection	
Connection elements	M12 plug connector
Connecting cable	
Temperature resistance	≥ 90 °C
Electrical safety	DIN EN 61010-1:2023
Requirements	The device must be equipped with an electrical circuit that meets the requirements with regard to "Limited-energy circuits".

The device labeling indicates a maximum power consumption in switching mode with 2 outputs including self-consumption. The actual power consumption depends on the connected load.

Inputs

Hysteresis	±1 mm
Repeatability	±1 mm
Switch-on delay	< 2 s, during this time the switching outputs are blocked
Switching delay	Adjustable 0.3 to 60 s
When the sensor is covered	0.5 s
When the sensor is uncovered	1 s
Filter time constant	Adjustable 0 to 100 s

Outputs

Number	
For IO-Link operation	1 (output signal according to IO-Link communication standard version 1.1)
For switching operation	2 (SIO mode; SIO = standard IO)
With PNP, NPN, push-pull	2
Configuration options	Hysteresis or window function, switching function, NC contact or NO contact, output p-switching (PNP) or n-switching (NPN), switch-on and switch-off delay, pulse-width modulation (PWM), pollution degree detection, wet test with medium
Pulse-width modulation (PWM)	
Period duration adjustable	50 to 1000 ms
Mark-to-space ratio	0 to 100 %
Switching current	≤ 200 mA per output
Voltage drop at switching transistor	≤1V
Short-circuit resistance	Yes (clocked)
Reverse voltage protection	Yes
Current limiting	Yes

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany Postal address: 36035 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD

JUMO House
Temple Bank, Riverway
Harlow, Essex, CM20 2DY, UK
Phone: +44 1279 63 55 33
Fax: +44 1279 62 50 29
Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com



Data Sheet 408401

Page 3/13

Interface

IO-Link

Communication	Via end device with IO-Link master and device description file (IODD)		
Communication interface	IO-Link device V 1.1		
Data transfer rate (baud rate)	COM3 (230.4 kBaud)		
Max. cable length	20 m, unshielded		
Min. cycle time	0.7 ms		
Function	Transfer of process data, configuration data, and device information		
Profiles	Common Profile, Smart Sensor Profile, Firmware Update Profile		
IO Device Description (IODD)	Depending on the ordered operating temperature range; available on the manufacturer's website https://en.jumo.de or at www.ioddfinder.io-link.com		
Menu navigation	According to VDMA 24574-4		

Display

Color display	According to NE107, IO-Link, customer-specific		
Brightness	4 levels (configurable)		
Self-diagnosis/self-monitoring	According to NE107 and VDI/VDE 2650		

Environmental influences

100 % relative humidity including condensation on the device outer case			
90 % relative humidity without condensation			
-40 to +80 °C (fixed), -25 to +80 °C (movable)			
-40 to +85 °C			
-40 to +80 °C			
-40 to 115 °C (standard), <1 h/d to 135 °C and T _{amb} <50 °C			
-40 to +200 °C (for versions with sliding connection)			
-1 to +60 bar			
DIN EN 60529			
IP69			
IP67			
5300 m above sea level			
DIN EN 61326-1:2022			
Class B ^a			
Class A ^b			
Industrial requirement			
Domestic requirement			
IEC 60068-2-6, DIN EN 61373, DIN EN 50155, category 1 B			
4 g at 25 to 100 Hz			
3 g (vertical) or 5 g (transverse and longitudinal) for 30 ms			
I Indoors			

^a The product is suitable for industrial use as well as for households and small businesses.

b The product is only suitable for industrial use.

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD JUMO House

Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6724 Joy Road
East Syracuse, NY 13057, USA
Phone: +1 315 437 5866
Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 408401

Mechanical features

Materials	
Parts in contact with the medium	
Process connection	PEEK (depending on sealing concept stainless steel 316 L)
Sliding connection 360, 361	PEEK, FKM/FPM, stainless steel 316 L
Parts not in contact with the medium	
Housing	Stainless steel 316 L
Connection cable	PUR
Surface roughness	R _a ≤ 0.8 μm
Cable bending radius	
Fixed	r ≥ 21 mm
Movable	r ≥ 42 mm
Installation position	Any
Weight	60 g for G1/2" with M12 plug connector

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD JUMO House

Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 +44 1279 62 50 29 Fax: Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6724 Joy Road East Syracuse, NY 13057, USA


Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 408401

Dimensions

Device



Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk


JUMO Process Control, Inc.


6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com




Data Sheet 408401

Process connections






Α Immersion depth, PEEK tip 12.5 mm



Α Immersion depth, PEEK tip 12.5 mm

Α Immersion depth, PEEK tip 12.5 mm



Α Immersion depth, PEEK tip 12.5 mm

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD


JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 408401



Length 100 mm or 250 mm

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD JUMO House

Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 +44 1279 62 50 29 Fax: Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6724 Joy Road East Syracuse, NY 13057, USA


Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 408401

Page 8/13

Cable



Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29

Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com




Data Sheet 408401

Connection elements


The connection diagram in the data sheet provides information on product selection.

For the electrical connection, only use the installation instructions or the operating manual.



Terminal assignment

M12 plug connector



Designation	Description	Assignment ^a	
IO-Link	L+	1 BN (brown)	
	L-	3 BU (blue)	
	I/Q = OUT2	2 WH (white)	
	C/Q = IO-Link	4 BK (black)	
PNP	L+	1 BN (brown)	
	L-	3 BU (blue)	
	OUT2	2 WH (white)	
	OUT1	4 BK (black)	
NPN	L+	1 BN (brown)	
	L-	3 BU (blue)	
	OUT2	2 WH (white)	
	OUT1	4 BK (black)	
push-pull	L+	1 BN (brown)	
	L-	3 BU (blue)	
	OUT2	2 WH (white)	
	OUT1	4 BK (black)	

The color coding is only valid for A-coded standard cables!

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

6724 Joy Road
East Syracuse, NY 13057, USA
Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com

JUMO Process Control, Inc.

JUMO

Data Sheet 408401


Page 10/13

If connected to a certified intrinsically safe electrical circuit [Ex i], the following values are given.


Output signal	Max. voltage U _i	Max. current U _i	Max. power P _i	Inner inductance	Inner capacitance
	in V	in mA	in mW	in μH	in nF
PNP	≤ 30	≤ 100	≤ 750	57	35
NPN				For cable version 1 µH/m	For cable version 0,2 nF/
push-pull				add connecting cable	m add connecting cable

Connection examples

Standard



Ex i



Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com




Data Sheet 408401

Page 11/13


Current limiting for capacitive loads

In the case of capacitive loads, the switching contact (S) must be protected with a resistor.



Protective circuit for inductive loads for capacitive loads

In the case of inductive loads, the switching contact (S) must be protected with a flyback diode.



Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net www.jumo.net Internet:

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 408401

Order details

	(1)	Basic type
408401		JUMO ZELOS C01 LS – Capacitive level switch
	(2)	Basic type extension
000		None
062		Shipbuilding approval
065		Hygienic design
262		WHG approval
263		WHG approval, explosion protection, intrinsically safe, Ex i
265		WHG approval, explosion protection, intrinsically safe, Ex i, and hygienic design
362		Explosion protection, intrinsically safe, Ex i
365		Explosion protection, intrinsically safe, Ex i, and hygienic design
662		Shipbuilding approval and explosion protection, intrinsically safe, Ex i
	(3)	Electrical connection
036		M12 plug connector
170		Cable, PUR
	(4)	Cable length
0		None
2000		2,000 mm
5000		5,000 mm
10000		10,000 mm
	(5)	Process connection
105		Fitting G 3/4"
133		Fitting M24 × 1.5
360		Sliding connection, G 1/2", 100 mm adjustable
361		Sliding connection, G 1/2", 250 mm adjustable
387		Fitting G 1/2" with PEEK seal
997		JUMO PEKA – Hygienic process connection
	(6)	Output
447		Digital (push-pull)
458		IO-Link measured value transmission, including digital output
469		NPN switching output
470		PNP switching output
	(7)	Medium temperature
487		-40 to +200 °C
500		-40 to +115 °C
	(8)	Extra codes
061		UL approval
374		acceptance test certificate 3.1 Material DIN EN 10204
634		TAG number
950		Railway application



Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD JUMO House

Temple Bank, Riverway
Harlow, Essex, CM20 2DY, UK
Phone: +44 1279 63 55 33
Fax: +44 1279 62 50 29
Email: sales@jumo.co.uk
Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866

Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 408401

Page 13/13

Stock versions

Order code	Part no.
408401/000-036-0-387-458-500/061	00771685
408401/065-036-0-387-458-500/061	00771693
408401/065-036-0-387-470-500/061	00771694
408401/362-036-0-387-470-500/061	00771696
408401/062-036-0-387-470-500/061	00771699

Accessories

When using a device with UL application, the user has to ensure that the accessories he uses are also approved for a UL application (e.g. cables with UL approval AVLV2/8 suitable for external connection and/or cables with UL approval CYJV/7 or CYJV/8 or PVVA/7 or PVVA2/8, each approved for ambient temperatures > 80 °C).

Designation	Part no.
Connection line M8/voltage supply, length 2 m, IO-Link master, 4 channel, with UL approval	00767913
Connection line M8/Ethernet, length 2 m, IO-Link master, 4 channel, with UL approval	00767923
Connection line M12/voltage supply, length 2 m, IO-Link master, 8 channel, with UL approval	00767914
Connection line M12/Ethernet, length 2 m, IO-Link master, 8 channel, with UL approval	00767927
USB IO-Link master, 1-channel	00694070
IO-Link master, 4 channel, with UL approval	00759867
IO-Link master, 8 channel, with UL approval	00759875
Magnetic pen for teach function	00736330
Welding socket G 1/2" for process connection 387	00378264
Adapter G 1/2" VARIVENT Type N DN 50/40	30054461
T-piece with PEKA connection DN 100	00643582
T-piece with PEKA connection DN 80	00643581
T-piece with PEKA connection DN 65	00643580
T-piece with PEKA connection DN 50	00643579
T-piece with PEKA connection DN 40	00643576
T-piece with PEKA connection DN 32	00643574
T-piece with PEKA connection DN 25	00643555
T-piece with screw connection G 1/2" DN 100	00772334
T-piece with screw connection G 1/2" DN 80	00772333
T-piece with screw connection G 1/2" DN 65	00772332
T-piece with screw connection G 1/2" DN 50	00772331
T-piece with screw connection G 1/2" DN 40	00772330
T-piece with screw connection G 1/2" DN 32	00772321
T-piece with screw connection G 1/2" DN 25	00772316
Configuration cable for Ex devices	30048990
Connection line M12, M12, black, PUR, length 2 m (straight coupling/straight connector; 5 pole; A-coded)	00777804
Cable PUR, 4 × 0.34, black, length 2 m, with UL approval	00776248
Cable PUR, 4 × 0.34, black, length 5 m, with UL approval	00776250
Cable PUR, 4 × 0.34, black, length 10 m, with UL approval	00776252
Line socket, 4-pole, M12 × 1, straight, length 2 m	00404585
Line socket, 4-pole, M12 × 1, angled, length 2 m	00409334
Sealing ring A24 × 2 - Vf for process connection 133	00704485
Sealing ring A26 × 2 - Vf for process connection 105	30049315
Service deployment	00427970
Preconfiguration (Service)	00427968