

Product Data Sheet

9295420303

VWS0148PULDS

6318N/2TDH3P-303

**ebmpapst**

The engineer's choice



6318N/2TDH3P-303

INDEX

**1 General ..... 3**

**2 Mechanics ..... 3**

    2.1 General..... 3

    2.2 Connections..... 3

**3 Operating Data ..... 5**

    3.1 Electrical Interface - Input..... 5

    3.2 Electrical Operating Data ..... 6

    3.3 Electrical Interface - Output..... 7

    3.4 Electrical Features ..... 8

    3.5 Data According ErP Directive ..... 8

    3.6 Aerodynamics ..... 9

    3.7 Sound Data..... 10

**4 Environment..... 10**

    4.1 General..... 10

    4.2 Climatic Requirements ..... 10

    4.3 Mechanical Requirements..... 11

**5 Safety..... 13**

    5.1 Electrical Safety ..... 13

    5.2 Approval Tests ..... 13

**6 Reliability..... 13**

    6.1 General..... 13

**1 General**


Fan type	Fan	
Rotating direction looking at rotor	Counterclockwise	
Airflow direction	Air outlet over struts	
Bearing system	Ball bearing	
Mounting position - shaft	Any	

**2 Mechanics****2.1 General**

Depth	51,0 mm	
Diameter	172,0 mm	
Mass	0,875 kg	
Housing material	Metal	
Impeller material	Plastic	
Max. torque when mounted across both mounting flanges Screw size	Wire outlet corner: 440 Ncm Remaining corners: 440 Ncm ISO 4762 - M4 degreased, without an additional brace and without washer	

**2.2 Connections**

Electrical connection	Wires	
Lead wire length	L = 365 mm	
Tolerance	+ - 10,0 mm	
Tube length	S = 10 mm	
Tolerance	+ - 5,0 mm	



Wire	Color	Operation	Wire size	Insulation diameter
1	red	+ UB	AWG 20	2,05 mm
2	blue	- GND	AWG 20	2,05 mm
3	violet	PWM	AWG 22	1,7 mm
4	white	Tacho	AWG 22	1,7 mm

The auxiliaries shown on the schematic diagram (which are required for the intended use) are not part of our delivery.

Lead wire 1 - 2: AWG20 (Insulation diameter 2,05 mm)  
 Lead wire 3 - 4: AWG22 (Insulation diameter 1,70 mm)



3 Operating Data

3.1 Electrical Interface - Input

Control input	PWM
---------------	-----

Features

Input type	Open collector	
PWM - Frequency		1 kHz - 20 kHz typical: 2 kHz



The shown pull-up resistor R1 to the internal reference voltage (+5V) has 4.7kOhm.

**Information to the curve:**

- 0% - <=7% PWM: 0 1/min (Fan off)
- 7% PWM: 1.000 1/min (Start-up, coming from 0% PWM)
- 7% - 10 % PWM: 1.000 1/min (corresp. to min fan speed)

10% - 90% PWM: Linear increasing curve  
 90% - 100% PWM: 7.500 1/min (corresp. to max fan speed)  
 5% PWM: 800 1/min or 0 1/min (Fan turns off, coming from 100% PWM)

**Transistor Requirements:**

VCE max.  $\geq$  12V  
 Isink max  $>$  5mA  
 VCEsat  $<$  0,15V

**3.2 Electrical Operating Data**

Measurement conditions: Normal air density = 1,2 kg/m<sup>3</sup>; Temperature 23°C +/- 3°C; Motor axis horizontal; warm-up time before measuring 5 minutes (unless otherwise specified). In the intake and outlet area should not be any solid obstruction within 0,5 m.

$\Delta p = 0$ : corresp. to free air flow (see chapter aerodynamics)  
 I: corresp. to arithm. mean current value


Name	Condition
PWM 0001	PWM: 95 %; f: 2 kHz

**>90% PWM; f = 2 kHz or broken lead wire (open control input)**

Features	Condition	Symbol	Values	
Voltage range		U	36 V	72,0 V
Nominal voltage		$U_N$		48,0 V
Power consumption	$\Delta p = 0$	P		160 W
Tolerance	PWM 0010			
Current consumption	$\Delta p = 0$	I		3.330 mA
Tolerance	PWM 0010			
Speed	$\Delta p = 0$	n		7.500 1/min
Tolerance	PWM 0010			


3.3 Electrical Interface - Output

Tacho type	/2 (open collector)
------------	---------------------



$$R_a = \frac{U_{BS} - U_{S\ low}}{I_{sink}}$$

Lüfter / Fan      Kunde / Customer




Features	Note	Values
Tacho operating voltage	$U_{BS}$	$\leq 60\text{ V}$
Tacho signal Low	$U_{S\ low}$	$\leq 0,4\text{ V}$
Tacho signal High	$U_{S\ high}$	$\leq 60\text{ V}$
Maximum sink current	$I_{sink}$	$\leq 20\text{ mA}$
External resistor	External resistor $R_a$ from $U_{BS}$ to $U_S$ required. All voltages measured to GND.	
Tacho frequency	$(6 \times n) / 60$	750 Hz
Tacho isolated from motor	No	
Slew rate		$\Rightarrow 0,5\text{ V/us}$

n = revolutions per minute (1/min)

### 3.4 Electrical Features

Electronic function	Speed-Controlled	
Reversed polarity protection	P-CH FET	
Max. residual current at $U_N$	$I_F \leq 5 \text{ mA}$	
Locked rotor protection	Auto restart	
Locked rotor current at $U_N$	$I_{\text{block}}$ approx. 1.000 mA	
Clock signal at locked rotor	$t_3 / t_4$ typical: 5 s / 10,0 s	
Internal fuse	Littelfuse NANO2 > Very Fast-Acting > 451/453 Series 12A / 75V (Art.No.: 0451012.MRL)	
Voltage control *)	Fan turns on at $U_B > 33 \text{ V}$ or $< 76 \text{ V}$ Fan turns off at $U_B < 31 \text{ V}$ or $> 78 \text{ V}$	

\*) This fan has an undervoltage and overvoltage control circuit integrated which turns the motor off if the voltage is out of range.



This fan has a startup delay of 2 seconds after applying supply voltage.

### 3.5 Data According ErP Directive

Installation / Efficiency category	A / static
Speed control	integrated
Specific ratio	1,00457
Target overall efficiency 2015	29,2 %
Overall efficiency	48,9 %
Efficiency grade	40
Power input	194 W
Speed	7.400 1/min

All values measured in optimum energy efficiency point.

Productiondatecode is printed on the fan label.




3.6 Aerodynamics

Measurement conditions: Measured with a double chamber intake rig acc. to DIN EN ISO 5801. Normal air density = 1,2 kg/m<sup>3</sup>; Temperature 23°C +/- 3°C; In the intake and outlet area should not be any solid obstruction within 0,5 m. Motor shaft horizontal. The information is only valid under the specified test conditions and may be changed by the installation conditions. If there are deviations from the standard test conditions, the characteristic values must be checked under the installed conditions. Power consumption of the fan motor when operating at normal voltage is shown. Depending on the operating conditions of the application, the power input may be higher.

a.) Operation condition:

7.500 1/min at free air flow	PWM 95 %; f: 2 kHz		
------------------------------	--------------------	--	--

Max. free-air flow ( $\Delta p = 0 / \dot{V} = \text{max.}$ )	1.040 m <sup>3</sup> /h	
Max. static pressure ( $\Delta p = \text{max.} / \dot{V} = 0$ )	1.100 Pa	



### 3.7 Sound Data

Measurement conditions: Sound pressure level: 1 meter distance between microphone and the air intake.  
Sound power level: Acc. to DIN 45635 part 38 (ISO 10302)  
Measured in a semianchoic chamber with a background noise level of  $L_p(A) < 5 \text{ dB(A)}$   
For further measurement conditions see chapter aerodynamics.

a.) Operation condition:

7.500 1/min at free air flow	PWM 95 %; f: 2 kHz		
------------------------------	--------------------	--	--

Optimal operating point	@ 310 Pa		
Sound power level at the optimal operating point	8,3 bel(A)		
Sound pressure level at free air flow, measured in rubber bands	75 dB(A)		

## 4 Environment

### 4.1 General

Min. permitted ambient temperature TU min.	-20 °C		
Max. permitted ambient temperature TU max.	70 °C		
Min. permitted storage temperature TL min.	-40 °C		
Max. permitted storage temperature TL max.	80 °C		

### 4.2 Climatic Requirements

Humidity requirements	humid heat, constant; according to DIN EN 60068-2-78, 14 days		
Water exposure	None		
Dust requirements	None		
Salt fog requirements	None		

Permitted application area:

The product is intended for use in sheltered rooms with controlled temperature and controlled humidity. Directly exposure to water must be avoided.

Pollution degree 1 (according DIN EN 60664-1)

There is either no pollution or it occurs only dry, non-conductive pollution. The pollution has no negative impact.

4.3 Mechanical Requirements

severity level	Vibration (sinusoidal)	
1 G	Vibration (sinusoidal) in use IEC 60068-2-6 Displacement / frequency range Acceleration / frequency range Sweep rate Sweep cycles Duration Axes of vibration	Vibration (sinusoidal) 0,075 mm / 10-58, 58-10 Hz 1 G / 58-500-58 Hz 1 Oct./min 10 2 hrs. 3

severity level	stationary use		
1	storage / transportation	Random vibration not in use IEC 60068-2-64 Frequency range / ASD  G <sub>RMS</sub> Axes of vibration Test duration	Random vibration 5 - 20 Hz : 1,0 m <sup>2</sup> / s <sup>3</sup> 20 - 500 Hz : - 3 dB / Oct 0,91 G 3 3 x 5 h
	storage / transportation	Bump not in use IEC 60068-2-29 Shock spectrum Acceleration Duration Number of bumps (+X, -X, -Y, +Y, -Z, +Z) Total bumps	Bump half sine 18 G 6 ms 100 in each direction 600
	stationary use	Random vibration in use IEC 60068-2-64 Frequency range / ASD  G <sub>RMS</sub> Axes of vibration Test duration	Random vibration 5 - 20 Hz : 2,0 m <sup>2</sup> / s <sup>3</sup> 20- 150 Hz : - 3 dB / Oct 0,83 G 3 3 x 5 h
	stationary use	Bump in use IEC 60068-2-29 Shock spectrum Acceleration Duration Number of bumps (+X, -X, -Y, +Y, -Z, +Z) Total bumps	Bump half sine 5 G 11 ms 100 in each direction 600

severity level	Railroad application	
1 IEC 61373 Category 1	Random vibration in use IEC 60068-2-64 Frequency range / ASD	Random vibration 5 - 20 Hz : 2,0 m <sup>2</sup> / s <sup>3</sup>

Class B	$G_{RMS}$ Axes of vibration Test duration	20- 150 Hz : - 3 dB / Oct 0,83 G 3 3 x 5 h
	Shock in use IEC 60068-2-27 Shock spectrum Acceleration Duration Number of bumps (+X, -X, -Y, +Y, -Z, +Z) Total bumps	Shock half sine 7 G 18 ms 10 in each direction 60

## 5 Safety

### 5.1 Electrical Safety

Dielectric strength DIN EN 60950 (VDE 0805) and DIN EN 60335 (VDE 0700) A.) Type test Measuring conditions: After 48h of storage at 95% R.H. and 25°C. No arcing or breakdown is allowed! All connections together to ground.	1000 VAC / 1 Min.	
B.) Routine test Measuring conditions: At indoor climate. No arcing or breakdown is allowed! All connections together to ground.	1700 VDC / 1 Sec.	
Isolation resistance Measuring conditions: After 48h of storage at 95% R.H. and 25°C measured with U=500 VDC for 1 min.	RI > 10 MOhm	
Clearance / creepage distance	1,0 mm / 1,5 mm	
Protection class	I	


### 5.2 Approval Tests

CE	EC Declaration of Conformity	Yes
EAC	Eurasian Conformity	Yes
UL	Underwriters Laboratories	Yes / UL507, Electric Fans E38324
VDE	Association for Electrical, Electronic and Information Technologies	Yes / Approval acc. to EN 60950 (VDE 0805) - Information technology equipment
CSA	Canadian Standards Association	Yes / C22.2 No. 113 Fans and Ventilators
CCC	China Compulsory Certification	Yes / GB 12350 Safety Requirements for small Power Motors

## 6 Reliability

### 6.1 General

Life expectancy L10 at TU = 40 °C	57.500 h	
Life expectancy L10 at TU max.	35.000 h	
Life expectancy L10 acc. to IPC 9591 at TU = 40 °C	97.5 00 h	



Copyright of this document, and giving its status and the use or commission of the contents thereof, are  
 forbidden without express written consent. Therefore the status of the document is "draft". All rights are reserved.  
 Schutzwerk nach DIN ISO 9001:2015 nachher 1  
 Refer to protection holes DIN ISO 9001:2015

- 1.) Maße aus Montageausschnitt
  - 2.) Anzahl und Länge der Litzen/Schlauch  
siehe Produktspezifikation
  - 3.) Erdungsschraube nur wenn in der  
Luftergehäusestueckliste enthalten
- Axialspiel der Kugellager mit Feder  
spielfrei gelagert

- 1.) measures of mounting cut out
  - 2.) length an number of wires/tube see  
product specification
  - 3.) grounding screw only if contained in the  
fan housing part list
- ball bearing without clearance by a pre-  
load spring

Document Status / Document-Status	CD / Zeichnung / CAD-Drawing	Revision / Material	Volume / Menge / Quantity / Mass (t)
Part No. / Change No.	DATE / Datum	Part No. / Title	Form / Zeich. / Revision
Table / Drawing / Tolerances	SP-Referenzmodell / SP-Referenzmodell	Doc. No. / Drawing No.	Document Type / Type of Document
General Information / Gen. Information	ebmpapst	Doc. No. / Drawing No.	Form / Zeich. / Revision
	ebmpapst	Doc. No. / Drawing No.	Form / Zeich. / Revision
	ebmpapst	Doc. No. / Drawing No.	Form / Zeich. / Revision