BPW41N

Vishay Semiconductors

Silicon PIN Photodiode

FEATURES

- Package type: leaded
- · Package form: side view
- Dimensions (in mm): 5 x 4 x 6.8
- Radiant sensitive area (in mm²): 7.5
- High radiant sensitivity
- · Daylight blocking filter matched with 940 nm emitters
- Fast response times
- Angle of half sensitivity: $\varphi = \pm 65^{\circ}$
- · Compliant to RoHS Directive to 2002/95/EC and in accordance to WEEE 2002/96/EC

Note

Please see document "Vishay Material Category Policy": www.vishay.com/doc?99902

APPLICATIONS

- · High speed detector for infrared radiation
- · Infrared remote control and free air data transmission systems, e.g. in combination with TSALxxxx series IR emitters

PRODUCT SUMMARY				
COMPONENT	I _{ra} (μΑ)	φ (deg)	λ _{0.5} (nm)	
BPW41N	45	± 65	870 to 1050	

Note

DESCRIPTION

900 nm to 950 nm IR emitters.


Test condition see table "Basic Characteristics"

ORDERING INFORMATION				
ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM	
BPW41N	Bulk	MOQ: 4000 pcs, 4000 pcs/bulk	Side view	

Note

• MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage		V _R	60	V
Power dissipation	T _{amb} ≤ 25 °C	Pv	215	mW
Junction temperature		Tj	100	°C
Operating temperature range		T _{amb}	- 40 to + 100	°C
Storage temperature range		T _{stg}	- 40 to + 100	°C
Soldering temperature	t ≤ 5 s	T _{sd}	260	°C
Thermal resistance junction/ambient	Connected with Cu wire, 0.14 mm ²	R _{thJA}	350	K/W






RoHS

COMPLIANT

GREEN (5-2008)**



BPW41N is a PIN photodiode with high speed and high

radiant sensitivity in a black, side view plastic package with

daylight blocking filter. Filter bandwidth is matched with

www.vishay.com



www.vishay.com

Vishay Semiconductors

BASIC CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Breakdown voltage	I _R = 100 μA, E = 0	V _(BR)	60			V
Reverse dark current	$V_{R} = 10 V, E = 0$	I _{ro}		2	30	nA
Diada conceitance	V _R = 0 V, f = 1 MHz, E = 0	CD		70		pF
Diode capacitance	V_{R} = 3 V, f = 1 MHz, E = 0	CD		25	40	pF
Open circuit Voltage	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	Vo		350		mV
Temperature coefficient of Vo	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	TK _{Vo}		- 2.6		mV/K
Short circuit current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	l _k		38		μA
Temperature coefficient of I_k	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	TK _{lk}		0.1		%/K
Reverse light current	$E_e = 1 \text{ mW/cm}^2, \lambda = 950 \text{ nm}, V_R = 5 \text{ V}$	I _{ra}	43	45		μA
Angle of half sensitivity		φ		± 65		deg
Wavelength of peak sensitivity		λρ		950		nm
Range of spectral bandwidth		λ _{0.5}		870 to 1050		nm
Noise equivalent power	$V_{\rm R} = 10 \text{ V}, \lambda = 950 \text{ nm}$	NEP		4 x 10 ⁻¹⁴		W/√ Hz
Rise time	$V_R = 10 \text{ V}, \text{ R}_L = 1 \text{ k}\Omega, \lambda = 820 \text{ nm}$	tr		100		ns
Fall time	V_R = 10 V, R_L = 1 k Ω , λ = 820 nm	t _f		100		ns

BASIC CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)





Fig. 1 - Relative Reverse Light Current vs. Ambient Temperature








Fig. 3 - Reverse Light Current vs. Reverse Voltage



2 For technical questions, contact: <u>detectortechsupport@vishay.com</u> Document Number: 81522

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Vishay Semiconductors




www.vishay.com

Fig. 5 - Relative Spectral Sensitivity vs. Wavelength



SHA







Fig. 6 - Relative Radiant Sensitivity vs. Angular Displacement



Rev. 1.6, 23-Aug-11

3

Document Number: 81522

For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.