

Type: DA12-NA40/Axxx

DC Current/Voltage

V/mA




DA12-NA40/A10x-7

Case 72 x 72 mm



DA12-NA40/A10x-4


Case 72 x 48 mm



positions of push-buttons with package size 72 x 36 / 48 / 72 mm (w x h)

DA12-NA40/A10x-3

Case 72 x 36 mm




DA12-NA40/A10x

Case 72 x 24 mm




Controls behind front glass




programming mode

enter into programing mode and to the next menu-position by operating of push-button T3

menupos.	display	description
0	P 0	enter min. display value select digit with T2 adjust digit with T1
1	P 1	P-L min input signal (to be applied) take over with T2
2	P 2	enter max. display value select digit with T2 adjust digit with T1
3	P 3	P-H max input signal (to be applied) take over with T2
4	P 4	-- 99 - L - - average value of 1-99 measurements Line-break indication with value falling 25% below measured value - = no 1 = yes
5	P 5	2/5/10 half correction of last digit by steps of 2, 5 or 10
6	--- 1	reciprocal indication value 0 = no 1 = yes
	- 0 - -	brightness adjustment (0 ... 9) 0 = bright 9 = dark
	EEP	EEPROM under programming, instrument changes into standard mode



rear connector with screw-type terminals




display- messages

EEP	EEPROM under programming
----	Overflow (flashing of display-segments in the middle)
-	Line-break indication


Technical data

aux. supply:	18-35V DC
power consumption:	max. 2,5 VA
measuring range V:	2V / 10V / 40V / 200V
measuring range A:	20mA / 200mA
display max.:	programmable
display min.:	programmable
conversion rate:	approx. 1 per second
principle of measurement:	dual-slope-integration
error of measurement:	+/- 0,01% of measuring value +/- 1 digit/segment
overflow:	flashing of display segments in the middle
average value:	adjustable from 1 to 99 measurements
display:	14 mm, LED red or green

input resistance:	terminal	1	Ri	100	kOhm
		2		560	kOhm
		3		2,2	MOhm
		4		12	MOhm
		6		100	Ohm
		7		10	Ohm
resolution:		-1999 ... 9999			
panel cutout:	DA12-NA40/A10x:	68(+0,7) x 22,2(+0,3) mm			
	DA12-NA40/A10x-3:	68(+0,7) x 33(+0,6) mm			
	DA12-NA40/A10x-4:	68(+0,7) x 45(+0,6) mm			
	DA12-NA40/A10x-7:	68(+0,7) x 68(+0,7) mm			
mounting depth:	110 mm				
bezel height:	5,25 mm				



without indication = 72 x 24 mm	3 = 72 x 36 mm	4 = 72 x 48 mm	7 = 72 x 72 mm
R = red	G = green		
1 = 24VDC			
A = DC current/voltage			
40 = 4 digits			



GS Gebhardt & Schäfer Industrie-Elektronik GmbH

Moltkestraße 44a, D-42799 Leichlingen
Postfach 15 52, D-42786 Leichlingen
Tel. +49 (0) 21 75 / 89 91 30
Fax +49 (0) 21 75 / 89 91 39
Internet: <http://www.GS-GmbH.de>
E-Mail: info@GS-GmbH.de

Deutsche Bank 24
Konto-Nr. 851 085 100
BLZ 375 700 24
Kreissparkasse Köln
Konto-Nr. 031 200 61 45
BLZ 370 502 99

Foreign Payments:
Deutsche Bank 24
Account-No. 851 085 1
Bank Code 375 700 24
IBAN DE30375700240851085100
BIC / SWIFT-Code DEUTDE33

Geschäftsführer:
Karlheinz Schäfer
Guido Gebhardt
USt.-Nr. DE 123713297
Amtsgericht Köln
HRB 48860