Technical Data Sheet 10 Bar Graph Displays

Features :

- Industrial standard size.
- Low power consumption.
- Categorized for luminous intensity.
- Pb free
- The product itself will remain within RoHS compliant version
- Descriptions :
- The ELB-1001 series are ten-element
 - bar graph displays. designed for
 - viewing distances up to 7 meters.
 - There are separate anodes and
- cathodes for each light segment and choice of five colors is offered.
- These devices are made with white segments and gray surface.

Applications :


- Audio equipment
- Instrument panels
- Digital read out display

	Chip		
PART NO.	Material	Emitted Color	
ELB-1001SYGWA/S530-E2	AlGaInP	Super Yellow Green	

A0211074 50001469

EVERLIGHT ELECTRONICS CO.,LTD. Device Number :CDDB-100-027 http://www.everlight.com Prepared date:2006/3/8 Rev.: 2 Page: 1 of 6 Prepared by: YanLi Zhong

ELB-1001SYGWA/S530-E2








Technical Data Sheet 10 Bar Graph Displays

ELB-1001SYGWA/S530-E2

Package Dimensions



Notes: 1.All dimensions are in millimeters , tolerance is 0.25mm unless otherwise noted.2.Above specification may be changed without notice.Supplier will reserve authority on material change for above specification.

EVERLIGHT ELECTRONICS CO.,LTD. Device Number :CDDB-100-027 http://www.everlight.com Prepared date:2006/3/8 Rev.: 2 Page: 2 of 6 Prepared by: YanLi Zhong

Technical Data Sheet 10 Bar Graph Displays

EVERLIGHT

ELB-1001SYGWA/S530-E2

Parameter	Symbol	Rating	Unit
Reverse Voltage	VR	5	V
Forward Current	IF	25	mA
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40 to +100	°C
Soldering Temperature *	Tsol	260 ± 5	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	60	mW

Absolute maximum ratings at $Ta = 25^{\circ}C$:

Note: *Soldering time \leq 5 seconds.

Electronic optical characteristics :

Parameter		Symbol	Min.	Тур.	Max.	Unit	Condition	
Luminous Intensity	Per segment	Iv		2.0		mcd	IF=2mA	
			2.8	4.5		mcd	IF=10mA	
Peak Wavelength		λp		575		nm	IF=20mA	
Dominant Wavelength		λd		573		nm	IF=20mA	
Spectrum Radiation Bandwidth		$ riangle \lambda$		20		nm	IF=20mA	
Forward Voltage		VF		2.0	2.4	V	IF=20mA	
Reverse Current		IR			100	μA	VR=5V	

EVERLIGHT ELECTRONICS CO.,LTD. Device Number :CDDB-100-027


http://www.everlight.com Prepared date:2006/3/8 Rev.: 2 Page: 3 of 6 Prepared by: YanLi Zhong



Technical Data Sheet 10 Bar Graph Displays

ELB-1001SYGWA/S530-E2

Typical Electro-Optical Characteristic Curves:



EVERLIGHT ELECTRONICS CO.,LTD. http://www.everlight.com Device Number : CDDB-100-027

Prepared date:2006/3/8

Rev.: 2 Page: 4 of 6 Prepared by: YanLi Zhong

100

80



Technical Data Sheet 10 Bar Graph Displays

ELB-1001SYGWA/S530-E2

Reliability test items and conditions:

The reliability of products shall be satisfied with items listed below.

Confidence level: 97%

LTPD: 3%

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Re
1	Solder Heat	TEMP:260℃ ±5℃	5 SEC	76 PCS		0/1
2	Temperature Cycle	H : +85℃ 30min ∫ 5 min L : -55℃ 30min	50 CYCLE	76 PCS		0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	Iv≦Ivt*0.5	0/1
4	High Temperature Storage	TEMP: 100°C	1000 HRS	76 PCS	or Vf≧U or	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	Vf≦L	0/1
6	DC Operating Life	IF = 10 mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS		0/1

Note: Ivt: The test Iv value of the chip before the reliablility test

 $\operatorname{Iv}\,$: The test value of the chip that has completed the reliablility test

- U: Upper Specification Limit
- L: Lower Specification Limit

http://www.everlight.com Prepared date:2006/3/8 Rev.: 2Page: 5 of 6Prepared by: YanLiZhong

Technical Data Sheet 10 Bar Graph Displays

ELB-1001SYGWA/S530-E2

Packing Quantity Specification

- 1. 19PCS/tube, 72 tubes/box
- 2. 4Boxes/Carton

Label Form Specification



CPN: Customer's Production Number P/N : Production Number QTY: Packing Quantity CAT: Ranks HUE: Dominant Wavelength REF: Reference LOT No: Lot Number MADE IN CHINA: Production Place

Notes :

1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.

2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute

maximum ratings and the instructions included in these specification sheets.

3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT' sconsent.

EVERLIGHT ELECTRONICS CO., LTD. Office: 7c Building ,Lian Hua Port Industrial District, Lian Hua Shan Bonded Pricessing, Zone Pan Yu, Guang Zhou, China Tel: (020) 84860913 , 84860914 Fax: (020) 84860600 http:\\www.everlight.com

EVERLIGHT ELECTRONICS CO.,LTD. Device Number :CDDB-100-027 http://www.everlight.com Prepared date:2006/3/8

Rev.: 2 Page: 6 of 6 Prepared by: YanLi Zhong