



1: Front Panels for Sub Racks and Enclosures



1.1 Flat Front Panels

- For sub racks and enclosures, solid
- Aluminium 2.5 mm, clear anodised (non-conductive)
- **Scope of delivery:**
 - Flat front panel
- Front panel screws, see below
- 2 HP version: screw retainer can not be fitted



1.1 Flat Front Panels for Sub Racks and Enclosures, Solid

Width	B		Height		Part-No.					
	mm	inch	1 U 39.8mm	ca. 1 U* 42.15mm	2 U 84.2mm	3 U 128.7mm	4 U 173.1mm	6 U 262.0mm	7 U 306.5mm	9 U 395.4mm
2 HP ⁽¹⁾	10.0	0.39	—	—	—	21N302	—	21N602	—	—
3 HP	15.2	0.59	—	—	—	21N303	21N403	21N603	—	—
4 HP	20.1	0.79	—	—	—	21N304	21N404	21N604	—	21N904
5 HP	25.2	0.99	—	—	—	21N305	21N405	21N605	—	—
6 HP	30.3	1.19	—	—	—	21N306	21N406	21N606	—	—
7 HP	35.3	1.38	—	—	—	21N307	21N407	21N607	—	—
8 HP	40.4	1.59	—	—	—	21N308	21N408	21N608	—	—
10 HP	50.6	1.99	—	—	—	21N310	21N410	21N610	—	—
11 HP	55.7	2.19	—	—	—	21N311	—	—	—	—
12 HP	60.7	2.38	—	—	—	21N312	21N412	21N612	—	—
14 HP	70.9	2.79	—	—	—	21N314	21N414	21N614	—	—
16 HP	81.1	3.19	—	—	—	21N316	21N416	21N616	—	—
20 HP	101.4	3.59	—	—	—	21N320	21N420	21N620	—	—
21 HP	106.5	4.19	—	—	—	21N321	—	21N621	—	—
28 HP	142.0	5.59	—	—	—	21N328	—	21N628	—	—
32 HP	162.3	6.38	—	—	—	21N332	21N432	—	—	—
42 HP	213.1	8.38	—	—	21N242	21N342	21N442	21N642	—	—
52 HP	263.9	10.38	—	—	—	21N352	21N452	21N652	—	—
63 HP	319.8	12.59	—	—	21N263	21N363	21N463	21N663	—	—
81 HP	411.3	16.19	—	—	21N281	21N381	21N481	21N681	—	—
84 HP	426.5	16.79	21N184	21N084*	21N284	21N384	21N484	21N684	21N784	21N984

* Coverplates for 1 U fan opening

1.1.1 Front Panel Screws

- Set of 10 screws, with screw retainer

Description	Part-No. 10 pcs.
Torx screws M2.5 x 11.3, size T8 with plastic screw retainer	63K159
Rounded head screws recessed M2.5 x 11.3 with plastic screw retainer	63-159