

## Polypropylene (PP) Capacitors for Pulse Applications with Metal Foil Electrodes, Schoopage Contacts, Double-Sided Metallization and Self-Healing Internal Series Connection for Highest Current Carrying Capability PCM 15 mm to 37.5 mm

### Special Features

- Extremely high pulse duty
- Self-healing
- Internal series connection
- Very low dissipation factor
- Negative capacitance change versus temperature
- According to RoHS 2002/95/EC

### Typical Applications

For high pulse and high frequency applications e.g.

- Switch mode power supplies
- Converters in drives and power electronics
- Deflection systems in monitors and TV-sets
- Electronic ballasts

### Construction


#### Dielectric:

Polypropylene (PP) film

#### Capacitor electrodes:

Aluminium foil and double-sided metallized plastic film

#### Internal construction:



#### Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

#### Terminations:

Tinned wire.

#### Marking:

Colour: Red. Marking: Black.  
Epoxy resin seal: Yellow

### Electrical Data

#### Capacitance range:

100 pF to 0.22  $\mu$ F (E12-values on request)

#### Rated voltages:

400 VDC, 630 VDC, 1000 VDC, 1250 VDC, 1600 VDC, 2000 VDC, 4000 VDC, 6000 VDC

#### Capacitance tolerances:

$\pm 20\%$ ,  $\pm 10\%$ ,  $\pm 5\%$  (other tolerances are available subject to special enquiry)

#### Operating temperature range:

$-55^{\circ}$  C to  $+100^{\circ}$  C

#### Climatic test category:

55/100/56 in accordance with IEC

#### Insulation resistance at $+20^{\circ}$ C:

$C \leq 0.1 \mu\text{F}$ :  $\geq 1 \times 10^5 \text{ M}\Omega$

(mean value:  $5 \times 10^5 \text{ M}\Omega$ )

$C > 0.1 \mu\text{F}$ :  $\geq 30\,000 \text{ sec (M}\Omega \times \mu\text{F)}$

(mean value: 100\,000 sec)

Measuring voltage: 100 V/1 min.

#### Test voltage:

$2 U_r$ , 2 sec / 6 kV:  $1.6 U_r$ , 2 sec.

#### Maximum pulse rise time:

Capacitance pF/ $\mu$ F	max. pulse rise time V/ $\mu$ sec at $T_A < 40^{\circ}$ C							
	400VDC	630VDC	1000VDC	1250VDC	1600VDC	2000VDC	4000VDC	6000VDC
100 ... 220	–	–	–	–	56000	56000	–	–
330 ... 680	–	–	–	–	51000	56000	56000	56000
1000 ... 2200	29000	29000	29000	29000	46000	51000	51000	51000
3300 ... 6800	9000	14000	27000	29000	29000	29000	29000	29000
0.01 ... 0.022	9000	11000	11000	11000	11000	13000	13000	13000
0.033 ... 0.068	9000	11000	11000	11000	11000	11000	–	–
0.1 ... 0.22	7000	11000	11000	11000	11000	–	–	–

for pulses equal to the rated voltage

### Mechanical Tests

#### Pull test on pins:

$d \leq 0.8 \phi$ : 10 N in direction of pins

$d > 0.8 \phi$ : 20 N in direction of pins

according to IEC 60068-2-21

#### Vibration:

6 hours at 10...2000 Hz and 0.75 mm

displacement amplitude or 10 g in

accordance with IEC 60068-2-6

#### Low air density:

1kPa = 10 mbar in accordance with

IEC 60068-2-13

#### Bump test:

4000 bumps at  $390 \text{ m/sec}^2$

in accordance with IEC 60068-2-29

#### Dissipation factors at $+20^{\circ}$ C: $\tan \delta$

at f	$C \leq 0.1 \mu\text{F}$	$0.1 \mu\text{F} < C \leq 0.22 \mu\text{F}$
1 kHz	$\leq 3 \times 10^{-4}$	$\leq 3 \times 10^{-4}$
10 kHz	$\leq 4 \times 10^{-4}$	$\leq 6 \times 10^{-4}$
100 kHz	$\leq 10 \times 10^{-4}$	–

#### Dielectric absorption:

0.05%

#### Voltage derating:

A voltage derating factor of 1.35 % per K

must be applied from  $+85^{\circ}$  C for DC

voltages and from  $+75^{\circ}$  C for AC

voltages

#### Reliability:

Operational life > 300\,000 hours

Failure rate < 1 fit ( $0.5 \times U_r$  and  $40^{\circ}$  C)

### Packing

Available taped and reeled up to and

including case size 15 x 26 x 31.5 /

PCM 27.5 mm.

Detailed taping information and graphs

at the end of the catalogue.

For further details and graphs please

refer to Technical Information.

## Continuation

### General Data

Capacitance	400 VDC/250 VAC*					630 VDC/400 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	5	11	18	15	FKP1G011004B00_____	5	11	18	15	FKP1J011004B00_____
1500 "	5	11	18	15	FKP1G011504B00_____	5	11	18	15	FKP1J011504B00_____
2200 "	5	11	18	15	FKP1G012204B00_____	5	11	18	15	FKP1J012204B00_____
3300 "	5	11	18	15	FKP1G013304B00_____	5	11	18	15	FKP1J013304B00_____
4700 "	5	11	18	15	FKP1G014704B00_____	5	11	18	15	FKP1J014704B00_____
6800 "	5	11	18	15	FKP1G016804B00_____	6	12.5	18	15	FKP1J016804C00_____
0.01 µF	5	11	18	15	FKP1G021004B00_____	7	14	18	15	FKP1J021004D00_____
0.015 "	6	12.5	18	15	FKP1G021504C00_____	5	14	26.5	22.5	FKP1J021005A00_____
0.022 "	7	14	18	15	FKP1G022204D00_____	8	15	18	15	FKP1J021504F00_____
	5	14	26.5	22.5	FKP1G022205A00_____	6	15	26.5	22.5	FKP1J021505B00_____
0.033 "	8	15	18	15	FKP1G023304F00_____	7	16.5	26.5	22.5	FKP1J022205D00_____
	6	15	26.5	22.5	FKP1G023305B00_____	8.5	18.5	26.5	22.5	FKP1J023305F00_____
0.047 "	7	16.5	26.5	22.5	FKP1G024705D00_____	10.5	20.5	26.5	22.5	FKP1J024705H00_____
	9	19	31.5	27.5	FKP1G024706A00_____		9	19	31.5	27.5
0.068 "	8.5	18.5	26.5	22.5	FKP1G026805F00_____	11	21	31.5	27.5	FKP1J026806B00_____
						9	19	41.5	37.5	FKP1J026807A00_____
0.1 µF	10.5	20.5	26.5	22.5	FKP1G031005H00_____	13	24	31.5	27.5	FKP1J031006D00_____
	9	19	31.5	27.5	FKP1G031006A00_____	11	22	41.5	37.5	FKP1J031007B00_____
0.15 "	11	21	31.5	27.5	FKP1G031506B00_____	13	24	41.5	37.5	FKP1J031507C00_____
0.22 "	13	24	31.5	27.5	FKP1G032206D00_____	15	26	41.5	37.5	FKP1J032207D00_____

Capacitance	1000 VDC/600 VAC*					1250 VDC/600 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
1000 pF	5	11	18	15	FKP1O111004B00_____	5	11	18	15	FKP1R011004B00_____
1500 "	5	11	18	15	FKP1O111504B00_____	5	11	18	15	FKP1R011504B00_____
2200 "	5	11	18	15	FKP1O112204B00_____	5	11	18	15	FKP1R012204B00_____
3300 "	5	11	18	15	FKP1O113304B00_____	6	12.5	18	15	FKP1R013304C00_____
4700 "	6	12.5	18	15	FKP1O114704C00_____	7	14	18	15	FKP1R014704D00_____
6800 "	7	14	18	15	FKP1O116804D00_____	8	15	18	15	FKP1R016804F00_____
0.01 µF	8	15	18	15	FKP1O121004F00_____	7	16.5	26.5	22.5	FKP1R021005D00_____
0.015 "	6	15	26.5	22.5	FKP1O121505B00_____	8.5	18.5	26.5	22.5	FKP1R021505F00_____
0.022 "	8.5	18.5	26.5	22.5	FKP1O122205H00_____	10.5	20.5	26.5	22.5	FKP1R022205H00_____
0.033 "	10.5	20.5	26.5	22.5	FKP1O123305H00_____	11	21	31.5	27.5	FKP1R023306B00_____
0.047 "	11	21	31.5	27.5	FKP1O124706B00_____	13	24	31.5	27.5	FKP1R024706D00_____
0.068 "	13	24	31.5	27.5	FKP1O126806D00_____	11	22	41.5	37.5	FKP1R024707B00_____
0.1 µF	13	24	41.5	37.5	FKP1O131007C00_____	15	26	41.5	37.5	FKP1R031007D00_____
0.15 "	15	26	41.5	37.5	FKP1O131507D00_____	17	29	41.5	37.5	FKP1R031507E00_____
0.22 "	19	32	41.5	37.5	FKP1O132207F00_____	19	32	41.5	37.5	FKP1R032207F00_____

\* AC voltage:  $f \leq 1000 \text{ Hz}$ ;  $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

\*\* PCM = Printed circuit module = pin spacing

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Rights reserved to amend design data without prior notification.

∅ d	PCM
0.8	15 - 27.5
1.0	37.5

Part number completion:

Tolerance: 20 % = M  
10 % = K  
5 % = J

Packing: bulk = S  
Pin length: 6-2 = SD

Taped version see page 127.

## Continuation

### General Data

Capacitance	1600 VDC/650 VAC*					2000 VDC/700 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF	5	11	18	15	FKP1T001004B00_____	5	11	18	15	FKP1U001004B00_____
150 "	5	11	18	15	FKP1T001504B00_____	5	11	18	15	FKP1U001504B00_____
220 "	5	11	18	15	FKP1T002204B00_____	5	11	18	15	FKP1U002204B00_____
330 "	5	11	18	15	FKP1T003304B00_____	6	12.5	18	15	FKP1U003304C00_____
470 "	5	11	18	15	FKP1T004704B00_____	6	12.5	18	15	FKP1U004704C00_____
680 "	5	11	18	15	FKP1T006804B00_____	6	12.5	18	15	FKP1U006804C00_____
1000 pF	6	12.5	18	15	FKP1T011004C00_____	7	14	18	15	FKP1U011004D00_____
	5	14	26.5	22.5	FKP1T011005A00_____	5	14	26.5	22.5	FKP1U011005A00_____
1500 "	7	14	18	15	FKP1T011504D00_____	6	15	26.5	22.5	FKP1U011505B00_____
	5	14	26.5	22.5	FKP1T011505A00_____					
2200 "	8	15	18	15	FKP1T012204F00_____	7	16.5	26.5	22.5	FKP1U012205D00_____
	5	14	26.5	22.5	FKP1T012205A00_____					
3300 "	6	15	26.5	22.5	FKP1T013305B00_____	7	16.5	26.5	22.5	FKP1U013305D00_____
4700 "	7	16.5	26.5	22.5	FKP1T014705D00_____	8.5	18.5	26.5	22.5	FKP1U014705F00_____
6800 "	8.5	18.5	26.5	22.5	FKP1T016805F00_____	10.5	20.5	26.5	22.5	FKP1U016805H00_____
0.01 µF	10.5	20.5	26.5	22.5	FKP1T021005H00_____	11	21	31.5	27.5	FKP1U021006B00_____
0.015 "	11	21	31.5	27.5	FKP1T021506B00_____	13	24	31.5	27.5	FKP1U021506D00_____
0.022 "	11	21	31.5	27.5	FKP1T022206B00_____	15	26	31.5	27.5	FKP1U022206F00_____
						13	24	41.5	37.5	FKP1U022207C00_____
0.033 "	13	24	31.5	27.5	FKP1T023306D00_____	13	24	41.5	37.5	FKP1U023307C00_____
	13	24	41.5	37.5	FKP1T023307C00_____					
0.047 "	13	24	41.5	37.5	FKP1T024707C00_____	17	29	41.5	37.5	FKP1U024707E00_____
0.068 "	15	26	41.5	37.5	FKP1T026807D00_____	19	32	41.5	37.5	FKP1U026807F00_____
0.1 µF	17	29	41.5	37.5	FKP1T031007E00_____					

Capacitance	4000 VDC/700 VAC*					6000 VDC/700 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
470 pF	5	14	26.5	22.5	FKP1X004705A00_____	5	14	26.5	22.5	FKP1Y004705A00_____
680 "	5	14	26.5	22.5	FKP1X006805A00_____	5	14	26.5	22.5	FKP1Y006805A00_____
1000 pF	5	14	26.5	22.5	FKP1X011005A00_____	5	14	26.5	22.5	FKP1Y011005A00_____
1500 "	7	16.5	26.5	22.5	FKP1X011505D00_____	7	16.5	26.5	22.5	FKP1Y011505D00_____
2200 "	8.5	18.5	26.5	22.5	FKP1X012205F00_____	10.5	20.5	26.5	22.5	FKP1Y012205H00_____
3300 "	10.5	20.5	26.5	22.5	FKP1X013305H00_____	10.5	20.5	26.5	22.5	FKP1Y013305H00_____
4700 "	11	21	31.5	27.5	FKP1X014706B00_____	11	21	31.5	27.5	FKP1Y014706B00_____
6800 "	13	24	31.5	27.5	FKP1X016806D00_____	13	24	31.5	27.5	FKP1Y016806D00_____
0.01 µF	15	26	31.5	27.5	FKP1X021006F00_____	15	26	31.5	27.5	FKP1Y021006F00_____
0.015 "	13	24	41.5	37.5	FKP1X021507C00_____	13	24	41.5	37.5	FKP1Y021507C00_____
0.022 "	17	29	41.5	37.5	FKP1X022207E00_____	17	29	41.5	37.5	FKP1Y022207E00_____

\* AC voltage:  $f \leq 1000 \text{ Hz}$ ;  $1.4 \times U_{\text{rms}} + \text{UDC} \leq U_r$

\*\* PCM = Printed circuit module = pin spacing

Dims. in mm.

Ionisation inception level in isolated cases may be lower than admissible rated AC voltage.

Rights reserved to amend design data without prior notification.

Part number completion:

Tolerance: 20 % = M

10 % = K

5 % = J

Packing: bulk = S

Pin length: 6-2 = SD

Taped version see page 127.


AC voltage graphs see page 61.

# WIMA MKP 10




## Continuation

Permissible AC voltage in relation to frequency at 10° C internal temperature rise (general guide).



# WIMA FKP 1

Permissible AC voltage in relation to frequency at 10° C internal temperature rise (general guide).



Technical information and general data see page 66.

## Recommendation for Processing and Application of Through-Hole Capacitors

### Soldering Process

A preheating of through-hole WIMA capacitors is allowed for temperatures  $T_{\max} < 100^{\circ}\text{C}$ . In practice a preheating duration of  $t < 5$  min. has been proven to be best.


#### Single wave soldering

Soldering bath temperature:  $T < 260^{\circ}\text{C}$   
Immersion time:  $t < 5$  sec

#### Double wave soldering

Soldering bath temperature:  $T < 260^{\circ}\text{C}$   
Immersion time:  $2 \times t < 3$  sec

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



## WIMA Quality and Environmental Philosophy

### ISO 9001:2008 Certification

ISO 9001:2008 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2008 of our factories by the VDE inspectorate certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

### WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application of WPCS during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- AQL check

### WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- Lead
- PCB
- CFC
- Hydrocarbon chloride
- Chromium 6+
- PBB/PBDE
- Arsenic
- Cadmium
- Mercury
- etc.

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- foamed polystyrene (Styropor®)
- adhesive tapes made of plastic
- metal clips

### RoHS Compliance

According to the RoHS Directive 2002/95/EC certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei konform RoHS 2002/95/EG

WIMA capacitors are lead free in accordance with RoHS 2002/95/EC

Tape for lead-free WIMA capacitors

### DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

# Typical Dimensions for Taping Configuration




Diagram 1:  
PCM 2.5/5/7.5mm

Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5\*mm

\*PCM 27.5 taping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 taping	PCM 5 taping	PCM 7.5 taping	PCM 10 taping*	PCM 15 taping*	PCM 22.5 taping	PCM 27.5 taping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W <sub>0</sub>	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W <sub>1</sub>	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W <sub>2</sub>	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D <sub>0</sub>	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P <sub>0</sub>	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to pin	P <sub>1</sub>	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P <sub>2</sub>	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H <sub>1</sub>	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 24.5 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 25.0 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 26.0 to 37.0	H+H <sub>component</sub> < H <sub>1</sub> 30.0 to 43.0	H+H <sub>component</sub> < H <sub>1</sub> 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 <sup>+0.8</sup> <sub>-0.2</sub>	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2
Package (see also page 128)	ROLL/AMMO			AMMO				
	REEL	φ 360 max. φ 30 ±1	B 52 ±2 58 ±2 } depending on comp. dimensions	REEL	φ 360 max. φ 30 ±1	52 ±2 58 ±2 or 66 ±2	REEL	φ 500 max. φ 25 ±1
Unit	see details page 130.							

Dims in mm.

\* Diameter of pins see General Data.

\* PCM 10 and PCM 15 can be crimped to PCM 7.5.

Position of components according to PCM 7.5 (sketch 11). P<sub>0</sub> = 12.7 or 15.0 is possible

Please clarify customer-specific deviations with the manufacturer.

# Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm



PCM	Size				bulk	pcs. per packing unit								
						ROLL		REEL				AMMO		
	W	H	L	Codes		S	H16.5	H18.5	ø 360	ø 500	340 x 340	490 x 370		
					N	O	F	I	H	J	A	C	B	D
<b>2.5 mm</b>	2.5	7	4.6	<b>0B</b>	5000		2200	2500				2800		
	3	7.5	4.6	<b>0C</b>	5000		2000	2300				2300		
	3.8	8.5	4.6	<b>0D</b>	5000		1500	1800				1800		
	4.6	9	4.6	<b>0E</b>	5000		1200	1500				1500		
	5.5	10	4.6	<b>0F</b>	5000		900	1200				1200		
<b>5 mm</b>	2.5	6.5	7.2	<b>1A</b>	5000		2200	2500				2800		
	3	7.5	7.2	<b>1B</b>	5000		2000	2300				2300		
	3.5	8.5	7.2	<b>1C</b>	5000		1600	2000				2000		
	4.5	6	7.2	<b>1D</b>	6000		1300	1500				1500		
	4.5	9.5	7.2	<b>1E</b>	4000		1300	1500				1500		
	5	10	7.2	<b>1F</b>	3500		1100	1400				1400		
	5.5	7	7.2	<b>1G</b>	4000		1000	1200				1200		
	5.5	11.5	7.2	<b>1H</b>	2500		1000	1200				1200		
	6.5	8	7.2	<b>1I</b>	2500		800	1000				1000		
	7.2	8.5	7.2	<b>1J</b>	2500		700	1000				1000		
	7.2	13	7.2	<b>1K</b>	2000		700	950				1000		
	8.5	10	7.2	<b>1L</b>	2000		600	800				800		
8.5	14	7.2	<b>1M</b>	1500		600	800				800			
11	16	7.2	<b>1N</b>	1000		500	700				700			
<b>7.5 mm</b>	2.5	7	10	<b>2A</b>	5000			2500	4400			2500		
	3	8.5	10	<b>2B</b>	5000			2200	4300			2300	4150	
	4	9	10	<b>2C</b>	4000			1700	3200			1700	3100	
	4.5	9.5	10.3	<b>2D</b>	3500			1500	2900			1400	2800	
	5	10.5	10.3	<b>2E</b>	3000			1300	2500			1300		
	5.7	12.5	10.3	<b>2F</b>	2000			1000	2200			1100		
	7.2	12.5	10.3	<b>2G</b>	1500			900	1800			1000		
<b>10 mm</b>	3	9	13	<b>3A</b>	3000			1100	2200				1900	
	4	8.5	13.5	<b>FA</b>	3000			900	1600				1450	
	4	9	13	<b>3C</b>	3000			900	1600				1450	
	4	9.5	13	<b>3D</b>	3000			900	1600				1400	
	5	10	13.5	<b>FB</b>	2000			700	1300				1200	
	5	11	13	<b>3F</b>	3000			700	1300				1200	
	6	12	13	<b>3G</b>	2400			550	1100				1000	
	6	12.5	13	<b>3H</b>	2400			550	1100				1000	
8	12	13	<b>3I</b>	2000			400	800				740		
<b>15 mm</b>	5	11	18	<b>4B</b>	2400			600	1200				1150	
	5	13	19	<b>FC</b>	1000			600	1200				1200	
	6	12.5	18	<b>4C</b>	2000			500	1000				1000	
	6	14	19	<b>FD</b>	1000			500	1000				1000	
	7	14	18	<b>4D</b>	1600			450	900				850	
	7	15	19	<b>FE</b>	1000			450	900				850	
	8	15	18	<b>4F</b>	1200			400	800				740	
	8	17	19	<b>FF</b>	500			400	800				740	
	9	14	18	<b>4H</b>	1200			350	700				650	
	9	16	18	<b>4J</b>	900			350	700				650	
	10	18	19	<b>FG</b>	500			300	650				590	
11	14	18	<b>4M</b>	1000			300	600				540		
<b>22.5 mm</b>	5	14	26.5	<b>5A</b>	1200				800				770	
	6	15	26.5	<b>5B</b>	1000				700				640	
	7	16.5	26.5	<b>5D</b>	760				600				550	
	8	20	28	<b>FH</b>	500				500				480	
	8.5	18.5	26.5	<b>5F</b>	500				480				450	
	10	22	28	<b>FI</b>	540*				420				380	
	10.5	19	26.5	<b>5G</b>	680*				400				360	
	10.5	20.5	26.5	<b>5H</b>	680*				400				360	
	11	21	26.5	<b>5I</b>	680*				380				350	
	12	24	28	<b>FJ</b>	450*				350				310	

\* Tray Packing-System  
Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.





## Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm

PCM	Size				bulk	pcs. per packing units								
						ROLL		REEL				AMMO		
	W	H	L	Codes		S	H16.5	H18.5	ø 360		ø 500		340 × 340	
					N	O	F	I	H	J	A	C	B	D
<b>27.5 mm</b>	9	19	31.5	<b>6A</b>	640*	–	–	–	–	460/340*	–	–	–	420
	11	21	31.5	<b>6B</b>	544*	–	–	–	–	380/280*	–	–	–	350
	13	24	31.5	<b>6D</b>	448*	–	–	–	–	300	–	–	–	290
	13	25	33	<b>6K</b>	336*	–	–	–	–	270	–	–	–	250
	15	26	31.5	<b>6F</b>	384*	–	–	–	–	–	–	–	–	–
	15	26	33	<b>6L</b>	288*	–	–	–	–	–	–	–	–	–
	17	29	31.5	<b>6G</b>	176*	–	–	–	–	–	–	–	–	–
	17	34.5	31.5	<b>6I</b>	176*	–	–	–	–	–	–	–	–	–
	19	30	31.5	<b>6L</b>	50*	–	–	–	–	–	–	–	–	–
	20	32	33	<b>6M</b>	216*	–	–	–	–	–	–	–	–	–
20	39.5	31.5	<b>6J</b>	144*	–	–	–	–	–	–	–	–	–	
<b>37.5 mm</b>	9	19	41.5	<b>7A</b>	480*	–	–	–	–	–	–	–	–	–
	11	22	41.5	<b>7B</b>	408*	–	–	–	–	–	–	–	–	–
	13	24	41.5	<b>7C</b>	252*	–	–	–	–	–	–	–	–	–
	15	26	41.5	<b>7D</b>	144*	–	–	–	–	–	–	–	–	–
	17	29	41.5	<b>7E</b>	132*	–	–	–	–	–	–	–	–	–
	19	32	41.5	<b>7F</b>	108*	–	–	–	–	–	–	–	–	–
	20	39.5	41.5	<b>7G</b>	108*	–	–	–	–	–	–	–	–	–
	24	45.5	41.5	<b>7H</b>	84*	–	–	–	–	–	–	–	–	–
	31	46	41.5	<b>7I</b>	72*	–	–	–	–	–	–	–	–	–
	35	50	41.5	<b>7J</b>	35*	–	–	–	–	–	–	–	–	–
40	55	41.5	<b>7K</b>	28*	–	–	–	–	–	–	–	–	–	
<b>48.5 mm</b>	19	31	56	<b>8D</b>	50*	–	–	–	–	–	–	–	–	–
	23	34	56	<b>8E</b>	72*	–	–	–	–	–	–	–	–	–
	27	37.5	56	<b>8H</b>	60*	–	–	–	–	–	–	–	–	–
	33	48	56	<b>8J</b>	48*	–	–	–	–	–	–	–	–	–
	37	54	56	<b>8L</b>	25*	–	–	–	–	–	–	–	–	–
<b>52.5 mm</b>	35	50	57	<b>9F</b>	25*	–	–	–	–	–	–	–	–	–
	45	55	57	<b>9H</b>	20*	–	–	–	–	–	–	–	–	–
	45	65	57	<b>9J</b>	20*	–	–	–	–	–	–	–	–	–

\* for 2-inch transport pitches.

\* Tray Packing System

Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.





A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Special features (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Lead length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
<b>M</b>	<b>K</b>	<b>S</b>	<b>2</b>	<b>C</b>	<b>0</b>	<b>2</b>	<b>1</b>	<b>0</b>	<b>0</b>	<b>1</b>	<b>A</b>	<b>0</b>	<b>0</b>	<b>M</b>	<b>S</b>	<b>S</b>	<b>D</b>
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2		-		20%	bulk	6 -2		

<p><b>Type description:</b></p> <p>SMD-PET = SMDT  SMD-PPS = SMDI  FKP 02 = FKP0  MKS 02 = MKS0  FKS 2 = FKS2  FKP 2 = FKP2  MKS 2 = MKS2  MKS 2 = MKP2  FKS 3 = FKS3  FKP 3 = FKP3  MKS 4 = MKS4  MKP 4 = MKP4  MKP 10 = MKP1  FKP 4 = FKP4  FKP 1 = FKP1  MKP-X2 = MKX2  MKP-X2 R = MKXR  MKP-Y2 = MKY2  MP 3-X2 = MPX2  MP 3-X1 = MPX1  MP 3-Y2 = MPY2  MP 3R-Y2 = MPRY  Snubber MKP = SNMP  Snubber FKP = SNFP  GTO MKP = GTOM  DC-LINK MKP 4 = DCP4  DC-LINK MKP 5 = DCP5  DC-LINK MKP 6 = DCP6  DC-LINK HC = DCH_  SuperCap C = SCSC  SuperCap MC = SCMC  SuperCap R = SCSR  SuperCap MR = SCMR</p>	<p><b>Rated voltage:</b></p> <p>2.5 VDC = A1  4 VDC = A2  14 VDC = A3  28 VDC = A4  40 VDC = A5  5 VDC = A6  50 VDC = B0  63 VDC = C0  100 VDC = D0  160 VDC = E0  250 VDC = F0  400 VDC = G0  450 VDC = H0  600 VDC = I0  630 VDC = J0  700 VDC = K0  800 VDC = L0  850 VDC = M0  900 VDC = N0  1000 VDC = O1  1100 VDC = P0  1200 VDC = Q0  1250 VDC = R0  1500 VDC = S0  1600 VDC = T0  2000 VDC = U0  2500 VDC = V0  3000 VDC = W0  4000 VDC = X0  6000 VDC = Y0  250 VAC = 0W  275 VAC = 1W  300 VAC = 2W  400 VAC = 3W  440 VAC = 4W  500 VAC = 5W</p>	<p><b>Capacitance:</b></p> <p>22 pF = 0022  47 pF = 0047  100 pF = 0100  150 pF = 0150  220 pF = 0220  330 pF = 0330  470 pF = 0470  680 pF = 0680  1000 pF = 1100  1500 pF = 1150  2200 pF = 1220  3300 pF = 1330  4700 pF = 1470  6800 pF = 1680  0.01 µF = 2100  0.022 µF = 2220  0.047 µF = 2470  0.1 µF = 3100  0.22 µF = 3220  0.47 µF = 3470  1 µF = 4100  2.2 µF = 4220  4.7 µF = 4470  10 µF = 5100  22 µF = 5220  47 µF = 5470  100 µF = 6100  220 µF = 6220  1 F = A010  2.5 F = A025  50 F = A500  100 F = B100  110 F = B110  600 F = B600  1200 F = C120  ...</p>	<p><b>Size:</b></p> <p>4.8x3.3x3 Size 1812 = KA  4.8x3.3x4 Size 1812 = KB  5.7x5.1x3.5 Size 2220 = QA  5.7x5.1x4.5 Size 2220 = QB  7.2x6.1x3 Size 2824 = TA  7.2x6.1x5 Size 2824 = TB  10.2x7.6x5 Size 4030 = VA  12.7x10.2x6 Size 5040 = XA  15.3x13.7x7 Size 6054 = YA  2.5x7x4.6 PCM 2.5 = 0B  3x7.5x4.6 PCM 2.5 = 0C  2.5x6.5x7.2 PCM 5 = 1A  3x7.5x7.2 PCM 5 = 1B  2.5x7x10 PCM 7.5 = 2A  3x8.5x10 PCM 7.5 = 2B  3x9x13 PCM 10 = 3A  4x9x13 PCM 10 = 3C  5x11x18 PCM 15 = 4B  6x12.5x18 PCM 15 = 4C  5x14x26.5 PCM 22.5 = 5A  6x15x26.5 PCM 22.5 = 5B  9x19x31.5 PCM 27.5 = 6A  11x21x31.5 PCM 27.5 = 6B  9x19x41.5 PCM 37.5 = 7A  11x22x41.5 PCM 37.5 = 7B  94x49x182 DCH_ = H0  94x77x182 DCH_ = H1  ...</p>	<p><b>Tolerance:</b></p> <p>20% = M  10% = K  5% = J  2.5% = H  1% = E  ...</p> <p><b>Packing:</b></p> <p>AMMO H16.5 340x340 = A  AMMO H16.5 490x370 = B  AMMO H18.5 340x340 = C  AMMO H18.5 490x370 = D  REEL H16.5 360 = F  REEL H16.5 500 = H  REEL H18.5 360 = I  REEL H18.5 500 = J  ROLL H16.5 = N  ROLL H18.5 = O  BLISTER W12 180 = P  BLISTER W12 330 = Q  BLISTER W16 330 = R  BLISTER W24 330 = T  Bulk Standard = S  TPS Standard = Y  ...</p>	
				<p><b>Special features:</b></p> <p>Standard = 00  Version A1 = 1A  Version A1.1.1 = 1B  Version A1.2 = 1C  ...</p>	<p><b>Lead length (untaped)</b></p> <p>3.5 ±0.5 = C9  6 -2 = SD  16 ±1 = P1  ...</p>

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.