

SPECIFICATION




■ Features :

- Universal AC input / Full range
- Built-in active PFC function, PF>0.94
- High efficiency up to 89%
- Withstand 300VAC surge input for 5 seconds
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Built-in cooling fan ON-OFF control
- Built-in DC OK signal
- Built-in remote ON-OFF control
- Standby 5V@0.3A
- Built-in remote sense function
- No load power consumption<0.75W (Note.7)
- Current sharing up to 2400W (3+1) (24V,36V,48V)
- 5 years warranty



MODEL		HRPG-600-3.3	HRPG-600-5	HRPG-600-7.5	HRPG-600-12	HRPG-600-15	HRPG-600-24	HRPG-600-36	HRPG-600-48	
	DC VOLTAGE	3.3V	5V	7.5V	12V	15V	24V	36V	48V	
	RATED CURRENT	120A	120A	80A	53A	43A	27A	17.5A	13A	
	CURRENT RANGE	0 ~ 120A	0 ~ 120A	0 ~ 80A	0 ~ 53A	0 ~ 43A	0 ~ 27A	0 ~ 17.5A	0 ~ 13A	
	RATED POWER	396W	600W	600W	636W	645W	648W	630W	624W	
	RIPPLE & NOISE (max.) Note.2	100mVp-p	100mVp-p	100mVp-p	120mVp-p	150mVp-p	150mVp-p	200mVp-p	240mVp-p	
OUTPUT	VOLTAGE ADJ. RANGE	2.8 ~ 3.8V	4.3 ~ 5.8V	6.8 ~ 9V	10.2 ~ 13.8V	13.5 ~ 18V	21.6 ~ 28.8V	28.8 ~ 39.6V	40.8 ~ 55.2V	
	VOLTAGE TOLERANCE Note.3	±2.0%	±2.0%	±2.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.3%	±0.3%	±0.2%	±0.2%	±0.2%	
	LOAD REGULATION	±1.0%	±1.0%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	SETUP, RISE TIME	1000ms, 50ms/230VAC 2500ms, 50ms/115VAC at full load								
	HOLD UP TIME (Typ.)	16ms/230VAC 16ms/115VAC at full load								
	VOLTAGE RANGE Note.5 85 ~ 264VAC 120 ~ 370VDC									
	FREQUENCY RANGE	47 ~ 63Hz								
	POWER FACTOR (Typ.)	PF>0.94/230V/	AC PF>0.9	99/115VAC at full	load					
INPUT	EFFICIENCY (Typ.)	78.5%	82%	86%	88%	88%	88%	89%	89%	
• .	AC CURRENT (Typ.)	8.5A/115VAC	5A/230VAC	10070	1 00 /0	1 00 /0	1 00 /0	3370	0070	
	INRUSH CURRENT (Typ.)	35A/115VAC 70A/230VAC 3A/230VAC								
	LEAKAGE CURRENT	<1.2mA/240VAC								
	LEARAGE CORRECT									
OVERLOAD 105 ~ 135% rated output power Protection type : Constant current limiting, recovers automatical						ofter fault eendit	ion is removed			
		3.96 ~ 4.62V	6 ~ 7V	9.4 ~ 10.9V	14.4 ~ 16.8V	18.8 ~ 21.8V	30 ~ 34.8V	41.4 ~ 48.6V	57.6 ~ 67.2V	
OVER VOLTAGE						00 01.01	11.1 10.01	01.0 01.24		
PROTECTION		Protection type: Shut down o/p voltage, re-power on to recover 80°C ±5°C (TSW1)detect on heatsink of power transistor								
	OVER TEMPERATURE	90°C ±5°C (TSW2) detect on heatsink of power transistor 90°C ±5°C (TSW2) detect on heatsink of power doide for 3.3V,5V,7.5V; 100°C ±5°C (TSW2) detect on main power output choke for others Protection type: Shut down o/p voltage, recovers automatically after temperature goes down								
	OVER TEMPERATURE									
	5V STANDBY	5VSB: 5V@0.3A; tolerance ± 5%, ripple: 50mVp-p(max.)								
	DC OK SIGNAL	PSU turn on: 3.3 ~ 5.6V; PSU turn off: 0 ~ 1V								
FUNCTION	REMOTE CONTROL	RC+/RC-: $4 \sim 10V$ or open = power on; $0 \sim 0.8V$ or short = power off								
		Load $35\pm15\%$ or RTH2 \geq 50°C Fan on								
	FAN CONTROL (Typ.) WORKING TEMP.									
		-40 ~ +70°C (Refer to "Derating Curve")								
ENVIRONMENT	WORKING HUMIDITY STORAGE TEMP., HUMIDITY	20 ~ 90% RH non-condensing								
ENVINONMENT	TEMP. COEFFICIENT									
	VIBRATION	±0.03%/°C (0 ~ 50°C) 10 ~ 500Hz, 5G 10min./1cycle, 60min, each along X, Y, Z axes								
		,		,	nig A, T, Z axes					
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1 approved								
SAFETY & WITHSTAND VOLTAGE I/P-O/P:3KVAC I/P-FG:2KVAC O/P-FG:0.5KVAC EMC ISOLATION RESISTANCE I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH										
EMC (Note 4)	ISOLATION RESISTANCE					1				
(14016-4)	EMC EMISSION		,	PR22) Class B, E						
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, EN61000-6-2, heavy industry level, criteria A								
	MTBF	147.7K hrs min	. MIL-HDBK	-217F (25°C)						
OTHERS	DIMENSION	218*105*63.5mm (L*W*H)								
	PACKING	1.58Kg;8pcs/13	3.6Kg/1.34CUFT	•						
NOTE	Ripple & noise are measure Tolerance : includes set up The power supply is consid EMC directives. For guidan (as available on http://www. Derating may be needed ur	ally mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. red at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. to tolerance, line regulation and load regulation. dered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets no how to perform these EMC tests, please refer to "EMI testing of component power supplies." v.meanwell.com) under low input voltages. Please check the derating curve for more details. easured at first cold start. Turning ON/OFF the power supply may lead to increase of the set up time.								





AC Input Terminal Pin No. Assignment

_	
Pin No.	Assignment
1	AC/L
2	AC/N
3	FG ±

DC Output Terminal Pin No. Assignment


-	
Pin No.	Assignment
1~3	-V
4~6	+V

AMBIENT TEMPERATURE (°C)

Connector Pin No. Assignment(CN100): HRS DF11-10DP-2DS or equivalent

Pin No.	Assignment	Pin No.	Assignment	Mating Housing	Terminal		
1	AUXG	6,8	GND				
2	AUX	7	DC-OK	UD0 DE44 40D0			
3	RC+	9	+S	HRS DF11-10DS or equivalent	or equivalent		
4	RC-	10	-S	or oquivalone	or oquivalent		
5	CS						

INPUT VOLTAGE (V) 60Hz





■ Function Description of CN100

Pin No.	Function	Description
1	AUXG	Auxiliary voltage output ground. The signal return is isolated from the output terminals (+V & -V).
2		Auxiliary voltage output, 4.75~5.25V, referenced to pin 1(AUXG). The maximum load current is 0.3A. This output has the built-in oring diodes and is not controlled by the "remote ON/OFF control".
3	RC+	Turns the output on and off by electrical or dry contact between pin 4 (RC-), Short: Power OFF, Open: Power ON.
4	RC-	Remote control ground.
5	cs	Current sharing signal. When units are connected in parallel, the CS pins of the units should be connected to allow current balance between units.
6,8	GND	This pin connects to the negative terminal(-V). Return for DC-OK signal output.
7	DC-OK	DC-OK signal is a TTL level signal, referenced to pin8(DC-OK GND). High when PSU turns on.
9		Positive sensing. The +S signal should be connected to the positive terminal of the load. The +S and -S leads should be twisted in pair to minimize noise pick-up effect. The maximum line drop compensation is 0.5V.
10		Negative sensing. The -S signal should be connected to the negative terminal of the load. The -S and +S leads should be twisted in pair to minimize noise pick-up effect. The maximum line drop compensation is 0.5V.

■ Function Manual

1.Remote Sense

The remote sensing compensates voltage drop on the load wiring up to $0.5 \ensuremath{\text{V}}.$





Fig 1.1

2.DC-OK Signal

DC-OK signal is a TTL level signal. High when PSU turns on.

Between DC-OK(pin7) and GND(pin6,8)	Output Status	
3.3 ~ 5.6V	ON	
0 ~ 1V	OFF	







Fig 2.1



3.Remote Control

The PSU can be turned ON/OFF by using the "Remote Control" function.

Between RC+(pin3) and RC-(pin4)	Output Status
SW ON (Short)	OFF
SW OFF (Open)	ON







Fig 3.1

4. Current Sharing with Remote Sensing (Only for 24V, 36V and 48V)

HRPG-600 has the built-in active current sharing function and can be connected in parallel to provide higher output power:

- (1)Parallel operation is available by connecting the units shown as below.
 - (+S,-S,CS and GND are connected mutually in parallel).
- (2) Difference of output voltages among parallel units should be less than 2%.
- (3) The total output current must not exceed the value determined by the following equation. (output current at parallel operation)=(Rated current per unit)×(Number of unit)×0.9
- (4)In parallel operation 4 units is the maximum, please consult the manufacturer for applications of more connecting in parallel.
- (5) The power supplies should be paralleled using short and large diameter wiring and then connected to the load.



 $Note: 1. In \ parallel \ connection, \ may be \ only \ one \ unit \ (master) \ operate \ if \ the \ total \ output \ load \ is \ less \ than \ 2\% \ of \ rated \ load \ condition.$

The other PSU (slave) may go into standby mode and its output LED and relay will not turn on.

2.2% min. of dummy load is required.