## Braided Sleeving

## Light weight standard polyester braided sleeving

• Helagaine HEGPL

3.15

## **Features and Benefits**

Helagaine HEGPL is very light, flexible and resistant to abrasion. HEGPL provides very good protection against the mechanical and chemical influences typically found in automobiles. Due to its high expansion rate of more than 3:1, HEGPL can be easily applied to hose assemblies and cable harnesses with very irregular diameters.

## Application

Helagaine HEGPL is used primarily in automobile interiors, motor compartments, car bodies and underfloors.



Helagaine HEGPL Braided Sleeving.

sleeve can	be cut with	
the hot cutting tool		
HSG0, see	page 424.	

Material Data	
Material	Polyester (PET)
Colour	Black (BK)
Operating Temperature	-50 °C to +150 °C, Intermittent +220 °C
Melting Point	+250 °C
Flammability	UL94 V2, FMVSS 302 Type B
	halogenfree

Technical Table						
Article-No.	Туре	Bundle Ø min.	Bundle Ø max.	Reel Length (m)		
170-80503	HEGPL03	3	8	1000		
170-80506	HEGPL06	5	12	400		
170-80512	HEGPL12	8	21	300		
170-80520	HEGPL20	12	30	300		
170-80530	HEGPL30	18	55	200		
170-80540	HEGPL40	24	66	150		
170-80550	HEGPL50	30	82	150		

All dimensions in mm. Subject to technical changes.

Colour grey available on request.

Cuts in any lengths.