




IFS207 Inductive sensors





Made in Germany

C C CUL US		Made in Germany
Product characteristics		
Inductive sensor		
Metal thread M12 x 1		
Connector		
Increased sensing range		
gold-plated contacts		
Sensing range 7 mm [nf]		
non-flush mountable		
Electrical data		
Electrical design		DC PNP
Operating voltage	[V]	1036 DC
Current consumption	[mA]	< 10 (24 V)
Protection class		II
Reverse polarity protection	1	yes
Outputs		
Output function		normally closed
Voltage drop	[V]	< 2.5
Current rating	[mA]	100
Short-circuit protection		pulsed
Overload protection		yes
Switching frequency	[Hz]	700
Range		
Sensing range	[mm]	7
Real sensing range (Sr)	[mm]	7 ± 10 %
Operating distance	[mm]	05.7
Accuracy / deviations		
Correction factors		mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3
Hysteresis	[% of Sr]	315
Switch-point drift	[% of Sr]	-1010

Tests / approvals

Environment Ambient temperature

Protection

EMC EN 61000-4-2 ESD: 4 kV CD / 8 kV AD EN 61000-4-3 HF radiated: 10 V/m (80...1000 MHz) EN 61000-4-4 Burst: 2 kV EN 61000-4-6 HF conducted: 10 V (0.15...80 MHz)

EN 55011:

-25...70

IP 67

class B

[°C]





IFS207 Inductive sensors

MTTF	[Years]	2017
Mechanical data		
Mounting		non-flush mountable
Housing materials		brass white bronze coated; active face: PBT
Weight	[kg]	0.025

Displays / operating elements


Output status indication LED yellow (4 x 90°)

Electrical connection

Connection M12 connector; gold-plated contacts

Wiring





Accessories

Accessories (included) 2 lock nuts

 $ifm\ electronic\ gmbh\ \bullet\ Friedrichstraße\ 1\ \bullet\ 45128\ Essen\ -\ We\ reserve\ the\ right\ to\ make\ technical\ alterations\ without\ prior\ notice.\ -\ GB\ -\ IFS207\ -\ 06.03.2003$