
# efectorioo



IGS204 Inductive sensors





Made in Germany

LISTED		
Product characteristics	S	
Inductive sensor		
Metal thread M18 x 1		
Connector		
Increased sensing range		
gold-plated contacts		
Sensing range 8 mm [f]		
flush mountable		
Electrical data		
Electrical design		DC PNP
Operating voltage	[V]	1036 DC
Current consumption	[mA]	< 10
Protection class		<u> </u>
Reverse polarity protection	on	yes
Outputs		
Output function		normally open
Voltage drop	[V]	< 2.5
Current rating	[mA]	100
Short-circuit protection		pulsed
Overload protection		yes
Switching frequency	[Hz]	400
Range		
Sensing range	[mm]	8
Operating distance	[mm]	06.5
Accuracy / deviations		
Correction factors		mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3
Hysteresis	[% of Sr]	120
Environment		
Ambient temperature	[°C]	-2570
Protection		IP 67
Tests / approvals		
EMC		EN 61000-4-2 ESD: 4 kV CD / 8 kV AD EN 61000-4-3 HF radiated: 10 V/m (802000 MHz) EN 61000-4-4 Burst: 2 kV

EN 61000-4-6 HF conducted:

EN 55011:

[Years]

MTTF

10 V (0.15...80 MHz)

class B

2072





IGS204 Inductive sensors

Mechanical data				
Mounting		flush mountable		
Housing materials		brass white bronze coated; active face: PBT (Pocan)		
Weight	[kg]	0.044		

## Displays / operating elements


Output status indication LED yellow (4 x 90°)

## Electrical connection

Connection M12 connector; gold-plated contacts

#### Wiring





#### Accessories

Accessories (included) 2 lock nuts

 $ifm\ electronic\ gmbh \bullet Friedrichstraße\ 1 \bullet 45128\ Essen\ -\ We\ reserve\ the\ right\ to\ make\ technical\ alterations\ without\ prior\ notice.\ -\ GB\ -\ IGS204\ -\ 06.03.2003$