
efectorioo



IGS206 Inductive sensors





Made in Germany

Product characteristics		
Inductive sensor		
Metal thread M18 x 1		
Connector		
Increased sensing range		
gold-plated contacts		
Sensing range 8 mm [f]		
flush mountable		
Electrical data		
Electrical design		DC PNP
Operating voltage	[V]	1036 DC
Current consumption	[mA]	< 10
Protection class		II
Reverse polarity protection	1	yes
Outputs		
Output function		normally closed
Voltage drop	[V]	< 2.5
Current rating	[mA]	100
Short-circuit protection		pulsed
Overload protection		yes
Switching frequency	[Hz]	400
Range		
Sensing range	[mm]	8
Real sensing range (Sr)	[mm]	8 ± 10 %
Operating distance	[mm]	06.5
Accuracy / deviations		
Correction factors		mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3
Hysteresis	[% of Sr]	315
Switch-point drift	[% of Sr]	-1010
Environment		

Tests / approvals

Protection

Ambient temperature

 EMC EN 61000-4-2 ESD: 4 kV CD / 8 kV AD EN 61000-4-3 HF radiated: 10 V/m (80...1000 MHz) EN 61000-4-4 Burst: 2 kV

-25...70

IP 67

[°C]





IGS206 Inductive sensors

EN 61000-4-6 HF conducted: 10 V (0.15...80 MHz)

EN 55011: class B

MTTF [Years] 1935

 Mechanical data

 Mounting
 flush mountable

 Housing materials
 brass white bronze coated; active face: PBT (Pocan)

Weight [kg] 0.044

Displays / operating elements


Output status indication LED yellow (4 x 90°)

Electrical connection

Connection M12 connector; gold-plated contacts

Wiring





Accessories
Accessories (included) 2 lock nuts

 $ifm\ electronic\ gmbh\ \bullet\ Friedrichstraße\ 1\ \bullet\ 45128\ Essen\ -\ We\ reserve\ the\ right\ to\ make\ technical\ alterations\ without\ prior\ notice.\ -\ GB\ -\ IGS206\ -\ 06.03.2003$