
FM41P_{Series} (1806 Size)







6A max, 1806 size chip 3-terminal capacitor for power lines. *Please refer to the products which are designed for both power lines and signal lines.




Refer to pages from p.142 to p.147 for mounting information.

■ Rated Value (□: packaging code)

	Part Number	Capacitance	Rated Current	Rated Voltage	Insulation Resistance (min.)	Operating Temperature Range	
ı	NFM41PC204F1H3□	0.2µF +80/-20%	2A	50Vdc	1000M ohm	-55°C to +85°C	Kit ≧1A
	NFM41PC155B1E3	1.5µF ±20%	6A	25Vdc	300M ohm	-55°C to +85°C	Kit ≧3A

Number of Circuit: 1

■ Insertion Loss Characteristics (Main Items)



muRata

[⚠]Note • Please read rating and ⚠CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
• This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.