



- Features:
- · Output current level selectable by DIP S.W.
- 180~295VAC input only
- · Built-in active PFC function
- Protections: Short circuit / Over voltage / Over temperature
- · Cooling by free air convection
- · Fully isolated plastic case
- · Built-in DALI interface and push dimming function
- Built-in 12V/50mA auxiliary output
- Temperature compensation function by external NTC
- No load power consumption <1.2W(Note.7)
- · Power supplies synchronization function up to 10 units
- · Suitable for indoor LED lighting applications
- 3 years warranty


110 W W 🗇 SELV 🕝 3 SUs 🖫 CB(€ **SPECIFICATION**

MODEL		LCM-60DA						
	SELECTABLE CURRENT Note.3	500mA	600mA	700mA	900mA	1050mA	1400mA	
	DC VOLTAGE RANGE	2~90V	2 ~ 90V	2 ~ 86V	2 ~ 67V	2 ~ 57V	2 ~ 42V	
	RATED POWER	60.3W						
	RIPPLE CURRENT	±5%						
OUTPUT	RIPPLE & NOISE (max.) Note.2	700mVp-p						
	NO LOAD OUTPUT VOLTAGE (max.)	95V			73V			
	CURRENT ACCURACY	±5.0%						
	SETUP, RISE TIME Note.5	1000ms, 80ms / 230VAC at rated power						
	HOLD UP TIME (Typ.)	16ms/230VAC at rated power						
	VOLTAGE RANGE Note.4	180 ~ 295VAC 25	4 ~ 417VDC					
	FREQUENCY RANGE	47 ~ 63Hz						
	POWER FACTOR (Typ.)	PF ≥ 0.975/230VAC, PF ≥ 0.96/277VAC at rated power (Please refer to "Power Factor Characteristic" curve)						
INPUT	TOTAL HARMONIC DISTORTION	Total harmonic distorti	on will be lower	than 20% when outpu	t loading is 75% or hig	jher		
INPUI	EFFICIENCY (Typ.) Note.6	92%						
	AC CURRENT (Typ.)	0.32A/230VAC 0.	27A/277VAC					
	INRUSH CURRENT (Typ.)	COLD START 20A(twidtl	$n=270\mu$ s measure	ed at 50% Ipeak) at 230\	/AC			
	LEAKAGE CURRENT	<0.5mA / 240VAC						
	SHORT CIRCUIT	Constant current limitir	ıg, recovers auto	matically after fault co	ndition is removed			
	OVER VOLTAGE	105 ~ 125V						
PROTECTION	OVER VOLIAGE	Protection type : Shutdown o/p voltage, re-power on to recover						
	OVER TEMPERATURE	90°C ±10°C (RTH2)						
	OVER TEINIFERATURE	Protection type: Shut down o/p voltage, re-power on to recover						
	AUXILIARY POWER	12V @ 50mA for drivin	g fan; Tolerance	±5%				
FUNCTION	TEMP. COMPENSATION	By external NTC(not p	rovide with the p	ower supply), please	see "Temperature cor	mpensation operation	"	
FUNCTION	DIMMING	Please see "Dimming Operation"						
	SYNCHRONIZATION	Please see "Synchronization Operation"						
	WORKING TEMP.	-30 ~ +60°C (Refer to "	Derating Curve")					
	WORKING HUMIDITY	20 ~ 90% RH non-cond	lensing					
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +80 °C, 10 ~ 95% RH						
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)						
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes						
	SAFETY STANDARDS	UL8750, ENEC EN613	47-1, EN61347-2	2-13,EN62384 indepe	ndent approved			
	DALI STANDARDS	Comply with IEC62386-101, 102, 207						
SAFETY &	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC						
EMC	ISOLATION RESISTANCE	I/P-O/P:>100M Ohms / 500VDC / 25°C / 70% RH						
	EMC EMISSION	Compliance to EN55015, EN61000-3-2 Class C(≥40% rated power) ; EN61000-3-3						
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, EN61547 light industry level (surge 2KV), criteria A						
	MTBF	193.6K hrs min. MIL-HDBK-217F (25°C)						
OTHERS	DIMENSION	123.5*81.5*23mm (L*W*H)						
	PACKING	0.24Kg; 54pcs/15Kg/1.12CUFT						
NOTE	Ripple & noise are measure Please see "DIP switch tab Derating may be needed ur	ters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. Dise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf parallel capacitor.						


- Length of set up time is measured at first cold start. Turning ON/OFF the power supply may lead to increase of the set up time.
- 6. Efficiency is measured at 900mA/67V output set by DIP switch.
- 7. No load power consumption<1.2W is measured at 180~277VAC, with lighting fixture connected and output current dimmed to 0%.
- 8. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.



■ Mechanical Specification



※ T case: Max. Case Temperature.




Terminal Pin No. Assignment(TB1)

Terminari iir No. Assigninenii (TDT)					
Pin No.	Assignment	Pin No.	Assignment		
1	AC/L	4	DA+		
2	AC/N	5	DA-		
3	PUSH				

Case No.LCM-60A

Unit:mm



Terminal Pin No. Assignment(TB3)

		. ,	
Pin No.	Assignment	Pin No.	Assignment
1	+FAN	3	+NTC
2	-FAN	4	-NTC


Terminal Pin No. Assignment(TB5)

Pin No.	Assignment
1	+Vo
2	-Vo

SYN. Connector(CN101/CN100):JST B2B-XH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1,3	+	JST XHP	JST SXH-001T-P0.6
2,4	-	or equivalent	or equivalent

PFC fosc: 60KHz PWM fosc: 80KHz



70 (HORIZONTAL)

■ Derating Curve

-30

-15

■ Block Diagram


100 Others 80 60 40 1050mA / 1400mA 20

AMBIENT TEMPERATURE (°C)

30

15

Static Characteristics




■ DIP Switch Table

LCM-60DA is a multiple-stage output current supply, selection of output current through DIP switch as table below.


lo DIP S.W.	1	2	3	4	5	6
500mA						
600mA	ON					
700mA(Factory Setting)	ON	ON				
900mA	ON	ON	ON			ON
1050mA	ON	ON	ON	ON		ON
1400mA	ON	ON	ON	ON	ON	ON

■ Power Factor Characteristic

Constant Current Mode




Constant Current Mode



■ EFFICIENCY vs LOAD

LCM-60DA series possess superior working efficiency that up to 92% can be reached in field applications.



(230Vac Input)

95.0% 90.0% 85.0% 80.0% **EFFICIENCY (%)** 500 75.0% 70.0% 700 65.0% 900 60.0% 1050 55.0% **1400** 50.0% 45.0% 40.0% 10% 20% 30% 40% 50% 60% 70% 80% 90% 100%




■ DIMMING OPERATION

% PUSH dim(primary side)

Ignore	Ignore To avoid reaction on AC spike	
Short push Push to turn ON-OFF		0.1~1 sec.
Long push	Dimming up or down	1.5~10 sec.
Reset push	Setting light to 100%	>11 sec.

- Maximum number of drivers up to 10 pcs.
- Maximum length of the cable, from push button to last driver is 20 meter.
- · Factory setting at 100%.
- · When the light is lower than 10% it will always dim up, or when the light output is higher than 90% it will always dim down.




Warning: The pushbutton can only be connected in between the PUSH terminal of LCM-60DA and AC/L (brown or black color). It would cause short circuit if it is connected to AC/N.

DALI interface(primary side)

- · DALI protocol including 16 groups and 64 addresses.
- · First step is fixed at 6% light output.


■ SYNCHRONIZATION OPERATION

- 10 drivers(max.) synchronization (1 master + 9 slaves)
- · Maximum cable length between each units: 20 meter.





■ TEMPERATURE COMPENSATION OPERATION



Sensed Temperature(degree)

LCM-60DA have the built-in temperature compensation function (T ↑, Io ↓). By connecting a temperature sensor (NTC resistor) between the NTC +/terminal of LCM-60DA and the detecting point on the lighting system or the surrounding environment, output current of LCM-60DA could be correspondingly changed to ensure the long life of LED.

1.LCM-60DA can still be operated well when the NTC resistor is not connected and the value of output current will be the current level that you set through the DIP switch.

2.

NTC resistance	Output Current
220K	< 60°C, 100% of the rated current (corresponds to the setting current level) > 60°C, output current begin to reduce, details please refer to the curve.
330K	< 70°C, 100% of the rated current (corresponds to the setting current level) > 70°C, output current begin to reduce, details please refer to the curve.
470K	< 80°C, 100% of the rated current (corresponds to the setting current level) > 80°C, output current begin to reduce, details please refer to the curve.

Notes: 1. MW does not offer the NTC resistor and all the data above are measured by using THINKING TTC03 series.

- 2. If other brands of NTC resistor is applied, please check the temperature curve first.
- 3. Synchronization function of the power supply will be invalid when the" temperature compensation function" is in use.