

Front element, +bulkhead interface RJ45

Part no. Article no. Catalog No. M22-RJ45-SA 107413 M22-RJ45-SAQ



## **Delivery programme**

Product range	RMQ-Titan (drilling dimensions 22.5 mm)
Accessories	General accessories
Basic function	Accessories
Basic function accessories	Bulkhead interface, RJ45 socket
Single unit/Complete unit	Single unit
Degree of Protection	IP65 (with closed cover) IP20 (with plug connected)
For use with	Front mounting RJ45, socket to socket 8/8, CAT5e
Front ring	Front ring: titanium
Connection to SmartWire-DT	no
Terminal diagram / contact assignment	SH SH   1 1   2 2   3 2   3 3   4 4   5 6   6 7   8 8   SH SH

SH: Schirmung

# Technical data

Technical data			
Nominal voltage	UL		AC 24 V
Voltage range			AC 50 V
Rated current		mA	1500
Pole			8 pole
Class / category			5
Contact type art			1:1
Screen earth kit			yes
General			
Design			RJ45
Insulation resistance	R <sub>ISO</sub>	MΩ	>≧ 100
Volume resistance			< 30 mΩ
Contact material			CuSn, gold-plated
Mounting			Front panel cutout d = 22.5 mm
Mounting depth:		mm	ca. 70 (incl. Krümmung)
Ambient temperature		°C	- 25 - + 70
Storage		°C	- 25 - + 80
Lifespan, mechanical	Operations		< 750 insertion cycles
Weight		kg/piece	0.02

#### Design verification as per IEC/EN 61439

Technical data for design verification			
Heat dissipation capacity	P <sub>diss</sub>	W	0

C/EN 61439 design verification	
10.2 Strength of materials and parts	
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Please enquire
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must l observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must l observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### **Technical data ETIM 5.0**


Low-voltage industrial components (EG000017) / Accessories for control circuit devices (EC002024)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Low-voltage switch technology (accessories) / Control circuit devices (accessories) (ecl@ss8-27-37-92-16 [AC0043007])			
Type of electrical accessory			
Type of mechanical accessory	· · · · · · · · · · · · · · · · · · ·		

## Approvals

UL 508; CSA-C22.2 No. 142; IEC/EN 6113-2; CE marking
E330994
DUXR, DUXR7
UL report applies to both US and Canada
-
UL listed, certified by UL for use in Canada
IEC: IP65 and UL/CSA NEMA Type 12 when closed, IP20 when connected

Ch-			
una	racte	eristi	CS

SH	- SH
1 —	<b>_</b>
2 🗖 —	
3 —	3
	<b>-------------</b>
5 —	<b>-------------</b>
SH	
	<b>-L</b> 3П



#### Additional product information (links)

#### IL04716002Z (AWA1160-1745) RMQ-Titan System

IL04716002Z (AWA1160-1745) RMQ-Titan System ftp://ftp.moeller.net/DOCUMENTATION/AWA\_INSTRUCTIONS/IL04716002Z2013\_08.pdf