



## Complete device, top mouting



Powering Business Worldwide™

**Part no.** M22-WRS/KC11/I

**Article no.** 216526





Maintained/momentary function and key withdraw convertible with coding adapters M22-XC-..., → Engineering

With 1 key

2 positions, maintained

Lock mechanism MS1



### Program

Range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Key-operated buttons
Single unit/Complete unit			Complete unit
Description			Stay-put/spring-return function, can be changed with coding parts M22-XC-Y Key withdraw convertible with coding adapters M22-XC-... With 1 key Lock mechanism MS1
Function			2 positions, maintained
Number of locations		Qty.	1
Auxiliary contacts:  = safety function, by positive opening to IEC/EN 60947-5-1			
N/O = Normally open			1 N/O
N/C = Normally closed			1 N/C 
Contact sequence			
Colour of enclosure top			
RAL Value			RAL 7035
Front ring			Bezel: Silver
Connection to SmartWire-DT			no

### Approbationen

UL approval	Yes
CSA approval	Yes
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	012528
CSA Class No.	3211-03
NA Certification	UL listed, CSA certified
Degree of Protection	UL/CSA Type 3R, 4X, 12, 13

### General

Standards			IEC/EN 60947 VDE 0660
Lifespan, mechanical	Operations	x 10 <sup>6</sup>	> 0.1
Operating frequency	Operations/ h		 100
Operating torque		Nm	 0.5

Protection type			IP66
Climatic proofing			Damp heat, constant to IEC 60068-2-78 Damp heat, cyclic to IEC 60068-2-30
Ambient temperature		°C	
Open		°C	- 25 - + 70
Mounting position			As required
Mechanical shock resistance		g	30 Shock duration 11 ms Sinusoidal according to IEC 60068-2-27
Cable entry knockouts			
Base		Quantity x M...	2 x 16
Sides		Quantity x M...	1 x 20 2 x 25/20

### Technical data according to ETIM 4.0

Protection type (IP)			IP66
Number of contacts as N/Cs			1
Housing material			Insulated material
Number of contacts as changeover contact			0
Color housing cover			gray
Number of mushroom pushbuttons			0
Number of selector switches			1
Number of key switches			1
Number of contacts as N/O			1
Rated control voltage Us at AC 50HZ		V	500
Rated control voltage Us at DC		V	230
Number of indicator lights			0
Suitable for emergency switching off			No
Number of pushbutton actuators			0
Rated control voltage Us at AC 60HZ		V	500
Number of locations			1

### CAD-Data

Product standards CAD data:

<http://eaton-moeller.partcommunity.com>

### Additional product information (links)

IL04716002Z (AWA1160-1745) RMQ-Titan System	<a href="ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2011_03.pdf">ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2011_03.pdf</a>
<b>Engineering</b>	
Key to part numbers	<a href="ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/TYPENSCHLUESSEL_RM-Q-TITAN_de.pdf">ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/TYPENSCHLUESSEL_RM-Q-TITAN_de.pdf</a>
Ordering example for custom complete units	<a href="ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/Bestellbeispiel_F0315_COMBINATION_de.pdf">ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/Bestellbeispiel_F0315_COMBINATION_de.pdf</a>
Order form for custom complete units	<a href="ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf">ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf</a>
Dimensions	<a href="ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/DIM_RM-Q-Titan_Schliesseltasten_Einzel_G.pdf">ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/DIM_RM-Q-Titan_Schliesseltasten_Einzel_G.pdf</a>