

PT-104 Data Logger

Temperature, Resistance, Voltage


The ultimate in resolution and accuracy

0.001 °C

0.01 °C

- Measures and records up to 4 platinum resistance thermometers
- Works with PT100 and PT1000 sensors
- Supports 2, 3 and 4-wire sensors
- Measures voltage and resistance
- 24-bit ADC
- Uses calibrated reference resistors for stability
- Supplied with PicoLog data logging software
- USB interface ensures easy installation
- Ethernet interface for remote operation
- Powered by USB port or Power-over-Ethernet (PoE)
- Multiple units can be run on a single PC





www.picotech.com

USB PT-104 PRT Data Logger



Flexible: Measures temperatures with either PT100 or PT1000 sensors, as well as resistance and voltage.

Adaptable: Can measure and record temperatures ranging from –200 °C to +800 °C.


Stable: Instead of voltage references, which tend to drift with temperature, the PT-104 uses high-precision

reference resistors. **Expandable:** Up to 20 units can be used simultaneously on one PC. **Portable:** The PT-104 obtains its power from either the USB port or Power-over-Ethernet (PoE), so no additional power cable is needed.



PicoLog

PicoLog is a powerful and flexible data acquisition program designed for collecting, analyzing and displaying data over long or short periods of time. Data can be viewed both during and after data collection in spreadsheet or graphical format. If required, the data can also be easily exported to other applications.



In addition to the monitor view, PicoLog can also display a graph, a spreadsheet and user notes. It can display them all at once, as shown here, or individually in any combination.

Software drivers

For users who wish to write their own software or use our products with third-party software, we provide, free of charge, a range of software drivers and examples. Drivers are included for Windows XP (SP2), Vista and Windows 7. Programming examples are supplied for C, LabVIEW and Excel.

ORDER CODES and PRICES

CODE	DESCRIPTION	GBP	USD*	EUR*
PP682	PT-104 Data Logger	399.00	658.35	482.79
PP660	Screw Terminal Adapter	6.00	9.90	7.02
SE011	PT-100 Temperature Sensor	23.00	37.95	27.83

* Dollar and euro prices were correct at the time of printing. For latest prices see our website or contact us at the address below.



Pico Technology James House T: +44 (0) 1480 396 395

Colmworth Business Park St No F: +44 (0) 1480 396 296

St Neots Cambridgeshire PE19 8YP 6 296 E: sales@picotech.com

Specifications

	Temperature	Resistance	Voltage	
Sensor	PT100, PT1000	N/A	N/A	
Range	-200 to +800 °C	0 to 375 Ω	0 to 115 mV	
		0 to 10 kΩ	0 to 2.5 V	
Linearity	20 ppm	20 ppm	20 ppm	
Accuracy at 25 °C	0.01 °C	20 ppm	0.2% (2.5 V)	
Temp. coefficient	5 ppm∕°C	5 ppm∕°C	100 ppm/°C	
RMS noise with filter	0.01 °C	10 ppm	10 ppm	
Resolution	0.001 °C	1 μΩ	0.156 µV	
Overload protection	±30 V			
Number of inputs	Number of inputs 4			
Converter resolution	24 bits			
Conversion time	720 ms per channel			
Input connectors	4-pin mini DIN			
Input impedance	>> 1 MΩ			
Output connectors	USB & Ethernet			
Power supply	USB or Ethernet			
Temperature range	20 °C to 30 °C for stated accuracy			
	0 °C to 70 °C operating			
	-20 °C to +80 °C storage			
Humidity range	20% to 90% RH, non-condensing, operating			
	5% to 95% RH, non-condensing, storage			
Dimensions	184 x 135 x 36 mm			
	(5.31 × 7.24 × 1.42 in.)			

Screw-terminal adapter

Connects discrete wires to the PT-104 without soldering. Suitable for wire-ended sensors and custom circuits.



PRTs

General-purpose probe

Many other types available!

Pico Technology offers a range of platinum resistance thermometers (PRTs) for use with the PT-104. The PT-104 is compatible with all standard PT100 and PT1000 PRTs, which offer high accuracy, resolution and stability. All our probes have a stainless steel body and a 1 m long cable.

For full information on PRT specifications, characteristics and prices, go to :

accessories.picotech.com

and click "Sensors".



Copyright © 2010 Pico Technology Ltd.

MM000-1