


Multilayer Capacitors, SMD



Capacitor, 0805



SPECIFICATION:

Construction form	0805
Ceramic type	COG/NPO
Temperature range	-55...+125 °C
Length	2 mm
Width	1.5 mm

PRODUCT RANGE:

Art. Nr.	Capacitance	Rated voltage	Capacitance tolerance	Dimensions L x H x W	Height
RND1500805N0R5C500	0.5 pF	50 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N1R0C500	1 pF	50 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N1R0C201	1 pF	200 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N1R0C501	1 pF	500 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N1R5C500	1.5 pF	50 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N1R5C501	1.5 pF	500 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N2R0C500	2 pF	50 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N2R2C201	2.2 pF	200 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N3R0C500	3 pF	50 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N3R3C201	3.3 pF	200 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N3R3C501	3.3 pF	500 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N4R0C500	4 pF	50 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N4R7C201	4.7 pF	200 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N4R7C501	4.7 pF	500 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N5R0C500	5 pF	50 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N6R0D500	6 pF	50 VDC	±0.5 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N6R8C201	6.8 pF	200 VDC	±0.25 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N7R0D500	7 pF	50 VDC	±0.5 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N8R0D500	8 pF	50 VDC	±0.5 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N9R0D500	9 pF	50 VDC	±0.5 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N100D500	10 pF	50 VDC	±0.5 pF	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N100J500	10 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N100J101	10 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N100J501	10 pF	500 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N120J500	12 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N150J500	15 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N150J101	15 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N180J500	18 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N180J101	18 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N220J500	22 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N220J101	22 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm

Distrelec Schweiz AG, Grabenstrasse 6, 8606 Nänikon, Switzerland, T +41 44 944 99 11, info@distrelec.com, distrelec.com

Art. Nr.	Capacitance	Rated voltage	Capacitance tolerance	Dimensions L x H x W	Height
RND1500805N220J201	22 pF	200 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N270J500	27 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N330J500	33 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N330J101	33 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N330J201	33 pF	200 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N330J501	33 pF	500 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N470J500	47 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N470J101	47 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N470J201	47 pF	200 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N560J500	56 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N680J500	68 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N680J101	68 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N680J201	68 pF	200 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N680J501	68 pF	500 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N820J500	82 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N101J500	100 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N101J101	100 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N101J201	100 pF	200 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N101J501	100 pF	500 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N121J500	120 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N151J500	150 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N151J101	150 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N221J500	220 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N221J101	220 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N221J201	220 pF	200 VDC	±5%	2 x 1.25 x 1.5 mm	1.25 mm
RND1500805N221J501	220 pF	500 VDC	±5%	2 x 1.25 x 1.5 mm	1.25 mm
RND1500805N271J500	270 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N331J500	330 pF	50 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N331J101	330 pF	100 VDC	±5%	2 x 0.6 x 1.5 mm	0.6 mm
RND1500805N331J201	330 pF	200 VDC	±5%	2 x 1.25 x 1.5 mm	1.25 mm
RND1500805N331J501	330 pF	500 VDC	±5%	2 x 1.25 x 1.5 mm	1.25 mm
RND1500805N391J500	390 pF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N471J500	470 pF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N471J101	470 pF	100 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N511J500	510 pF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N561J500	560 pF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N681J500	680 pF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N681J101	680 pF	100 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N821J500	820 pF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N102J500	1 nF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N102J101	1 nF	100 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N122J500	1.2 nF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N152J500	1.5 nF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N182J500	1.8 nF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N222J500	2.2 nF	50 VDC	±5%	2 x 0.8 x 1.5 mm	0.8 mm
RND1500805N272J500	2.7 nF	50 VDC	±5%	2 x 1.25 x 1.5 mm	1.25 mm