


Multilayer Capacitors, SMD



Capacitor 0805



FEATURES:

Offers soft & flexible polymer layer termination
Withstands high bending stress in SMT line

SPECIFICATION:

Construction form	0805
Dimensions L x H x W	2.00 x 1.25 x 1.25 mm
Temperature range	-55...+125 °C
Height	1.25 mm
Length	2.00 mm
Width	1.25 mm

PRODUCT RANGE:

Art. Nr.	Capacitance	Rated voltage	Ceramic type	Capacitance tolerance
RND150SH21B101K160	100 pF	16 VDC	X7R	±10%
RND150SH21B101K250	100 pF	25 VDC	X7R	±10%
RND150SH21B101K500	100 pF	50 VDC	X7R	±10%
RND150SH21B101K101	100 pF	100 VDC	X7R	±10%
RND150SH21B151K500	150 pF	50 VDC	X7R	±10%
RND150SH21B221K500	220 pF	50 VDC	X7R	±10%
RND150SH21B221K101	220 pF	100 VDC	X7R	±10%
RND150SH21B471K101	470 pF	100 VDC	X7R	±10%
RND150SH21B102K100	1 nF	10 VDC	X7R	±10%
RND150SH21B102K160	1 nF	16 VDC	X7R	±10%
RND150SH21B102K250	1 nF	25 VDC	X7R	±10%
RND150SH21B102K500	1 nF	50 VDC	X7R	±10%
RND150SH21B222K250	2.2 nF	25 VDC	X7R	±10%
RND150SH21B472K160	4.7 nF	16 VDC	X7R	±10%
RND150SH21B472K250	4.7 nF	25 VDC	X7R	±10%
RND150SH21B472K500	4.7 nF	50 VDC	X7R	±10%
RND150SH21B472K101	4.7 nF	100 VDC	X7R	±10%
RND150SH21B682K500	6.8 nF	50 VDC	X7R	±10%
RND150SH21B103K100	10 nF	10 VDC	X7R	±10%
RND150SH21B103K160	10 nF	16 VDC	X7R	±10%
RND150SH21B103K250	10 nF	25 VDC	X7R	±10%
RND150SH21B103K500	10 nF	50 VDC	X7R	±10%
RND150SH21B103K101	10 nF	100 VDC	X7R	±10%
RND150SH21B153K500	15 nF	50 VDC	X7R	±10%
RND150SH21B223K250	22 nF	25 VDC	X7R	±10%
RND150SH21B333K500	33 nF	50 VDC	X7R	±10%

Distrelec Schweiz AG, Grabenstrasse 6, 8606 Nänikon, Switzerland, T +41 44 944 99 11, info@distrelec.com, distrelec.com

Art. Nr.	Capacitance	Rated voltage	Ceramic type	Capacitance tolerance
RND150SH21B473K500	47 nF	50 VDC	X7R	±10%
RND150SH21B683K101	68 nF	100 VDC	X7R	±10%
RND150SH21B104K100	100 nF	10 VDC	X7R	±10%
RND150SH21B104K160	100 nF	16 VDC	X7R	±10%
RND150SH21B104K250	100 nF	25 VDC	X7R	±10%
RND150SH21B104K500	100 nF	50 VDC	X7R	±10%
RND150SH21B104K101	100 nF	100 VDC	X7R	±10%
RND150SH21B154K500	150 nF	50 VDC	X7R	±10%
RND150SH21B224K500	220 nF	50 VDC	X7R	±10%