# Stacked Coin Type

Series: SD

#### ■ Features

• Endurance: 70 °C 1000 h RoHS directive compliant





### ■ Recommended Applications

 Memory back-up for video and audio equipment, cameras, telephones, printers, data terminals, rice cookers, intelligent remote controls

## Specifications

Category Temp. Range	−25 °C to +70 °C					
Maximum Operating Voltage	5.5 V.DC					
Nominal Cap.Range	0.022 F to 0.33 F					
Characteristics at Low Temperature	Capacitance change	±30 % of initial measured value at +20 °C (at -25 °C)				
	Internal resistance	≤5 times of initial measured value at +20 °C (at -25 °C)				
Endurance	After 1000 hours application of 5.5 V. DC at +70 °C, the capacitor shall meet the following limits.					
	Capacitance change	±30 % of initial measured value				
	Internal resistance	≤4 times of initial specified value				
Shelf Life	After 1000 hours storage at +70°C without load, the capacitor shall meet the specified limits for Endurance.					

### ■ Dimensions in mm(not to scale)

(Unit: mm) Terminal: V Terminal: H Sleeve ø10.5 max 10.5 max. B max (00 11.5 max  $0.2 \pm 0.05$ 0.8±0.05 5.0±0.8 0.2±0.05 (1.7) 10.0±0.5 0.8±0.05 Cap. (F) Cap. (F) В 0.022 to 0.1 5.5 5.0 0.022 to 0.22 0.22 6.0 0.33 5.5 0.33 6.5

### ■ Standard Products

- Claridard Froducto								
Maximum Operating Voltage		Capacitance tolerance	Internal resistance (Initial specified value)	Part number	Min. Packaging Q'ty			
(V.DC)	(F)	(F)	(Ω) at 1kHz		(pcs)			
5.5	0.022	0.0176 to 0.0396	≤ 150	EECS0HD 223()	200			
	0.047	0.0376 to 0.0846	≤ 120	EECS0HD 473()	200			
	0.10	0.080 to 0.180	≤ 75	EECS0HD 104()	200			
	0.22	0.176 to 0.396	≦ 75	EECS0HD 224()	200			
	0.33	0.264 to 0.594	≤ 75	EECS0HD 334()	200			

() Please use V or H, to indicate the terminal style.

Note: Do not use reflow soldering. (IR, Atmosphere heating methods, etc.)

Please refer to EE208 "Mounting Specifications".