



## Description

This Isolated Ground series provide negative / positive ground reference compatibility, allowing connection of negative ground equipment to positive or floating ground battery system or vice versa. They offer protection level for themselves and to the connected loads. They also offer protection against transient voltages spikes typically encountered on electric fork lifts. Being switch mode, they have high efficiency (>80%), produces little heat and are of small size for the power they deliver.

## **Features**

- Negative or positive ground reference
- High efficiency 88%
- Low profile, high power density
- Protection against transient voltages
- **EMC INTERFERENCE IMMUNITY**
- 22 30VDC input voltage
- Overload and short circuit protection
- Over current protection
- LED power on indicator

## **Specifications**

Models	SSDC - 210	SSDC - 240	
Input Voltage Range	22 - 30VDC	22 - 30VDC	
Output Voltage	13.8VDC	13.8VDC	
Continuous Output Current	8A	35A	
Maximum Output Current	10A	40A	
Ripple & Noise (peak-peak)	<100mVp-p	<250mVp-p	
Load Regulation (0-100% load)	350mV	250mV	
Line Regulation (20-30V variation)	30mV	50mV	
Efficiency	>86%	>84%	
Input Connection Type	Cable	Cable	
Output Connection Type	Cable	Terminal	
Indicators	Power on LED	Power on LED	
Cooling System	Natural Convection	Variable Speed Thermally Control Fan	
Protection Devices	Overload, Short Circuit	Overload, Short Circuit	
Input Fuse Type	Standard Car Blade Fuse	Standard Car Blade Fuse	
CE Approvals	EN 55011	EN 55022	
e-Mark Approvals	e11 02 1520	NIL	
Dimensions (WxHxD)	125x47x120 mm 4.9x1.9x4.7 incl	156x57x240 mm 6.1x2.2x9.5 inch	
Weight	0.65 kg 1.4 lbs	2.2 kg 5 lbs	
Accessory	Nil	Mounting Bracket	

- All values are based on the Standard ambient Temperature 25°C and Pressure 0.1 Mpa.
- SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE