
SIEMENS

3RW40 37-1BB14 Data sheet



SIRIUS SOFT STARTER, S2, 63A, 30KW/400V, 40 DEGR., AC 200-480V, AC/DC 110-230V, SCREW **TERMINALS**

SIRIUS
Yes
Yes
Yes
Yes
No
Yes
Yes
No
No
Q
G
Soft starter

Operating current		
• at 40 °C rated value	Α	63
• at 50 °C rated value	Α	58
• at 60 °C rated value	Α	53
Mechanical power output for three-phase motors		
● at 230 V		
— at standard circuit at 40 °C rated value	W	18 500
● at 400 V		
— at standard circuit at 40 °C rated value	W	30 000
Yielded mechanical performance [hp] for three-phase	hp	15
AC motor at 200/208 V at standard circuit at 50 °C rated value	·	
Operating frequency rated value	Hz	50 60
Relative negative tolerance of the operating	%	-10
frequency		
Relative positive tolerance of the operating frequency	%	10
Operating voltage at standard circuit rated value	V	200 480
Relative negative tolerance of the operating voltage at standard circuit	%	-15
Relative positive tolerance of the operating voltage at standard circuit	%	10
Minimum load [% of IM]	%	20
Adjustable motor current for motor overload	Α	26
protection minimum rated value		
Continuous operating current [% of le] at 40 °C	%	115
Power loss [W] at operating current at 40 °C during operation typical	W	12
Control electronics		
Type of voltage of the control supply voltage		AC/DC
Control supply voltage frequency 1 rated value	Hz	50
Control supply voltage frequency 2 rated value	Hz	60
Relative negative tolerance of the control supply	%	-10
voltage frequency		
Relative positive tolerance of the control supply	%	10
voltage frequency		
Control supply voltage 1 at AC at 50 Hz	V	110 230
Control supply voltage 1 at AC at 60 Hz	V	110 230
Relative negative tolerance of the control supply voltage at AC at 60 Hz	%	-15
Relative positive tolerance of the control supply voltage at AC at 60 Hz	%	10
Control supply voltage 1 at DC	V	110 230
Relative negative tolerance of the control supply voltage at DC	%	-15

Relative positive tolerance of the control supply	%	10
voltage at DC		
Display version for fault signal		red
Mechanical data		
Size of engine control device		S2
Width	mm	55
Height	mm	160
Depth	mm	170
Mounting type		screw and snap-on mounting
Mounting position		With additional fan: With vertical mounting surface +/- 90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back Without additional fan: With vertical mounting surface +/-10° rotatable, with vertical mounting surface +/- 10° t
Required spacing with side-by-side mounting		
• upwards	mm	60
• at the side	mm	30
• downwards	mm	40
Installation altitude at height above sea level	m	5 000
Wire length maximum	m	300
Number of poles for main current circuit		3
Connections/Terminals		
Type of electrical connection		
• for main current circuit		screw-type terminals
 for auxiliary and control current circuit 		screw-type terminals
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		2
Number of CO contacts for auxiliary contacts		1
Type of connectable conductor cross-sections for main contacts for box terminal using the front clamping point		
• solid		2x (1.5 16 mm²)

Number of NC contacts for auxiliary contacts	0
Number of NO contacts for auxiliary contacts	2
Number of CO contacts for auxiliary contacts	1
Type of connectable conductor cross-sections for	
main contacts for box terminal using the front	
clamping point	
• solid	2x (1.5 16 mm²)
 finely stranded with core end processing 	0.75 25 mm²
• stranded	0.75 35 mm²
Type of connectable conductor cross-sections for	
main contacts for box terminal using the back	
clamping point	
• solid	2x (1.5 16 mm²)
 finely stranded with core end processing 	1.5 25 mm²
• stranded	1.5 35 mm²
Type of connectable conductor cross-sections for	
main contacts for box terminal using both clamping	
points	

• solid		2x (1.5 16 mm²)
 finely stranded with core end processing 		2x (1.5 16 mm²)
• stranded		2x (1.5 25 mm²)
Type of connectable conductor cross-sections at		
AWG conductors for main contacts for box terminal		
 using the back clamping point 		16 2
using the front clamping point		18 2
using both clamping points		2x (16 2)
Type of connectable conductor cross-sections for		
auxiliary contacts		
• solid		2x (0.5 2.5 mm²)
 finely stranded with core end processing 		2x (0.5 1.5 mm²)
Type of connectable conductor cross-sections at		
AWG conductors		
• for auxiliary contacts		2x (20 14)
 for auxiliary contacts finely stranded with core 		2x (20 16)
end processing		
Ambient conditions		
Ambient temperature		
·	°C	-25 +60
during operation		
during storage	°C	-40 +80

°C

40

IP00

Derating temperature

Certificates/approvals

Protection class IP

General Product Approval

EMC

For use in hazardous locations













Declaration of Conformity	Test Certificates		Shipping App	roval	
CE	spezielle Prüfbescheinigunge <u>n</u>	Typprüfbescheinigu ng/Werkszeugnis	GL®	Lloyd's Register	
EG-Konf.			GL	LRS	PRS

\sim	\sim	

Umweltbestätigung

Bestätigungen

UL/CSA ratings		
Yielded mechanical performance [hp] for three-phase		
AC motor		
● at 220/230 V		
 at standard circuit at 50 °C rated value 	hp	20
● at 460/480 V		
— at standard circuit at 50 °C rated value	hp	40
Contact rating of auxiliary contacts according to UL		B300 / R300

Further information

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW4037-1BB14


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW4037-1BB14


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/ww/en/ps/3RW4037-1BB14

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW4037-1BB14&lang=en









last modified: 02/27/2017