

## **MLFB-Ordering data**

6SL3210-5BE24-0UV0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data		General teo	General tech. specifications	
nput		Power factor λ	0.72	
Number of phases	3 AC	Offset factor cos φ	0.95	
Line voltage	380 480 V -15 % +10 %	Efficiency η	0.98	
Line frequency	47 63 Hz	Ambient conditions		
Dutput		Cooling	External fan	
Number of phases	3 AC	Installation altitude	1000 m (3281 ft)	
Rated voltage	400 V	Ambient temperature		
Rated power (HO)	4.00 kW / 5.00 hp	Operation	-10 60 °C (14 140 °F)	
Rated power (LO)	4.00 kW / 5.00 hp	Storage	-40 70 °C (-40 158 °F)	
Rated current (HO)	8.80 A	Relative humidity		
Rated current (LO)	8.80 A	Max. operation	95 %	
Rated current (HO) at 480V	8.20 A	Communication		
Rated current (LO) at 480V	8.20 A	Communication	USS, Modbus RTU	
Pulse frequency	2 kHz			
Output frequency	0 550 Hz	Standards		
	000	Compliance with standards	CE, cULus, C-Tick (RCM), KC	
		CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3	

#### **Overload capability**

## Low Overload (LO)

110 % rated output current for 60 s, cycle time 300 s

#### High Overload (HO)

150 % rated output current for 60 s, cycle time 300 s



# **MLFB-Ordering data**

6SL3210-5BE24-0UV0



Figure similar

Mechanical data			Connections
Mounting position	rough-hole mounting / wall mounting / le-by-side mounting	Max. motor cable length	
10	le-by-side mounting	Shielded	25 m (82 ft)
Degree of protection IF	20	Unshielded	50 m (164 ft)
Size F:	В		
Net weight 1	60 kg ( 3.53 lb )		
Width 1	0.0 mm ( 5.51 in )		
Height 1	0.0 mm ( 6.30 in )		
Depth 1	4.5 mm ( 6.48 in )		
Inputs	Inputs / outputs		
Standard digital inputs		_	
Number	4		
Digital outputs			
Number as relay changeover cor	tact 1		
Number as transistor	1		
Analog inputs			
Number	2 (Can be used as additional digital input)		
Analog outputs			
Number	1		