## Reliable isolation transformers from Tufvassons

Tufvassons has a wide range of transformers and over fifty years' experience of making them ourselves. We offer isolation transformers of the highest quality for fixed installation, mounting on a DIN rail, as well as movable versions that are connected with a mains cable. Select products yourself or have our staff guide you to the right power supply.



## Optimum isolation, removes interference

The isolation transformer is used when you need to adapt one voltage level to another one, or separate a protective earth from a system earth. It provides optimum isolation, minimises interference and is simple to install – including in the USA thanks to its USA-compatible outlet that is used for 110-volt products. Just like Tufvassons' other products, the isolation transformer is CE-marked and also has short circuit and overload protection.

 Type:
 TEZ 50

 Part. no.:
 6745-0042

 Input voltage:
 230V, 50-60 Hz.

Output voltage: 110V
Rated power: 50VA (0,45A)
Weight: 0.8 kg
Encapsulation class: IP30
Insulation class: 4.2 kV
Ambient temperature: max. 40°C

**Design:**• Transformer potted in hard-setting plastic, with grey encapsulation made from impact resistant, self

extinguishing thermoplastics.

- Double insulated (earth connection not required).

- Short circuit and overload protection with thermo protection.

Primary mains cable with European mains plug.Fully enclosed secondary 2-pole American outlet.

**Mounting:** Install in any position.

Manufacturing standard: Security: EN 61558-1; EN 61558-2-4

Emissions: EN 61 000-6-3; EN 61 000-6-4, IEC 62041 Immunity: EN 61 000-6-1; EN 61 000-6-2, IEC 62041

Other information: If the mains cable or plug is damaged, the transformer must be destroyed/recycled.














## Wiring schedule and product illustration



## **Loading diagram**

