



■ Features :

- Universal AC input / Full range
- Built in active PFC function, PF>0.95
- Protections: Short circuit / Overload / Over voltage / Over temperature
- · Forced air cooling by built-in DC fan
- High power density 5.18w/in³
- · Low profile:43mm thickness
- Built-in remote ON-OFF control
- · Built-in remote sense function
- · Active AC surge current limiting
- · 3 years warranty


SPECIFICATION



ODEL	SP-480-3.3	SP-480-5	SP-480-12	SP-480-15	SP-480-24	SP-480-48		
DC VOLTAGE	3.3V	5V	12V	15V	24V	48V		
RATED CURRENT	85A	85A	40A	32A	20A	10A		
CURRENT RANGE	0 ~ 85A	0 ~ 85A	0 ~ 43A	0 ~ 35A	0 ~ 22A	0 ~ 11A		
RATED POWER	280.5W	425W	480W	480W	480W	480W		
PEAK LOAD(10min.) Note.	5 280.5W	425W	516W	525W	528W	528W		
RIPPLE & NOISE (max.) Note.	2 80mVp-p	80mVp-p	120mVp-p	150mVp-p	150mVp-p	240mVp-p		
VOLTAGE ADJ. RANGE	2.9 ~ 3.6V	4.5 ~ 5.5V	10.8 ~ 13.2V	13.5 ~ 18V	22 ~ 27.6V	41~ 56V		
VOLTAGE TOLERANCE Note.	3 ±2.0%	±2.0%	±1.5%	±1.5%	±1.0%	±1.0%		
LINE REGULATION	±0.5%	±0.5%	±0.3%	±0.3%	±0.2%	±0.2%		
LOAD REGULATION	±1.0%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%		
SETUP, RISE TIME	1000ms, 80ms/230VAC 2500ms, 80ms/115VAC at full load							
HOLD UP TIME (Typ.)	18ms/230VAC 18ms/115VAC at full load							
VOLTAGE RANGE Note.	85 ~ 264VAC 120 ~ 370VDC							
FREQUENCY RANGE	47 ~ 63Hz							
POWER FACTOR (Typ.)	PF>0.95/230VAC PF>0.98/115VAC at full load							
IPUT EFFICIENCY (Typ.)	73%	79%	85%	85%	87%	89%		
AC CURRENT (Typ.)	6.5A/115VAC 3.5A/230VAC							
INRUSH CURRENT (Typ.)	20A/115VAC 40A/230VAC							
LEAKAGE CURRENT	<2mA / 240VAC							
	87 ~ 103A	87 ~ 103A	45.15 ~ 58.05A	36.75 ~ 47.25A	23.1 ~ 29.7A	11.55 ~ 14.85A		
OVERLOAD	Protection type : Constant current limiting, recovers automatically after conditions is removed							
POTESTION OVER VOLTAGE	3.8 ~ 4.45V	5.75 ~ 6.75V	13.8 ~ 16.2V	18 ~ 21V	28.8 ~ 33.6V	57.6 ~ 67.2V		
ROTECTION OVER VOLTAGE	Protection type : Shut down o/p voltage, re-power on to recover							
OVER TEMPERATURE N.	80°C (TSW1) detect on heatsink of power transistor 90°C (TSW2) detect on heatsink of power diode							
OVER TEMPERATURE Note.	Protection type : Shut down o/p voltage, recovers automatically after temperature goes down							
UNCTION REMOTE CONTROL	RC+/RC-: 0 ~ 0.8V=p	RC+/RC-: 0 ~ 0.8V=power on ; 4 ~ 10V=power off						
WORKING TEMP.	-20 ~ +60°C (Refer to "Derating Curve")							
WORKING HUMIDITY	20 ~ 90% RH non-condensing							
VVIRONMENT STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH							
TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)							
VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes							
SAFETY STANDARDS	UL60950-1, TUV EN60950-1 approved							
AFETY & WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:1.5KVAC O/P-FG:Short							
MC ISOLATION RESISTANCE	I/P-O/P, I/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH							
Note 6) EMC EMISSION	Compliance to EN55	Compliance to EN55022 (CISPR22) Class B, EN61000-3-2,-3						
EMC IMMUNITY	Compliance to EN61	000-4-2,3,4,5,6,8,11,	EN61000-6-2 (EN500	82-2), light industry le	vel, criteria A			
MTBF	120.5K hrs min. N	IIL-HDBK-217F (25℃)					
THERS DIMENSION	278*127*43mm (L*W	/*H)						
PACKING	1.7Kg; 6pcs/11.3Kg/0.67CUFT							
	0							

- 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor.
- 3. Tolerance: includes set up tolerance, line regulation and load regulation.
- 4. TSW1: Detect on heatsink of power transistor.
 - TSW2: Detect on heatsink of output diode.
- 5. 33% Duty cycle maximum within every 30 minute. Average output power should not exceed the rated power.
 6. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)
- 7. Derating may be needed under low input voltages. Please check the derating curve for more details.





Terminal Pin No. Assignment:

Pin No.	in No. Assignment		Assignment					
1	AC/L	4~6	-V					
2	2 AC/N		+V					
3	FG ±							

Connector Pin No. Assignment (CN51): HRS DF11-6DP-2DS or equivalent

Pin No.	Assignment	Pin No.	Assignment	Mating Housing	Terminal
1	GND	4	N.C.	LIDO DE44 CDC	UD0 DE44 **00
2	RC-	5	RC+	HRS DF11-6DS or equivalent	HRS DF11-**SC or equivalent
3	-S	6	+S	3. 544.174.10111	S. Squiraiont

