XB4BVB3

green complete pilot light Ø22 plain lens with integral LED 24V



Main

Range of product	Harmony XB4		
Product or component type	Complete pilot light		
Device short name	XB4		
Bezel material	Chromium plated metal		
Fixing collar material	Zamak		
Mounting diameter	22 mm		
Sale per indivisible quantity	1		
Shape of signaling unit head	Round		
Cap/Operator or lens colour	Green		
Operator additional information	With plain lens		
Light source	Protected LED		
Bulb base	Integral LED		
Light source colour	Green		
[Us] rated supply voltage	24 V AC/DC, 50/60 Hz		

Complementary

47 mm				
30 mm				
54 mm				
(X1-X2)PL				
0.08 kg				
7000000 Pa at 55 °C,distance: 0.1 m				
Screw clamp terminals: <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 Screw clamp terminals: 1 x 0.222 x 2.5 mm² without cable end conforming to EN/IEC 60947-1				
250 V (degree of pollution: 3) conforming to EN 60947-1				
4 kV conforming to EN 60947-1				
Steady				
21.626.4 V AC				
18 mA				
100000 h at rated voltage and 25 °C				
1 kV conforming to IEC 61000-4-5				

Environment


Protective treatment	TH			
Ambient air temperature for storage	-4070 °C			
Ambient air temperature for operation	-2570 °C			
Class of protection against electric shock	Class I conforming to IEC 60536			
IP degree of protection	IP66 conforming to IEC 60529			
NEMA degree of protection	NEMA 13			
	NEMA 4X			
IK degree of protection	IK05 conforming to IEC 50102			

Standards	CSA C22-2 No 14			
	EN/IEC 60947-1			
	EN/IEC 60947-5-1			
	EN/IEC 60947-5-4			
	EN/IEC 60947-5-5			
	JIS C 4520			
	UL 508			
Product certifications	CSA			
	UL listed			
Vibration resistance	5 gn (f = 12500 Hz) conforming to IEC 60068-2-6			
Shock resistance	30 gn for 18 ms half sine wave acceleration conforming to IEC 60068-2-27			
	50 gn for 11 ms half sine wave acceleration conforming to IEC 60068-2-27			
Resistance to fast transients	2 kV conforming to IEC 61000-4-4			
Resistance to electromagnetic fields	10 V/m conforming to IEC 61000-4-3			
Resistance to electrostatic discharge	6 kV on contact (on metal parts) conforming to IEC 61000-4-2			
·	8 kV in free air (in insulating parts) conforming to IEC 61000-4-2			
Electromagnetic emission	Class B conforming to IEC 55011			
RoHS EUR status	Compliant			
RoHS EUR conformity date	0727			

Dimensions of Pilot Lights

Integral LED

XB4 BVB•, XB4 BVG•, XB4 BVM•




e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

b: 30 mm / 1.18 in. c: 46.5 mm / 1.83 in.

Direct Supply

XB4 BV6•





e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

b: 30 mm / 1.18 in. c: 46.5 mm / 1.83 in.

Via Integral Transformer

XB4 BV3•, XB4 BV4•, XB4 BV5•





e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

	a in mm	a in in.	b in mm	b in in.	c in mm	c in in.
XB4 BV••	66	2.60	30	1.18	46.5	1.83
XB4 BV5B•	89.6	3.53	40	1.57		

XB4BVB3

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Connection by Faston Connectors Printed Circuit Board (2) (5) (3) (6)

- (1) (2) (3) Diameter on finished panel or support
- 40 mm min. / 1.57 in. min.
- 30 mm min. / 1.18 in. min.
- Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0$ $^{+0.4}$ / 0.88 in. $_0$ $^{+0.016}$)
- (5) (6) 45 mm min. / 1.78 in. min.
- 32 mm min. / 1.26 in. min.