

FEATURES

- 1. High current transfer ratio.
- 2. Opaque type, mini-flat package.
- 3. Subminiature type (The volume is smaller than that of our conventional DIP type by as far as 30%).
- 4. Isolation voltage between input and output Viso: 3750 Vrms.
- 5. Employs double transfer mold technology.
- 6. Recognized by UL and CUL, file NO. E225308.
- 7.Packge: 1000Pcs / Reel.
- 8. Rohs compliant.

APPLICATIONS

- 1. Hybrid substrates that require high density mounting.
- 2. Programmable controllers.

*PACKAGE DIMENSIONS (UNIT:mm) SMD Type

Internal connection diagram $2.54(.1)\pm0.25$ 3 $4(.173)\pm0.$ Aonde mark 355 1 Anode 3 Emitter (2) Cathode (4) Collector 10 2 $0.4(.016)\pm0.1$ $3.6(.142)\pm0.3$ $5.3(.209)\pm0.3$ $.008)\pm0.05$ $.004)\pm0.1$ 0.5(.02) +8

UNIT: MM[INCH]

TOLERANCE: $\pm 0.5 [\pm 0.02]$ UNLESS OTHERWISE NOTED.



*Absolute Maximum Ratings (TA=25°C)

	Parameter	Symbol	Rating	Unit	
Input	Forward current	lF	50	mA	
	Reverse voltage	VR	6	V	
	Power dissipation	Р	70	mW	
Output	Collector-emitter voltage	VCEO	35	V	
	Emitter-collector voltage	VECO	6	٧	
	Collector current	Ic	80	mA	
	Collector power dissipation	Pc	150	mW	
Total power dis	sipation	Ptot	Ptot 170 mW		
*1 Isolation volt	age	Viso	3750	Vrms	
Operating temperature		Topr	-30 to +100	°C	
Storage tempe	rature	Tstg	-40 to +125	+125 °C	
*2 Soldering ter	mperature	Tsol	ol 260		

 $^{^{*1}}$ 40 to 60% RH,AC for 1 minute.

*Electro-optical Characteristics

	Paramete	er	Symbol	Conditions	Min.	Тур.	Max.	Unit
Input	Forward voltage		VF	IF=20mA	-	1.2	1.4	V
	Peak forward voltage		VFM	IFM=0.5A	-	-	3.0	V
	Reverse current		lR	VR=4V	-	-	10	uA
Output	Collector dark current		ICEO	Vce=10V,IF=0	-	-	10-6	Α
	Collector-emitter breakdown voltage		BVceo	Ic=0.1mA,IF=0	35	-	-	V
	Emitter-collector breakdown voltage		BVeco	IE=10uA,IF=0	6	-	-	٧
Transfer Charac- teristics	Current transfer ratio		CTR	IF=1mA,VCE=2V	600	1600	7500	%
	Collector-emitter saturation voltage		VCE(sat)	IF=20mA,Ic=1mA	-	0.8	1.0	V
	Response time	Rise time	Tr	VcE=2V,lc=2mA RL=100Ω	-	60	300	uS
		Fall time	Tf		-	53	250	uS

SPEC NO: DSAD2839 REV NO: V.5 DATE:NOV/22/2004 PAGE: 2 OF 6 APPROVED: J. Lu CHECKED: Tracy Deng DRAWN: Y.CHENG

 $^{^{\}star_2}$ For 10 seconds.

Kingbright

Fig. 1 Current Transfer vs. Forward Current




Fig. 3 Collector Current vs.
Collector-emitter Voltage




Fig. 5 Collector-emitter Saturation Voltage vs. Ambient Temperature





Fig. 7 Collector-emitter Saturation Voltage vs. Forward Current



KB355NT

Fig. 2 Forward Current vs. Forward voltage




Fig. 4 Forward Current vs.

Ambient Temperature




Fig. 6 Response Time vs. Load Resistance





Fig. 8 Collector Dark Current vs.
Ambient Temperature




PAGE: 4 OF 6



KB355NT

Test Circuit for Response Time



* NOTES ON HANDLING

1.Recommended soldering conditions (Dip soldering)

(1) Dip soldering

Temperature 260 or below (molten solder temperature)

Time Less than 10 seconds.

Cycle One cycle allowed to be dipped in solder including plastic nold portion.

Flux Rosin flux containing small amount of chlorine

(The flux with a maximum chlorine content of 0.2 Wt % is recommended.)

(2) Cautions

Fluxes

Avoid removing the residual flux with freon-based and chlorine-based cleaning solvent.

2. Cautions regarding noise

Be aware that power is suddenly into the component any surge current may cause damage happen, even if the voltage is within the absolute maximum ratings.

SPEC NO: DSAD2839 REV NO: V.5 DATE:NOV/22/2004 APPROVED: J. Lu CHECKED: Tracy Deng DRAWN: Y.CHENG



NOTES ON HANDLING

1.Recommended soldering conditions

(1).Infrared reflow soldering

Peak reflow temperature
 235 ° C or below(package surface temperature)


• Time of temperature higher than 210 ° C 30 seconds or less

Number or reflows Three

• Flux

Rosin flux containing small amount of chlorine(The flux with a maximum chlorine content of 0.2Wt % is recommended.)

Recommended Temperature Profile of infrared Reflow



CAUTION

Within this device there exists GaAs (Gallium Arsenide) material which is a harmful substance if ingested.

GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them.

RESTRICTIONS ON PRODUCT USE


- The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version. Not all devices / types available in every country.
- We are mention about our product quality stablity, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing KINGBRIGHT products, to observe standards of safety, and to a avoid situations in which a malfunction or failure of a KINGBRIGHT product could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that KINGBRIGHT products are used within specified operating ranges as set forth in the most recent products specifications.


SPEC NO: DSAD2839 REV NO: V.5 DATE:NOV/22/2004 PAGE: 5 OF 6 APPROVED: J. Lu CHECKED: Tracy Deng DRAWN: Y.CHENG




Outline and Dimension(Tape)

(Units: mm)






Tape Direction



Outline and Dimension(Reel)



Packing:1000pcs/reel