

Vishay Draloric

RoHSCOMPLIANT

HALOGEN

FREE GREEN

Cemented Wirewound Resistors with Lugs



The ZWS series, with a completely welded construction, is the perfect choice for high continuous power dissipation up to 250 W with the option for adjustable (ZWS E) and non-inductive (ZWS Ni) types. With their extremely high pulse power capability, they are the ideal choice as inrush current limiters. Typical applications include but are not limited to drive systems, power supplies, frequency inverters, AC and DC filters, and as snubber resistors. For a given application, requirements of ohmic value, rated power, peak voltage, pulse shape, pulse duration, termination style, and environmental conditions may be submitted to recommend the most suitable product.

FEATURES

- Lugs with various termination styles suitable for soldering or bolt connection
- Excellent pulse load capability
- Adjustable type (E) available
- Non inductive type (Ni) available
- Non-flammable coating according to UL94-V0
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Inrush current limiter
- · Capacitor charge / discharge
- Snubber resistor
- Brake resistor
- Filter resistor

TECHNICAL SPECIFICATION											
TYPE / VARIANT	RATED DISSIPATION P ₄₀	RESISTANCE RANGE ⁽¹⁾ TCR -10 ppm/K to -80 ppm/K WM50	RESISTANCE RANGE (1) TCR +100 ppm/K to +180 ppm/K WM110	RESISTANCE TOLERANCE	OPERATING VOLTAGE (2) U _{max.}						
ZWS 6	6 W	0.82 Ω to 5.1 kΩ	1.8 Ω to 13 kΩ	± 5 %, ± 10 %	250 V						
2W30	O VV	2.7 Ω to 5.1 k Ω	-	± 2 %	150 V						
ZWS 6 E	6 W	0.82 Ω to 130 Ω	1.8 Ω to 4.7 k Ω	± 5 %, ± 10 %	150 V						
ZWS 6 Ni	6 W	0.15 Ω to 910 Ω	$0.33~\Omega$ to $2.4~\text{k}\Omega$	± 10 %	100 V						
ZWS O INI	O VV	1.0 Ω to 910 Ω	2.0 Ω to 2.4 k Ω	± 5 %	100 V						
ZWS 8	8 W	0.68 Ω to 7.5 k Ω	1.8 Ω to 20 k Ω	± 5 %, ± 10 %	400 V						
ZW5 6	O VV	$3.3~\Omega$ to $7.5~\text{k}\Omega$	-	± 2 %	200 V						
ZWS 8 E	8 W	0.62 Ω to 200 Ω	1.8 Ω to 6.8 k Ω	± 5 %, ± 10 %	200 V						
ZWS 8 Ni	8 W	0.24 Ω to 1.3 k Ω	$0.56~\Omega$ to $3.6~\text{k}\Omega$	± 10 %	150 V						
2003 6 INI		1.0 Ω to 1.3 k Ω	$2.0~\Omega$ to $3.6~\text{k}\Omega$	± 5 %	150 V						
ZWS 12	12 W	0.62 Ω to 10 kΩ 1.8 Ω to		± 5 %, ± 10 %	550 V						
ZW3 12	1∠ VV	3.0 Ω to 10 kΩ -		± 2 %	300 V						
ZWS 12 E	12 W	0.56 Ω to 270 Ω	1.8 Ω to 9.1 kΩ	± 5 %, ± 10 %	300 V						
7WC 40 N:	10.14	0.33 Ω to 1.8 k Ω	0.75 Ω to 5.1 kΩ	± 10 %	000.1/						
ZWS 12 Ni	12 W	1.0 Ω to 1.8 kΩ	2.0 Ω to 5.1 k Ω	± 5 %	200 V						
7)NC 1E	15 \\\	0.68 Ω to 12 kΩ	2.2 Ω to 33 k Ω	± 5 %, ± 10 %	700 V						
ZWS 15	15 W	2.2 Ω to 12 kΩ	-	± 2 %	400 V						
ZWS 15 E	15 W	0.68 Ω to 330 Ω	2.2 Ω to 11 kΩ	± 5 %, ± 10 %	400 V						
7WC 45 N:	15 \\\	$0.39~\Omega$ to $2.2~\text{k}\Omega$	0.82 Ω to 6.2 kΩ	± 10 %	200.1/						
ZWS 15 Ni	15 W	1.0 Ω to 2.2 kΩ	2.0 Ω to 6.2 kΩ	± 5 %	300 V						

Revision: 19-Jul-16 1 Document Number: 21010



Vishay Draloric

TECHNICAL SPECIFICATION										
TYPE / DISSIPATION P40		RESISTANCE RANGE (1) TCR -10 ppm/K to -80 ppm/K WM50	RESISTANCE RANGE ⁽¹⁾ TCR +100 ppm/K to +180 ppm/K WM110	RESISTANCE TOLERANCE	OPERATING VOLTAGE ⁽²⁾ U _{max.}					
7140.00	0.62 Ω to 16 kΩ		1.3 Ω to 43 kΩ	± 5 %, ± 10 %	900 V					
ZWS 20	20 W	2.7 Ω to 16 k Ω	-	± 2 %	550 V					
ZWS 20 E	20 W	0.62 Ω to 430 Ω	1.3 Ω to 15 kΩ	± 5 %, ± 10 %	500 V					
7140 00 NI:	00.144	$0.47~\Omega$ to $2.7~\text{k}\Omega$	1.1 Ω to 8.2 kΩ	±10 %	400.14					
ZWS 20 Ni	20 W	1.0 Ω to 2.7 kΩ	2.0 Ω to 8.2 kΩ	± 5 %	400 V					
7140.05	05.144	1.1 Ω to 30 kΩ	2.7 Ω to 82 k Ω	± 5 %, ± 10 %	1500 V					
ZWS 35	35 W	1.3 Ω to 30 kΩ	-	± 2 %	1000 V					
ZWS 35 E	35 W	1.1 Ω to 750 Ω	$2.7~\Omega$ to $27~k\Omega$	± 5 %, ± 10 %	950 V					
ZWS 35 Ni	35 W	0.91 Ω to 5.1 kΩ	2.0 Ω to 15 kΩ	± 5 %, ± 10 %	700 V					
		1.3 Ω to 33 kΩ	$3.0~\Omega$ to $91~k\Omega$	± 5 %, ± 10 %	2100 V					
ZWS 50	50 W	2.2 Ω to 33 k Ω	-	± 2 %	1250 V					
ZWS 50 E	50 W	1.3 Ω to 910 Ω	$3.0~\Omega$ to $33~k\Omega$	± 5 %, ± 10 %	1250 V					
ZWS 50 Ni	50 W	1.1 Ω to 6.2 kΩ	$2.4~\Omega$ to $16~\text{k}\Omega$	± 5 %, ± 10 %	850 V					
ZWS 100 100 W		6.2 Ω to 200 kΩ	± 5 %, ± 10 %	4450 V						
	100 W	$2.7~\Omega$ to $68~\text{k}\Omega$	-	± 2 %	2600 V					
ZWS 100 E	100 W	2.7 Ω to 1.8 k Ω	$6.2~\Omega$ to $68~k\Omega$	± 5 %, ± 10 %	2600 V					
ZWS 100 Ni	100 W	2.2 Ω to 13 kΩ	$4.7~\Omega$ to $33~k\Omega$	± 5 %, ± 10 %	1800 V					
7140 450	450.14	470140010	11.0 Ω to 360 k Ω	± 5 %, ± 10 %	7300 V					
ZWS 150	150 W	4.7 Ω to 130 k Ω	-	± 2 %	4400 V					
ZWS 150 E	150 W	$4.7~\Omega$ to $3.3~\text{k}\Omega$	11.0 Ω to 120 kΩ	± 5 %, ± 10 %	4200 V					
ZWS 150 Ni	150 W	3.9 Ω to 22 k Ω	9.1 Ω to 62 k Ω	± 5 %, ± 10 %	3000 V					
7140.050	050.14	0.001.0001.0	20.0 Ω to 620 k Ω	± 5 %, ± 10 %	12400 V					
ZWS 250	250 W	8.2 Ω to 220 k Ω	-	± 2 %	7400 V					
ZWS 250 E	250 W	8.2 Ω to 6.2 k Ω	20.0 Ω to 220 k Ω	± 5 %, ± 10 %	7400 V					
ZWS 250 Ni	250 W	6.8 Ω to 39 kΩ	15.0 Ω to 110 kΩ	± 5 %, ± 10 %	5200 V					
7140 00/100	75.11	2.4 Ω to 62 kΩ	5.1 Ω to 180 kΩ	± 5 %, ± 10 %	3650 V					
ZWS 30/100	75 W	3.0 Ω to 62 k Ω	-	± 2 %	2150 V					
ZWS 30/100 E	75 W	2.4 Ω to 1.6 kΩ	5.1 Ω to 56 kΩ	± 5 %, ± 10 %	2000 V					
ZWS 30/100 Ni	75 W	2.0 Ω to 11 kΩ	4.3 Ω to 30 kΩ	± 5 %, ± 10 %	1500 V					
			7.5 Ω to 240 kΩ	± 5 %, ± 10 %	5100 V					
ZWS 30/133	110 W	$3.3~\Omega$ to $91~k\Omega$	-	± 2 %	3150 V					
ZWS 30/133 E	110 W	3.3 Ω to 2.4 kΩ	7.5 Ω to 82 kΩ	± 5 %, ± 10 %	3000 V					
ZWS 30/133 Ni	110 W	2.7 Ω to 16 kΩ	6.2 Ω to 43 kΩ	± 5 %, ± 10 %	2150 V					

Notes

[•] The operating temperature range for these resistors is from -55 °C up to 250 °C.

⁽¹⁾ Resistance values are to be selected for \pm 10 % from the E12 series, and for \pm 5 % and \pm 2 % from the E24 series.

⁽²⁾ Depending on the resistance value, limited by $\sqrt{P \times R}$




Vishay Draloric

TERMINALS					
	SL	ss	SB	SSB	FST
	- e	- i			b → e
TYPE / VARIANT	Lug for soldering	Screw terminal	Terminal with 2 screws, one for electrical, and one for mechanical connection	Terminal with bolt and 2 hexnuts	Fast on terminal with 6.3 mm x 0.8 mm DIN 46244
ZWS 6 ZWS 6 E ZWS 6 Ni	e = 1.5 mm	-			
ZWS 8 ZWS 8 E ZWS 8 Ni					
ZWS 12 ZWS 12 E ZWS 12 Ni			-		-
ZWS 15 ZWS 15 E ZWS 15 Ni	e = 2.0 mm	e = M3 x 16		-	
ZWS 20 ZWS 20 E ZWS 20 Ni			a M2 v 16		
ZWS 35 ZWS 35 E ZWS 35 Ni			e = M3 x 16		
ZWS 50 ZWS 50 E ZWS 50 Ni					
ZWS 100 ZWS 100 E ZWS 100 Ni					e = 1.65 mm
ZWS 150 ZWS 150 E ZWS 150 Ni		0 - M4 × 00	0 - M4 × 00	o = M4 × 20	b = 6.3 mm
ZWS 250 ZWS 250 E ZWS 250 Ni	-	e = M4 x 20	e = M4 x 20	e = M4 x 20	
ZWS 30/100 ZWS 30/100 E ZWS 30/100 Ni					
ZWS 30/133 ZWS 30/133 E ZWS 30/133 Ni					



Vishay Draloric

PACKAGING											
TYPE	PACKAGING QUANTITY		FORMAT	DIMENSION OF PACKAGE							
All	LX	Variable	Bulk, separately packed with paper	Box size selection according to quantity and product size							



Notes

- The products can be ordered using either the PRODUCT DESCRIPTION or the PART NUMBER.
- (1) For special windings or the non-inductive (ZWS Ni) versions, please contact: www1resistors@vishay.com.



Vishay Draloric

DESCRIPTION

The rugged design of cemented wirewound resistors enable them to withstand extreme high pulses and makes them well suited for use in high power / high current applications. Production is strictly controlled and follows an extensive set of instructions established for reproducibility. The winding is done with specific materials on a specially developed fine ceramic body (Al₂O₃). With different diameters and turn spacings, a large ohmic value range can be offered. The ceramic used meets the highest requirements against mechanical resistance, thermal shock shocks, dielectric strength, and insulation resistance at high temperatures. The cement coating is fired layer by layer several times at high temperatures. The resulting cement coating is resistant to the cleaning solvents specified in IEC 60115-1 ⁽¹⁾.

The resistors are marked with type, resistance, and tolerance.

Product quality is verified by testing procedures, performed on all individual resistors.

The ZWS series meet single lot / date code packaging requirements.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein (2)
- The Global Automotive Declarable Substance List (GADSL) (3)
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) (4) for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

ASSEMBLY

The resistors are available with lug style terminals (SL style) for soldering, multiple screw terminal options (SS style, SB style, or SSB style) for mechanical and electrical fixing, or fast plug terminals (FST style) for assembly / disassembly processes. The terminals of the resistors are completely lead (Pb)-free. The special tin plating used provides compatibility with lead (Pb)-free and lead-containing soldering processes.

3D-Models are available on request, please inquire at ww1resistors@vishay.com.

Different mounting accessories are available, see the datasheet: www.vishay.com/doc?21015.

The slider of the adjustable type should be only moved after removal of voltage and sufficient loosening of the screw.

APPLICATION INFORMATION

The power dissipation of the resistor generates a temperature rise with respect to the ambient. The permissible dissipation is derated for temperatures above 40°C, as shown in the derating diagram, in order to avoid overheating of the resistor. The heat dissipated from the resistor may affect adjacent components, hence proper clearance will be required in order to avoid overheating.

All materials used are non-flammable and inorganic according to UL 94-V0.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

RELATED PRODUCTS

In higher continuous power applications and more demanding environmental conditions the vitreous coated alternative, like the GWS series might be suitable, see the datasheet:

"Vitreous Wirewound Resistors with Lugs" www.vishay.com/doc?21003


For low ohmic values and rated dissipation up to 500 W, there is the cemented coated ZBS series, see the datasheet:


"Cemented Wirewound Resistors with Corrugated Ribbon" www.vishay.com/doc?21011

Notes

- (1) Other cleaning solvents with aggressive chemicals should be evaluated in actual cleaning process for their suitability.
- (2) The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at http://std.iec.ch/iec62474.
- (3) The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council, and available at www.gadsl.org.
- (4) The SVHC list is maintained by the European Chemical Agency (ECHA) and available at http://echa.europa.eu/candidate-list-table.

Vishay Draloric





ZWS 15

ZWS 15 E


ZWS 15 Ni


SL

SS

 11.8 ± 0.8

Vishay Draloric





 50.0 ± 2.0

 51.0 ± 2.0

 62.0 ± 2.0

4.0

5.0

5.0

5.0

19.0

11.5

5.5

5.5

2.0

M3 x 12

2.8

2.8

4.0

3.0


12.5




Vishay Draloric

DIMENSIONS AND MASS for ZWS 20, ZWS 35, and ZWS 50


PRODUCTS WITH SL TERMINALS







ADJUSTABLE LUGS

ZWS 20 E ... ZWS 50 E



PRODUCTS WITH SS AND SSB TERMINALS







CORE SECTION

ZWS 20 ... ZWS 35



PRODUCTS WITH SB TERMINALS






CORE SECTION

ZWS 50



PRODUCTS WITH FST TERMINALS






TYPE / VARIANT	TERMINAL	D (mm)	L (mm)	a (mm)	b (mm)	b ₁ (mm)	c (mm)	d (mm)	e (mm)	e ₁ (mm)	k (mm)	MASS (g)
	SL		62.0 ± 2.0	50.0 ± 2.0	4.0	5.0	20.5	5.5	2.0	3.2	4.0	- 25.0
ZWS 20 ZWS 20 E	SS	14.8 ± 0.8		51.0 ± 2.0	5.0	5.0	13.0	5.5	M3 x 12	3.2	3.0	
ZWS 20 Ni	SB	14.0 ± 0.0		51.0 ± 2.0	5.0	5.0	23.0	5.5	M3 x 12	3.2	3.0	
	FST			48.0 ± 2.0	6.3	5.0	23.5	5.5	1.65	3.2	3.0	
	SL	- 14.8 ± 0.8	100.0 ± 2.0	86.0 ± 2.0	4.0	5.0	20.5	5.5	2.0	3.2	5.0	33.0
ZWS 35 ZWS 35 E	SS			87.0 ± 2.0	5.0	5.0	13.0	5.5	M3 x 12	3.2	4.0	
ZWS 35 E ZWS 35 Ni	SB			87.0 ± 2.0	5.0	5.0	23.0	5.5	M3 x 12	3.2	4.0	
	FST			84.0 ± 2.0	6.3	5.0	23.5	5.5	1.65	3.2	4.0	
	SS	22.3 ± 1.3	100.0 ± 2.0	72.0 ± 2.0	8.0	5.0	18.5	10.0	M4 x 16	3.2	10.0	80.0
ZWS 50 ZWS 50 E ZWS 50 Ni	SSB			72.0 ± 2.0	8.0	5.0	18.5	10.0	M4 x 16	3.2	10.0	
	SB	22.0 ± 1.0		72.0 ± 2.0	8.0	5.0	29.5	10.0	M4 x 16	3.2	10.0	
	FST			72.0 ± 2.0	6.3	5.0	27.0	10.0	1.65	3.2	10.0	




Vishay Draloric

DIMENSIONS AND MASS for ZWS 100, ZWS 150, and ZWS 250


PRODUCTS WITH SS AND SSB TERMINALS







ADJUSTABLE LUGS

ZWS 100 E...ZWS 250 E




PRODUCTS WITH SB TERMINALS






CORE SECTION



PRODUCTS WITH FST TERMINALS





CORE SECTION

ZWS 250




←──── a ───── b → ←												
TYPE / VARIANT	TERMINAL	D (mm)	L (mm)	a (mm)	b (mm)	b ₁ (mm)	c (mm)	d (mm)	e (mm)	e ₁ (mm)	k (mm)	MASS (g)
	SS				8.0	5.0	18.5	10.0	M4 x 16	3.2	10.5	113.0
ZWS 100 ZWS 100 E	SSB	22.3 ± 1.3	165.0 . 2.0	126.0 . 2.0	8.0	5.0	18.5	10.0	M4 x 18	3.2	10.5	
ZWS 100 E	SB	22.3 ± 1.3	165.0 ± 2.0	136.0 ± 2.0	8.0	5.0	29.5	10.0	M4 x 16	3.2	10.5	
	FST				6.3	5.0	27.0	10.0	1.65	3.2	10.5	
	SS	- 22.3 ± 1.3	265.0 ± 4.0	235.0 ± 2.0	8.0	5.0	18.5	10.0	M4 x 16	3.2	10.5	194.0
ZWS 150 ZWS 150 E	SSB				8.0	5.0	18.5	10.0	M4 x 18	3.2	10.5	
ZWS 150 E	SB				8.0	5.0	29.5	10.0	M4 x 16	3.2	10.5	
	FST				6.3	5.0	27.0	10.0	1.65	3.2	10.5	
	SS	00.5 . 4.5		280.0 ± 2.0	8.0	8.0	23.5	20.0	M4 x 16	4.2	21.0	
ZWS 250	SSB		330.0 ± 5.0		8.0	8.0	23.5	20.0	M4 x 18	4.2	21.0	375.0
ZWS 250 E ZWS 250 Ni	SB	32.5 ± 1.5			8.0	8.0	35.0	20.0	M4 x 16	4.2	21.0	3/3.0
	FST				6.3	8.0	31.5	20.0	1.65	4.2	21.0	




Vishay Draloric

DIMENSIONS AND MASS for ZWS 30/100, and ZWS 30/133


PRODUCTS WITH SS AND SSB TERMINALS







ADJUSTABLE LUGS

ZWS 30/100 E; ZWS 30/133 E



PRODUCTS WITH SB TERMINALS






CORE SECTION

ZWS 30/100 E; ZWS 30/133 E



PRODUCTS WITH FST TERMINALS





TYPE / VARIANT	TERMINAL	D (mm)	L (mm)	a (mm)	b (mm)	b ₁ (mm)	c (mm)	d (mm)	e (mm)	e ₁ (mm)	k (mm)	MASS (g)
ZWS 30/100 ZWS 30/100 E ZWS 30/100 Ni	SS		100.0 ± 2.5	85.0 ± 2.0	8.0	8.0	23.5		M4 x 16	4.2	3.5	
	SSB	32.5 ± 1.5			8.0	8.0	23.5	14.0	M4 x 18	4.2	3.5	167.0
	SB	32.5 ± 1.5			8.0	8.0	35.0	14.0	M4 x 16	4.2	3.5	
	FST				6.3	8.0	31.5		1.65	4.2	3.5	
ZWS 30/133 ZWS 30/133 E ZWS 30/133 Ni	SS	32.5 ± 1.5	133.0 ± 3.0	118.0 ± 2.0	8.0	8.0	23.5		M4 x 16	4.2	3.5	212.0
	SSB				8.0	8.0	23.5	14.0	M4 x 18	4.2	3.5	
	SB				8.0	8.0	35.0	14.0	M4 x 16	4.2	3.5	
	FST				6.3	8.0	31.5		1.65	4.2	3.5	



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.