





Self Adhesive Clips Types TY8H1S, RA, RB, SAC

Features and Benefits




Wires, cables or hoses can be quickly and easily installed using these one piece fixing clips.

Application


These clips are ideal for use in applications which are difficult to access, or for areas where a self adhesive is the only possible fixing method (for example where fixing 'holes' would be unacceptable).



TY8H1S Self Adhesive Clip



RA3-18 Self Adhesive Clip



RB5-8 Self Adhesive Clip

For more information on the types of adhesive used please turn to page 120.

Material Data


Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2 (excluding adhesive)



Technical Table

Article-No.	Type	Length (L)	Width (W)	Width (W2)	Height (H)	Fixing Hole Ø (FH)	Bundle Ø max.	Material	Colour	Adhesive
151-22819	TY8H1	26.0	23.0	-	6.5	3.2	-	PA66	Natural (NA)	-
151-12819	TY8H1S	26.0	23.0	-	6.5	3.2	-	PA66	Natural (NA)	Acrylate
151-13018	RA3	13.0	13.0	5.0	5.0	-	3.0	PA66	Natural (NA)	Synthetic rubber
151-13019	RA6	19.0	19.0	5.0	9.0	-	6.0	PA66	Natural (NA)	Synthetic rubber
151-13020	RA9	19.0	19.0	7.5	12.5	-	9.0	PA66	Natural (NA)	Synthetic rubber
151-13021	RA13	25.0	25.0	10.0	16.5	-	13.0	PA66	Natural (NA)	Synthetic rubber
151-13119	RA18	28.5	28.5	10.0	23.0	-	18.0	PA66	Natural (NA)	Synthetic rubber
151-14059	RB5	19.0	19.0	9.7	6.0	-	5.0	PA66	Natural (NA)	Synthetic rubber
151-14000	RB5	19.0	19.0	9.7	6.0	-	5.0	PA66	Black (BK)	Synthetic rubber
151-13606	RB8	25.0	25.0	12.7	11.5	-	8.0	PA66	Natural (NA)	Synthetic rubber
151-13601	RB8	25.0	25.0	12.7	11.5	-	8.0	PA66	Black (BK)	Synthetic rubber
151-00505	RB14	33.2	27.4	23	16.0	-	14.0	PA66	Natural (NA)	Synthetic rubber
151-00502	RB14	33.2	27.4	23	16.0	-	14.0	PA66	Black (BK)	Synthetic rubber

All dimensions in mm. Subject to technical changes.



SAC-Series Self Adhesive Clip



Malleable tongue allows for a variety of sizes per clip.

For more information on the types of adhesive used please turn to page 120.

Material Data


Material	Electroplated mild steel (ST)
Adhesive	Acrylate with base of polyethylene foam
Operating Temperature	-40 °C to +70 °C



Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Material	Colour	Adhesive
151-00033	SAC0	20.0	15.0	3.0	ST	White (WH)	Acrylate
151-00100	SAC1	32.0	22.0	4.0	ST	White (WH)	Acrylate
151-00200	SAC2	38.0	25.0	8.0	ST	White (WH)	Acrylate
151-00300	SAC3	44.0	33.0	12.0	ST	White (WH)	Acrylate
151-00400	SAC4	54.0	38.0	16.0	ST	White (WH)	Acrylate

All dimensions in mm. Subject to technical changes.



130100 Self Adhesive Clip

Material Data


Material	Polyvinylchloride (PVC)
Operating Temperature	-25 °C to +65 °C



Technical Table

Article-No.	Type	Length (L)	Width (W)	Height (H)	Material	Colour	Adhesive
154-01119	130100	25.0	25.0	9.1	PVC	White (WH)	Acrylate

All dimensions in mm. Subject to technical changes.



ASI-Clip Self Adhesive Clip

Material Data

Material	Polyamide 6.6 High Impact Modified (PA66HIR)
Operating Temperature	-40 °C to +80 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 HB (excluding adhesive)



Technical Table

Article-No.	Type	Length (L)	Width (W)	Height (H)	Fixing Hole Ø (FH)	Material	Colour	Adhesive
150-11294	ASI-Clip	25.0	20.0	11.7	3.3	PA66HIR	Natural (NA)	Acrylate

All dimensions in mm. Subject to technical changes.