Multi-function

AI: ON delay

DI: ON pulse

• 35 mm rail mounting

GI: Fixed pulse delayed

SW: Symmetrical recycling:



Features 87.01 87.02

Mono-function and multi-function timer range - 22.5 mm wide


87.01 - 1 Pole Multi-function and multi-voltage 87.02 - 2 Pole Multi-function and multi-voltage, (timed + instantaneous options) External time setting potentiometer option

- Wide supply range, (24...240)V AC / (24...48)V DC
- LED indicator

Contact specification

Approvals (according to type)

- Time setting from 0.05 seconds to 60 hours
- 35 mm rail (EN 50022) mounting





AI: ON delay

DI: ON pulse

- 1 pole
- 35 mm rail mounting

GI: Fixed pulse delayed


SW: Symmetrical recycling:

wiring diagram


(without signal START)



BE: Signal OFF delay CE: Signal ON and OFF Delay DE: Signal ON pulse **EE a:** Signal OFF pulse








wiring diagram wiring diagram (with signal START) (without signal START)



- - BE: Signal OFF delay
 - CE: Signal ON and OFF Delay
 - **DE:** Signal ON pulse **EE a:** Signal OFF pulse



wiring diagram (with signal START)

Contact configuration		1 CO (SPDT)	2 CO (DPDT)
Rated current/Maximum peak current A		8/30	8/30
Rated voltage/Maximum switching voltage V AC		250/400	250/400
Rated load AC1	VA	2,000	2,000
Rated load AC15 (230 V A	AC) VA	400	400
Single phase motor rating ([230 V AC) kW	0.185	0.185
Breaking capacity DC1: 30	/110/220 V A	8/0.5/0.2	8/0.5/0.2
Minimum switching load	mW(V/mA)	300 (10/5)	300 (10/5)
Standard contact material		AgCdO	AgCdO
Supply specification			
Nominal voltage (U _N)	V AC (50/60 Hz)	24240	24240
	V DC	2448	2448
Rated power AC/DC	VA (50 Hz)/W	5/0.5	5/0.5
Operating range	AC	(0.851.1)U _N	(0.851.1)U _N
	DC	(0.851.2)U _N	(0.851.2)U _N
Technical data			
Specified time range		See page 194	See page 194
Repeatability	%	± 2	± 2
Recovery time	ms	50	50
Minimum control impulse	ms	50	50
Setting accuracy-full range	%	± 5	± 5
Electrical life at rated load	in AC1 cycles	100·10³	100·10³
Ambient temperature range	°C	-20+60	-20+60
Protection category		IP 20	IP 20

CE

Œ

c(UL) us

(GL)



Features 87.11 87.31 87.21 Mono-function and multi-function timer range - 22.5 mm wide 87.11 - ON delay, multi-voltage 87.21 - ON pulse, multi-voltage 87.31 - Symmetrical recycling, multi-voltage • 1 Pole output contact · Wide supply range, (24...240)V AC / (24...48)V DC • LED indicator • Mono-function Mono-function • Mono-function • Time setting; • 35 mm rail mounting • 35 mm rail mounting • 35 mm rail mounting Types 87.11/21 - 0.05 seconds to 60 hours Type 87.31 - 0.5 seconds to 10 seconds DI: ON pulse AI: ON delay SW: Symmetrical recycling: ON start • 35 mm rail (EN 50022) mount 22.5 000 78.8 101 87.31 22.5 **®0** wiring diagram wiring diagram wiring diagram 101 (without signal START) (without signal START) (without signal START) 87.11 / 87.21 **Contact specification** Contact configuration 1 CO (SPDT) 1 CO (SPDT) 1 CO (SPDT) Rated current/Maximum peak current 8/30 8/30 8/30 Rated voltage/Maximum switching voltage V AC 250/400 250/400 250/400 Rated load AC1 VA 2,000 2,000 2,000 Rated load AC15 (230 V AC) VA 400 400 400 Single phase motor rating (230 V AC) kW 0.185 0.185 0.185 Breaking capacity DC1: 30/110/220 V Α 8/0.5/0.2 8/0.5/0.2 8/0.5/0.2 Minimum switching load mW(V/mA)300 (10/5) 300 (10/5) 300 (10/5) Standard contact material AgCdO AgCdO AgCdO Supply specification V AC (50/60 Hz) 24...240 24...240 24...240 Nominal voltage (U_N) 24...48 V DC 24...48 24...48 Rated power AC/DC VA (50 Hz)/W 5/0.5 5/0.5 5/0.5 Operating range AC $(0.85...1.1)U_N$ $(0.85...1.1)U_N$ (0.85...1.1)U_N DC (0.85...1.2)U_N (0.85...1.2)U_N (0.85...1.2)U_N Technical data Specified time range See page 194 See page 194 See page 194 Repeatability % ± 0.2 ± 0.2 ± 0.2 50 50 50 Recovery time ms Minimum control impulse ms ± 5 % ± 5 ± 5 Setting accuracy-full range Electrical life at rated load in AC1 cycles $100 \cdot 10^{3}$ $100 \cdot 10^{3}$ 100 · 103 °C -20...+60 -20...+60 Ambient temperature range -20...+60 Protection category IP 20 IP 20 IP 20 Approvals (according to type) CE Œ (GL) c(VL) us



Features 87.41 87.61 87.62

Mono-function and multi-function timer range - 22.5 mm wide

87.41 - Signal OFF delay, multi-voltage, 1 Pole 87.61 - True OFF delay, multi-voltage, 1 Pole

- 87.62 True OFF delay, multi-voltage, 2 Pole • Wide supply range;
- Type 87.41, (24...240)V AC/(24...48)V DC Types 87.61/62, (24...240)V AC/DC
- LED indicator
- Time setting range; Type 87.41 - 0.05 seconds to 60 hours Types 87.61/62 - 0.15 seconds to 10 minutes
- 35 mm rail (EN 50022) mount



BE: Signal OFF delay

- Mono-function
- 35 mm rail mounting





- Mono-function
- 1 pole
- 35 mm rail mounting




BI: True OFF delay


- Mono-function
- 2 pole
- 35 mm rail mounting







BI: True OFF delay



Contact specification Contact configuration Rated current/Maximum peak current

Protection category

Approvals (according to type)

1 CO (SPDT) 8/30 250 /400

wiring diagram

(with signal START)

wiring diagram (without signal START)

1 CO (SPDT)

5/10

IP 20

(GL)

Œ

c(UL) us

wiring diagram (without signal START)

2 CO (DPDT)

5/10

· ·			1	,
Rated voltage/Maximum swi	itching voltage V AC	250/400	250/400	250/400
Rated load AC1	VA	2,000	1,250	1,250
Rated load AC15 (230 V A	AC) VA	400	250	250
Single phase motor rating (230 V AC) kW	0.185	0.125	0.125
Breaking capacity DC1: 30,	/110/220 V A	8/0.5/0.2	5/0.5/0.2	5/0.5/0.2
Minimum switching load	mW(V/mA)	300 (10/5)	300 (10/5)	300 (10/5)
Standard contact material		AgCdO	AgCdO	AgCdO
Supply specification				
Nominal voltage (U_N)	V AC (50/60 Hz)	24240	24240	24240
	V DC	2448	24240	24240
Rated power AC/DC	VA (50 Hz)/W	5/0.5	1.5/1.5	1.5/1.5
Operating range	AC	(0.851.1)U _N	(0.851.1)U _N	(0.851.1)U _N
	DC	(0.851.2)U _N	(0.851.2)U _N	(0.851.2)U _N
Technical data				
Specified time range		See page 194	See page 194	See page 194
Repeatability	%	± 0.2	± 1	± 1
Recovery time	ms	50	50	50
Minimum control impulse	ms	50	300 ms (A1 - A2)	300 ms (A1 - A2)
Setting accuracy-full range	%	± 5	± 5	± 5
Electrical life at rated load i	in AC1 cycles	100 · 10³	100 · 10³	100 · 10³
Ambient temperature range	°C	-20+60	-20+60	-20+60

IP 20

CE

IP 20



Features 87.82 87.91

Mono-function and multi-function timer range - 22.5 mm wide

87.82 - Star-Delta timer, multi-voltage, star and delta output contacts

87.91 - Multi-function Recycling timer, 1 Pole

- Wide supply range, (24...240)V AC / (24...48)V DC
- LED indicator
- Time setting range; Type 87.82 - 0.05 minute to 1 minute Type 87.91 - 0.05 seconds to 60 hours
- 35 mm rail (EN 50022) mount



- Mono-function: Star delta
- 2 pole
- 35 mm rail mounting





- Multi-function recycling
- 35 mm rail mounting


SD:	Star	-	delta
-----	------	---	-------

- (ON starting) PI: Asymmetrical recycling (OFF starting)
- LI: Asymmetrical recycling LE: Signal asymmetrical recycling (ON starting) **PE:** Signal asymmetrical

recycling (OFF starting)







wiring diagram (without signal START)

2 NO (DPST-NO)

wiring diagram (without signal START)

wiring diagram (with signal START)

1 CO (SPDT)

	101
2.5→	96
	101
ification	

Contact configuration

		(=	(/
Rated current/Maximum pe	eak current A	8/30	8/30
Rated voltage/Maximum switching voltage V AC		250/400	250/400
Rated load AC1	VA	2,000	2,000
Rated load AC15 (230 V A	AC) VA	400	400
Single phase motor rating ([230 V AC) kW	0.185	0.185
Breaking capacity DC1: 30	/110/220 V A	8/0.5/0.2	8/0.5/0.2
Minimum switching load	mW(V/mA)	300 (10/5)	300 (10/5)
Standard contact material		AgCdO	AgCdO
Supply specification			
Nominal voltage (U _N)	V AC (50/60 Hz)	24240	24240
	V DC	2448	2448
Rated power AC/DC	VA (50 Hz)/W	5/0.5	5/0.5
Operating range	AC	(0.851.1)U _N	(0.851.1)U _N
	DC	(0.851.2)U _N	(0.851.2)U _N
Technical data			
Specified time range		See page 194	See page 194
Repeatability	%	± 0.2	± 0.2
Recovery time	ms	50	50
Minimum control impulse	ms	-	50
Setting accuracy-full range	%	± 5	± 5
Electrical life at rated load	in AC1 cycles	100 · 10³	100 · 10³
Ambient temperature range	°C	-20+60	-20+60
Protection category		IP 20	IP 20

CE

(GL)

Œ


c(UL) us

Approvals (according to type)



Ordering information

Example: 87 series multi-function timer 8 A, 1 CO (SPDT) contact, (24...240)V AC (50/60 Hz) and (24...48)V DC supply.



Technical data

lechnical data					
EMC specifications					
Type of test		Reference standard			
Electrostatic discharge	contact discharge	EN 61000-4-2	8 kV		
	air discharge	EN 61000-4-2	8 kV		
Radio-frequency electromagnetic field (80 ÷	1000 MHz)	EN 61000-4-3	10 V/m		
Fast transients (burst) (5-50 ns, 5 kHz) on Su	ipply terminals	EN 61000-4-4	6 kV		
Surges (1.2/50 µs) on Supply terminals	common mode	EN 61000-4-5	4 kV		
	differential mode	EN 61000-4-5	_		
Radio-frequency common mode (0.15 ÷ 80	MHz) on Supply terminals	EN 61000-4-6	10 V		
Radiated and conducted emission		EN 55022	class B		
Other data					
Signal control (B1)					
current absorption		1 mA			
max cable lenght (capacity o	of ≤ 10 nF / 100 m)	250 m			
Power lost to the environment		87.01/02/11/21/31/41/91	87.61/62	87.82	
without contact current	W	5	1.5	8	
with rated current	W	15	7	18	
Screw torque	1.2				
Max. wire size		solid cable	stranded cable		
	mm ²	1x4 / 2x2.5	1x4 / 2x1.5		
	AWG	1x12 / 2x14	1x12 / 2x16		



Time scales

	Function		S	S	s	min	min	min	h	h	h	h
Туре	Code	Function	0.05	0.15	0.5	0.05	0.15	0.5	0.05	0.15	0.5	3
			1	3	10	1	3	10	1	3	10	60
87.01/	Al	ON delay	•	•	•	•	•	•	•	•	•	•
87.02	BE	Signal OFF delay	•	•	•	•	•	•	•	•	•	•
	CE	Signal ON and OFF delay	•	•	•	•	•	•	•	•	•	•
	DI	ON pulse	•	•	•	•	•	•	•	•	•	•
	DE	Signal ON pulse	•	•	•	•	•	•	•	•	•	•
	EE a	Signal OFF pulse	•	•	•	•	•	•	•	•	•	•
	Gl	Fixed pulse (0,5s) delayed	•	•	•	•	•	•	•	•	•	•
	SW	Symmetrical recycling: ON start	•	•	•	•	•	•	•	•	•	•
87.11	Al	ON delay	•	•	•	•	•	•	•	•	•	•
87.21	DI	ON pulse	•	•	•	•	•	•	•	•	•	•
87.31	SW	Symmetrical recycling: ON start			•							
87.41	BE	Signal OFF delay	•	•	•	•	•	•	•	•	•	•
87.61/	ВІ	True OFF delay (power OFF)		0.15		0.07						
87.62				2.5	•	1.3		•				
87.82	SD	Star - delta (T _U = ~60 ms)				•						
87.91	LI	Asymmetrical recycling (ON start)	•	•	•	•	•	•	•	•	•	•
-	LE	Signal asymmetrical recycling (ON start)	•	•	•	•	•	•	•	•	•	•
-	PI	Asymmetrical recycling (OFF start)	•	•	•	•	•	•	•	•	•	•
-	PE	Signal asymmetrical recycling (OFF start)	•	•	•	•	•	•	•	•	•	•



Functions

- **U** = Supply Voltage
- S = Signal switch
- C = Output Contact

LED**	Timing	NO output	Tin	ned	Contacts Instantaneous*			
Green	ııııııg	contact	Open	Closed	DIP switch	Open	Closed	
	None	Open	15 - 18 25 -28*	15 - 16 25 - 26*		21 - 24*	21 - 22*	
	In progress	Open	15 - 18 25 - 28*	15 - 16 25 - 26*		21 - 22*	21 - 24*	
	In progress	Closed	15 - 16 25 - 26*	15 - 18 25 - 28*	Down		21 - 22*	21 - 24*
	None	Closed	15 - 16 25 - 26*	15 - 18 25 - 28*		21 - 22*	21 - 24*	


- 25-26-28 only for type 87.02 with 2 timed contacts. 21-22-24 only for type 87.02 with 1 instantaneous contact + 1 timed positioning the front DIP switch.
- ** The LED on types 87.61 and 87.62 is illuminated when supply voltage is supplied to timer.

Wiring diagram

Z1-Z2 and position the

Timer potentiometer on

"zero".




Without signal Start = Start via contact in supply line (A1). With signal Start = Start via contact into control terminal (B1). With DC supply, positive polarity has to be connected to B1 terminal (according to EN 60204-1).

and ON, until the Signal Switch is opened.

Functions

Wiring diagram



87