

Easy-to-use personal data protection.

Put a lock on your personal data with Kingston's DataTraveler® Locker+ G3. It secures receipts, bank statements and other sensitive documents with hardware encryption and password protection for a double layer of data security. The drive locks down and reformats after 10 failed login attempts, so users can rest assured that their data is safe even if the drive is lost or stolen.

Its USB 3.0 interface delivers fast speeds that are approximately eight times the speed of the previous generation, to secure files faster.

DataTraveler Locker+ G3 is easy for anyone to setup and easy to use, with no application installation required; all the software and security needed is built in. It works on both Windows systems and Macs so users can access files from multiple systems, without installing a program on every computer used.

It features a durable metal casing to protect the drive from drops, bumps and knocks plus its built-in key loop makes it convenient to take your data anywhere. The cap fits on the back of the drive so it won't get lost.

DataTraveler Locker+ G3 is covered by a five-year warranty, free technical support and legendary Kingston[®] reliability.

- > Easy to use
- > Hardware encryption
- > Superior password protection
- >Customisable with your logo and/or digital files



SPEED			
8GB	READ 80MB/s*	WRITE 10MB/s*	
16GB	READ 135MB/s*	WRITE 20MB/s*	
32-64GB	READ 135MB/s*	WRITE 40MB/s*	

*Based on Internal Testing

Features/specs on reverse >>



DataTraveler Locker+ G3

FEATURES/BENEFITS

- > Hardware encryption the best in personal security to keep your data safe
- > Superior password protection user sets a password to prevent unauthorised access
- > Easy to use no application installation required
- > Versatile works interchangeably between Mac OS X and Windows systems
- > Secure drive locks down and reformats after 10 invalid login attempts
- > Stylish durable metal casing with built-in key loop
- > Co-logo programme available¹ customise DataTraveler Locker+ G3 by adding your logo and/or digital files and instantly increase your organisation's brand recognition. The Customisation Programme offers unique packaging, custom profiles, colour adjustments, content loading and more, all with easy and convenient ordering

SPECIFICATIONS

- > Capacities² 8GB, 16GB, 32GB, 64GB
- > Speed³ USB 3.0 speed: 8GB 80MB/s read, 10MB/s write 16GB - 135MB/s read, 20MB/s write 32GB-64GB - 135MB/s read, 40MB/s write USB 2.0 speed: 8GB - 30MB/s read, 10MB/s write 16GB-64GB - 30MB/s read, 20MB/s write
- > Dimensions 60.56mm x 18.6 mm x 9.75 mm
- > Minimum system requirements

- USB 3.0 compliant and 2.0 compatible - Two (2) free consecutive drive letters required for use⁴

- > Operating temperature 0°C to 60°C
- > Storage temperature -20°C to 85°C
- > Warranty/support 5-year warranty with free technical support









COMPATIBILITY TABLE

Operating System	USB 3.0	USB 2.0
Windows® 8.1	√	√
Windows® 8	√	√
Windows® RT		
Windows® 7 (SP1)	√	√
Windows Vista® (SP2)	√	√
Windows XP (SP3)	√	√
Mac OS v.10.6.x – 10.9.x	√	√

KINGSTON PART NUMBERS

DTLPG3/8GB DTLPG3/16GB DTLPG3/32GB DTLPG3/64GB



- 1 Minimum guantity required. Performed at the factory.
- 2 Some of the listed capacity on a Flash storage device is used for formatting and other functions and is thus not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide at kingston.com/flashguide.

3 Speed may vary due to host hardware, software and usage.

- 4 First free drive letters after physical devices such as system partition, optical drives etc.
- THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2014 Kingston Technology Europe Co LLP and Kingston Digital Europe Co LLP, Kingston Court, Brooklands Close, Sunbury-on-Thames, Middlesex, TW16 7EP, England. Tel: +44 (0) 1932 738888 Fax: +44 (0) 1932 785469. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-275EN

