# 1.5 GHz Active Probe

### TAP1500 Datasheet



TAP1500 Single-ended Active FET Probe provides excellent high-speed electrical and mechanical performance required for today's digital system designs.

#### **Key features**

- Outstanding electrical performance
  - ≥1.5 GHz probe bandwidth
  - <267 ps rise time</p>
  - ≤1 pF input capacitance
  - 1 MΩ input resistance
  - -8 V to +8 V input dynamic range
  - -10 V to +10 VDC input offset range
- Versatile mechanical performance
  - Small compact probe head for probing small geometry circuit elements
  - DUT attachment accessories enable connection to SMDs as small as 0.5 mm pitch
  - Robust design for reliability

- Easy to use
  - Connects directly to oscilloscopes with the TekVPI<sup>™</sup> probe interface
  - Provides automatic units scaling and readout on the oscilloscope display
  - Easy access to oscilloscope probe menu display for probe status/ diagnostic information, and to control probe DC offset
  - Remote GPIB/USB probe control through the oscilloscope
- Applications
  - High-speed Digital Systems Design
  - Component Design and Characterization
  - Manufacturing Engineering and Test
  - Educational Research
  - Signals with Voltage Swings up to 16 V

# 1.5 GHz active probes for TekVPI<sup>™</sup> probe interface

- Lower DUT loading effects with ≤1 pF input capacitance and 1 MΩ input resistance
- Versatile DUT connectivity for attaching to small SMDs
- Preserves instrument bandwidth at the probe tip for ≤1 GHz oscilloscopes



#### **Datasheet**

## **Specifications**

All specifications apply to all models unless noted otherwise.

#### Warranted electrical characteristics

Attenuation (probe only) 10X ±2%

#### **Typical characteristics**

Bandwidth (probe only) ≥1.5 GHz Rise time (probe only) <267 ps Input capacitance <1 pF Input resistance  $1 M\Omega$ 

±8 V (16 V<sub>p-p</sub>) Linearity

Input offset range ±10 V

Maximum non-destructive input

voltage

±15 V (DC + peak AC)

Propagation delay 5.3 ns

#### **Physical characteristics**

Probe head size

Height 11.25 mm (0.44 in) Width 5.1 mm (0.20 in) 60.4 mm (2.39 in) Length

Other dimensions

Cable length 1300 mm (51 in)

Weight

Net 0.45 kg (1.0 lbs)

#### **Power requirements**

The probe is powered directly by oscilloscopes with the TekVPI probe interface.

#### EMC, environment, and safety

Temperature

Operating 0 °C to +50 ° (+32 °F to 122 °F) Nonoperating -40 ° C to +71 °C (-40 °F to 160 °F)

Humidity

Operating 5% to 95% Relative Humidity up to +30 °C (+86 °F) 5% to 85% Relative Humidity at 30 °C to +50 °C (+86 °F to +122 °F)

noncondensing

5% to 95% Relative Humidity up to +30 °C (+86 °F) 5% to 85% Relative Humidity at 30 °C to +75 °C (+86 °F to +167 °F) Nonoperating

noncondensing

Altitude

Operating Up to 4,400 m (14,436 ft) Nonoperating Up to 12,192 m (40,000 ft) Regulatory

Compliance labeling WEEE (European Union)

# Ordering information

#### **TAP1500 models**

**TAP1500** 1.5 GHz Active Probe

TAP1500X2 1.5 GHz Active Probe. Discounted two TAP1500 probe package

#### Standard accessories

#### Standard accessories

Description	Quantity with TAP1500 or TAP1500X2	Reorder part number	Reorder quantity
Low-inductance 1 in. Z-Ground lead	2 each	196-3438-xx	1 each (Pkg of 10)
3 in. Ground lead	2 each	196-3437-xx	1 each (Pkg of 2)
6 in. Ground lead	2 each	196-3436-xx	1 each (Pkg of 2)
Y-Lead adapter	2 each	196-3463-xx	1 each (Pkg of 2)
Color-coding clips	2 each of 5 colors	016-1315-xx	2 each of 5 colors
Solderable probe tips,	10 each	131-5638-xx	1 each (Pkg of 10)
Micro CKT test tip,	4 each	206-0569-xx	1 each
Right angle square pin adapter	2 each	214-4227-xx	1 each
100 mm square pin ground adapter	2 each	131-5777-xx	1 each
User manual <sup>1</sup>	1 each	071-1809-xx English or 071-1810-xx Japanese or 071-1811-xx Simplified Chinese	1 each
Nylon carrying case <sup>2</sup>	1 each	016-1952-xx	1 each

#### Recommended oscilloscopes

Oscilloscopes with the TekVPI  $^{\!\scriptscriptstyle\mathsf{TM}}$  probe interface.

#### Warranty

One-year warranty covering all parts and labor.

Manual language must be specified when ordering.

<sup>&</sup>lt;sup>2</sup> The TAP1500X2 does not include individual probe cases. Users who desire the individual probe case should order the TAP1500 probe.

#### Datasheet

## **Options**

#### **Manual options**

Opt. L5 Japanese manual

Opt. L7 Simplified Chinese manual

#### Service options

Opt. C3 Calibration Service 3 Years Opt. C5 Calibration Service 5 Years Opt. D1 Calibration Data Report

Opt. D3 Calibration Data Report 3 Years (with Opt. C3) Opt. D5 Calibration Data Report 5 Years (with Opt. C5) Opt. R3 Repair Service 3 Years (including warranty) Opt. R5 Repair Service 5 Years (including warranty) Opt. SILV600 Standard warranty extended to 5 years

#### Recommended accessories

013-0309-xx IC Micro-grabber, Qty 2

006-3415-xx Antistatic wrist strap

067-1707-xx TekVPI calibration fixture (for PV)

CE Marking Not Applicable.



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.

#### **Datasheet**

ASEAN / Australasia (65) 6356 3900
Belgium 00800 2255 4835\*
Central East Europe and the Baltics +41 52 675 3777
Finland +41 52 675 3777
Hong Kong 400 820 5835
Japan 81 (3) 6714 3010
Middle East, Asia, and North Africa +41 52 675 3777
People's Republic of China 400 820 5835
Republic of Korea 001 800 8255 2835
Spain 00800 2255 4835\*
Taiwan 886 (2) 2722 9622

\* European toll-free number. If not accessible, call: +41 52 675 3777

Austria 00800 2255 4835\*
Brazil +55 (11) 3759 7627
Central Europe & Greece +41 52 675 3777
France 00800 2255 4835\*
India 000 800 650 1835
Luxembourg +41 52 675 3777
The Netherlands 00800 2255 4835\*
Poland +41 52 675 3777
Russia & CIS +7 (495) 6647564
Sweden 00800 2255 4835\*
United Kingdom & Ireland 00800 2255 4835\*

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777 Canada 1 800 833 9200

Denmark +45 80 88 1401 Germany 00800 2255 4835\* Italy 00800 2255 4835\* Mexico. Central/South Ame

Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90

Norway 800 16098 Portugal 80 08 12370 South Africa +41 52 675 3777 Switzerland 00800 2255 4835\* USA 1 800 833 9200

Updated 10 April 2013

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tektronix.com.

Copyright ® Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

15 May 2013

51W-19043-6

www.tektronix.com

