

Comfort series 3.5 mm slot width






€ 0102

General specifications	
Switching element function	NAMUR NC
Slot width	3,5 mm
Depth of immersion (lateral)	5 7 typ. 6 mm
Installation	
Nominal ratings	
Nominal voltage U _o	8 V
Operating voltage UB	5 25 V
Switching frequency f	0 3000 Hz
Current consumption	
Measuring plate not detected	≥ 3 mA
Measuring plate detected	≤ 1 mA
Standard conformity	
EMC in accordance with	EN 60947-5-2
Standards	DIN EN 60947-5-6 (NAMUR) VDE 660 Part 209
Ambient conditions	
Ambient temperature	-50 100 °C (223 373 K)
Mechanical specifications	
Connection type	0.5 m, flexible lead LIY
Core cross-section	0.14 mm ²
Housing material	PBT
Protection degree	IP67
Note	adjustable stop
General information	
Use in the hazardous area	see instruction manuals
Category	1G; 2G; 3G; 1D; 3D

Connection type:





Copyright Pepperl+Fuchs, Printed in Germany

Pepperl+Fuchs Group • Tel.: Germany +49 621 776-0 • USA +1 330 4253555 • Singapore +65 67799091 • Internet http://www.pepperl-fuchs.com

1

ATEX 1G

Instruction

Device category 1G Directive conformity Standard conformity

CE symbol

Ex-identification EC-Type Examination Certificate Assigned type Effective internal capacitance Ci Effective internal inductance Li Cable length

Explosion group IIC General

Highest permissible ambient temperature

Protection from mechanical danger

Installation, Comissioning

Maintenance

Special conditions

www.pepperl-fuchs.com

Manual electrical apparatus for hazardous areas

BR for use in hazardous areas with gas, vapour and mist 94/9/EG EN 50014:1997; EN 50020:1994; EN 50284:1999 Ignition protection "Intrinsic safety" Use is restricted to the following stated conditions €0102

⟨€x⟩ II 1G EEx ia IIC T6 PTB 00 ATEX 2049 X SJ3.5-SN...

 \leq 30 nF ; a cable length of 10 m is considered.

 \leq 100 μH ; a cable length of 10 m is considered.

Dangerous electrostatic charges on the fixed connection cable must be taken into account for lengths equal to and exceeding the following values: 30 cm

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EU prototype test certificate must be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the $\ensuremath{\mathsf{EU}}$ prototype test certificate. Note: Use the temperature table for category 1 !!! The 20 % reduction in accordance with EN 1127-1 has already been applied to the temperature table for category 1.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related

apparatus and according to the proof of intrinsic safety.

The associated apparatus must satisfy the requirements of category ia. Due to the possible danger of ignition, which can arise due to faults and/or transient currents in the equipotential bonding system, galvanic isolation of the power supply and signal circuit is preferable. Associated apparatus without electrical isolation must only be used if the appropriate requirements of IEC 60079-14 are met.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

The sensor must not be mechanically damaged.

When used in the temperature range below -20°C the sensor should be protected from knocks by the provision of an additional housing.

ATEX 2G

Instruction

Device category 2G Directive conformity Standard conformity

CE symbol

Ex-identification

 $\begin{array}{l} \mbox{EC-Type Examination Certificate} \\ \mbox{Assigned type} \\ \mbox{Effective internal capacitance } C_i \\ \mbox{Effective internal inductance } L_i \\ \mbox{General} \end{array}$

Highest permissible ambient temperature

Installation, Comissioning

Maintenance

Special conditions Protection from mechanical danger

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist 94/9/EG EN 50014:1997, EN 50020:1994

Ignition protection "Intrinsic safety" Use is restricted to the following stated conditions $C \in 0.002$

⟨Ex⟩ II 1G EEx ia IIC T6

PTB 00 ATEX 2049 X SJ3.5-SN...

 \leq 30 nF ; a cable length of 10 m is considered.

 \leq 100 μH ; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EU prototype test certificate must be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the EU prototype test certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

The sensor must not be mechanically damaged.

When used in the temperature range below -20°C the sensor should be protected from knocks by the provision of an additional housing.

Copyright Pepperl+Fuchs, Printed in Germany

ATEX 3G (nA)

Instruction

Device category 3G (nA) Directive conformity Standard conformity

CE symbol

Ex-identification General

Installation, Comissioning

Maintenance

Special conditions Minimum series resistance RV

Maximum operating voltage UBmax

Maximum permissible ambient temperature T_{Umax}

at U_{Bmax}=9 V, R_V =562 Ω using an amplifier in accordance with EN 60947-5-6 Protection from mechanical danger Protection from UV light

Protection of the connection cable

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist 94/9/EG EN 50021:2000 Ignition protection category "n" Use is restricted to the following stated conditions $C \in 0.002$

⟨ II 3G EEx nA IIC T6 X

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual.

The data stated in the data sheet are restricted by this operating instruction! The special conditions must be observed!

Laws and/or regulations and standards governing the use or intended usage goal must be observed.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

A minimum series resistance RV is to be provided between the power supply voltage and the proximity switch in accordance with the following list. This can also be assured by using a switch amplifier.

The maximum permissible operating voltage UB max is restricted to the values in the following list. Tolerances are not permissible.

Values can be obtained from the following list, depending on the max. operating voltage Ub max and the minimum series resistance $\mathsf{Rv}.$

57 °C

57 °C

The sensor must not be exposed to **ANY FORM** of mechanical danger. The sensor and the connection cable must be protected from damaging UVradiation. This can be achieved when the sensor is used in internal areas.

The connection cable must be prevented from being subjected to tension and torsional loading.

Copyright Pepperl+Fuchs, Printed in Germany

PEPPERL+FUCHS GmbH

ATEX 1D

Instruction

Device category 1D

Directive conformity Standard conformity

CE symbol

Ex-identification EC-Type Examination Certificate Assigned type Effective internal capacitance C_i Effective internal inductance L_i General

Maximum housing surface temperature

Installation, Comissioning

Maintenance

Special conditions Electrostatic charging

Manual electrical apparatus for hazardous areas

for use in hazardous areas with combustible dust 94/9/EG IEC 61241-11:2002: draft; prEN61241-0:2002 type of protection intrinsic safety "iD" Use is restricted to the following stated conditions

€0102

(☑) II 1D Ex iaD 20 T 108 °C ZELM 03 ATEX 0128 X

SJ3,5-SN...

 \leq 30 nF ; a cable length of 10 m is considered.

 \leq 100 μH ; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual.

The EU prototype test certificate must be observed.

The special conditions must be adhered to!

The maximum surface temperature of the housing is given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed.

The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

The associated apparatus must satisfy at least the requirements of category ia IIB or iaD. Because of the possibility of the danger of ignition, which can arise due to faults and/or transient currents in the equipotential bonding system, galvanic isolation in the power supply and signal circuits is preferable. Associated apparatus without electrical isolation must only be used if the appropriate requirements of IEC 60079-14 are met.

The intrinsically safe circuit has to be protected against influences due to lightning.

When used in the isolating wall between Zone 20 and Zone 21 or Zone 21 und Zone 22 the sensor must not be exposed to any mechanical danger and must be sealed in such a way, that the protective function of the isolating wall is not impaired. The applicable directives and standards must be observed.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

The connection cables are to be laid in accordance with EN 50281-1-2 and must not normally be subjected to chaffing during use.

SJ3.5-SN

Subject to reasonable modifications due to technical advances.

Copyright Pepperl+Fuchs, Printed in Germany

ATEX 3D

Instruction

Device category 3D

Directive conformity Standard conformity

CE symbol

Ex-identification General

Installation, Comissioning

Maintenance

Special conditions Minimum series resistance RV

Maximum operating voltage UBmax

Maximum heating (Temperature rise)

at U_{Bmax} =9 V, R_V =562 Ω using an amplifier in accordance with EN 60947-5-6 Protection from mechanical danger

Protection of the connection cable

Manual electrical apparatus for hazardous areas

for use in hazardous areas with non-conducting combustible dust 94/9/EG EN 50281-1-1 Protection via housing Use is restricted to the following stated conditions

C€0102

⟨ы⟩ II 3D IP67 T 112 °C X

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual.

The data stated in the data sheet are restricted by this operating instruction! The special conditions must be adhered to!

Laws and/or regulations and standards governing the use or intended usage goal must be observed.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

A minimum series resistance RV is to be provided between the power supply voltage and the proximity switch in accordance with the following list. This can also be assured by using a switch amplifier.

The maximum permissible operating voltage UBmax must be restricted to the values given in the following list. Tolerances are not permitted.

Values can be obtained from the following list, depending on the max. operating voltage Ub max and the minimum series resistance $\mathsf{Rv}.$

12 °C 12 °C

The sensor must not be mechanically damaged.

The connection cable must be prevented from being subjected to tension and torsional loading.

Copyright Pepperl+Fuchs, Printed in Germany

PEPPERL+FUCHS GmbH

ATEX 3G (nL)

Instruction

Device category 3G (nL) Directive conformity

Standard conformity

CE symbol

Ex-identification Effective internal capacitance C_i

Effective internal inductance L_i

General

Installation, Comissioning

Maintenance

[Fett]Special conditions	
Maximum permissible ambient temperature T_{Umax} at Ui = 20 V	
for Pi=34 mW, li=25 mA, T6	
for Pi=34 mW, li=25 mA, T5	
for Pi=34 mW, li=25 mA, T4-T1	
for Pi=64 mW, li=25 mA, T6	
for Pi=64 mW, li=25 mA, T5	
for Pi=64 mW, li=25 mA, T4-T1	
for Pi=169 mW, li=52 mA, T6	
for Pi=169 mW, li=52 mA, T5	
for Pi=169 mW, li=52 mA, T4-T1	
for Pi=242 mW, li=76 mA, T6	
for Pi=242 mW, li=76 mA, T5	
for Pi=242 mW, li=76 mA, T4-T1	
Protection from mechanical danger	

Connection parts

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist 94/9/EG

EN 50021:2000 Ignition protection category "n" Use is restricted to the following stated conditions

€0102

 $\label{eq:stability} \underbrace{\mbox{(b)}}_{\leq \mbox{(b)}} \mbox{II 3G EEx nL IIC T6 X} \\ \le \mbox{30 nF ; A cable length of 10 m is considered.}$

 \leq 100 μH ; A cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The data stated in the data sheet are restricted by this operating instruction! The special conditions must be observed!

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The sensor must only be operated with energy-limited circuits, which satisfy the requirements of IEC 60079-15. The explosion group depends on the connected and energy-limited supply circuit.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

70 °C
85 °C
100 °C
66 °C
81 °C
100 °C
45 °C
60 °C
89 °C
30 °C
45 °C
74 °C
The sensor must not be mechanically damaged. When used in the temperature range below -20°C the sensor should be pro-

When used in the temperature range below -20°C the sensor should be protected from knocks by the provision of an additional housing.

The connection parts are to be installed, such that a minimum protection class of IP20 is achieved, in accordance with IEC 60529.

Copyright Pepperl+Fuchs, Printed in Germany