

EVERLIGHT ELECTRONICS CO.,LTD.

Technical Data Sheet 10 Bar Graph Displays

FOREVER

Features :

LIGHTING

- Industrial standard size.
- Low power consumption.
- Categorized for luminous intensity.
- Pb free
- The product itself will remain within RoHS compliant version
- Descriptions :
- The ELB-1001 series are ten-element bar graph displays. designed for viewing distances up to 7 meters.
- There are separate anodes and cathodes for each light segment and choice of five colors is offered.
- These devices are made with red segments and gray surface.

Applications :

- Audio equipment
- Instrument panels
- Digital read out display


PART NO.	Chip		
PART NO.	Material	Emitted Color	
ELB-1001SDRDA/S530-A3/P42	AlGaInP	Deep-Red	

DR000009134

EVERLIGHT ELECTRONICS CO.,LTD. Device Number :DDF-0000317

http://www.everlight.com Prepared date:2009/4/27 Rev.: 1 Page: 1 of 6 Prepared by: YanLi Zhong

ELB-1001SDRDA/S530-A3/P42






EVERLIGHT ELECTRONICS CO., LTD.

Technical Data Sheet 10 Bar Graph Displays

ELB-1001SDRDA/S530-A3/P42

Package Dimensions



Notes: 1.All dimensions are in millimeters , tolerance is 0.25mm unless otherwise noted. 2.Above specification may be changed without notice.

Supplier will reserve authority on material change for above specification.

http://www.everlight.com Prepared date:2009/4/27 Rev.: 1 Page: 2 of 6 Prepared by: YanLi Zhong



EVERLIGHT ELECTRONICS CO., LTD.

LIGHTING FOREVER

Technical Data Sheet

10 Bar Graph Displays

ELB-1001SDRDA/S530-A3/P42

Absolute maximum ratings at $Ta = 25^{\circ}C$:

Parameter	Symbol	Rating	Unit
Reverse Voltage	VR	5	V
Forward Current	IF	25	mA
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40 to +100	°C
Soldering Temperature *	Tsol	260	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	60	mW

Note: *Soldering time \leq 5 seconds.

Electronic optical characteristics :

Parameter		Symbol	Min.	Тур.	Max.	Unit	Condition	
Luminous Intensity	Per segment	Iv		1.5		mcd	IF=2mA	
			2.8	6.4		mcd	IF=10mA	
Peak Wavelength		λp		650		nm	IF=20mA	
Dominant Wavelength		λd		639		nm	IF=20mA	
Spectrum Radiation Bandwidth		-		20		nm	IF=20mA	
Forward Voltage		VF		2.0	2.4	V	IF=20mA	
Reverse Current		IR			100	μΑ	VR=5V	

http://www.everlight.com Prepared date:2009/4/27




EVERLIGHT ELECTRONICS CO., LTD.

ELB-1001SDRDA/S530-A3/P42

Typical Electro-Optical Characteristic Curves:

(SDR)



Prepared date:2009/4/27



EVERLIGHT

Technical Data Sheet 10 Bar Graph Displays

ELB-1001SDRDA/S530-A3/P42

Reliability test items and conditions:

The reliability of products shall be satisfied with items listed below.

Confidence level: 97%

LTPD: 3%

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Re
1	Solder Heat	TEMP: $260^{\circ}C \pm 5^{\circ}C$	5 SEC	76 PCS		0/1
2	Temperature Cycle	H : +85℃ 30min ∫ 5 min L : -55℃ 30min	50 CYCLE	76 PCS		0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	Iv≦Ivt*0.5	0/1
4	High Temperature Storage	TEMP: 100°C	1000 HRS	76 PCS	or Vf≧U or	0/1
5	Low Temperature Storage	TEMP : -55℃	1000 HRS	76 PCS	Vf≦L	0/1
6	DC Operating Life	IF = 10 mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS		0/1

Note: Ivt: The test Iv value of the chip before the reliablility test

 $\operatorname{Iv}\,$: The test value of the chip that has completed the reliablility test

- U: Upper Specification Limit
- L: Lower Specification Limit

http://www.everlight.com Prepared date:2009/4/27 Rev.: 1 Page: 5 of 6 Prepared by: YanLi Zhong

EVERLIGHT ELECTRONICS CO.,LTD.

EVERLIGHT

LIGHTING FOREVER

Technical Data Sheet


10 Bar Graph Displays

ELB-1001SDRDA/S530-A3/P42

Packing Quantity Specification

- 1. 19PCS/tube, 72 tubes/box
- 2. 4Boxes/Carton

Label Form Specification



CPN: Customer's Production Number P/N : Production Number QTY: Packing Quantity CAT: Ranks HUE: Dominant Wavelength REF: Reference LOT No: Lot Number Reference:Volume label code

Notes :

1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.

2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT' sconsent.

EVERLIGHT ELECTRONICS CO., LTD.Tel: (020) 84860913 , 84860914Office: 7c Building ,Lian Hua Port Industrial District, Lian Hua ShanFax: (020) 84860600Bonded Pricessing, Zone Pan Yu, Guang Zhou, Chinahttp://www.everlight.com

EVERLIGHT ELECTRONICS CO.,LTD. Device Number :DDF-0000317 http://www.everlight.com Prepared date:2009/4/27 Rev.: 1 Page: 6 of 6 Prepared by: YanLi Zhong