# "FPF" SERIES FAN-FILTER UNITS

Filter Code: FPF08KR230B-110

Description: Fan Filter 230 Va.c.

### MECHANICAL SPECIFICATIONS

Dimensions: 105x105x67 mm

Weight: 0,5 Kg

Type of material: ABS/PC UL94V-0

Colour: RAL 7032

Protection degree: IP54 (EN60529) Fastener: by elastic hooks Plate thickness: from 1,5 to 2,2 mm

Storage temp.: -30°C to +75°C

Electric connection: by 2 leads UL1007 AWG22

Earth connection: by M4 screw

#### **OPERATING FEATURES**

Rated voltage: 230 [V] Rated frequency: 50/60 [Hz] Rated power: 10/8.0 [W] Rated current: 70/55 [mA] Fan speed: 2700/3200 [rpm]

Noise: 40.0/44.0 [dB(A)]

Operating temp.: - 10°C to +55°C

Relative humidity: 90% max Life (L10) at 40°C: 45.000 hours

## PERFORMANCES and APPROVALS

Max air flow: 23/30 [m<sup>3</sup>/h] Max static pressure: 42/62 [Pa] Type of media: P15/350S


Flammability: F1 (DIN 53438) Filtering class: EU3 (DIN 24185) Degree of separation: 85% (DIN 24185) Degree of efficacy: < 20% (DIN 24185)


Dust storage capacity: 600 g/m<sup>2</sup>

Approvals:


Note: the media is washable

# **FAN FILTER DIMENSIONS [mm]**






## **DIMENSIONS CUT-OUT [mm]**



## PERFORMANCE CURVES



Please refer to out terms of sales including our warranty and limited liabilities clauses.



=ISO 9001/2000=