# "FPF" SERIES FAN-FILTER UNITS

Filter Code: FPF12KR230BE-110

Description: Fan Filter 230 Va.c.

#### MECHANICAL SPECIFICATIONS

Dimensions: 150x150x71 mm

Weight: 0,8 Kg

Type of material: ABS/PC UL94V-0

Colour: RAL 7032

Protection degree: IP54 (EN60529) Fastener: by elastic hooks Plate thickness: from 1,5 to 2,2 mm

Storage temp.: -45°C to +75°C

Electric connection: by terminal block 2,5mm<sup>2</sup>

Earth connection: by M4 screw

#### **OPERATING FEATURES**

Rated voltage: 230 [V] Rated frequency: 50/60 [Hz] Rated power: 20/19 [W] Rated current: 125/110 [mA] Fan speed: 2650/3000 [rpm]

Noise: 43.0/48.0 [dB(A)]

Operating temp.: - 10°C to +50°C

Relative humidity: 90% max Life (L10) at 40°C: 45.000 hours

## PERFORMANCES and APPROVALS

Max air flow: **57/61** [m<sup>3</sup>/h] Max static pressure: 66/73 [Pa] Type of media: P15/350S


Flammability: F1 (DIN 53438) Filtering class: EU3 (DIN 24185) Degree of separation: 85% (DIN 24185) Degree of efficacy: < 20% (DIN 24185)

Dust storage capacity: 600 g/m<sup>2</sup>


Approvals:

Note: the media is washable


# **FAN FILTER DIMENSIONS [mm]**



## **DIMENSIONS CUT-OUT [mm]**



## PERFORMANCE CURVES



Please refer to out terms of sales including our warranty and limited liabilities clauses.

