




"RAC" HEATERS WITH CABLE Description: 45/60/80/100/150 W



Heating element: PTC thermistor, self regulating

Heat sink: black anodised extruded aluminium profile

Method of mounting: snap-on fixing on RAIL 35 mm

DIN 46 277/3 EN 50 022

Rated temp. range: from -30° C to $+40^{\circ}$ C Storage temp. range: from -40° C to $+90^{\circ}$ C

Protection degree by heaters: IP50

External cable: by 3 poles cable L-N-PE 3x20AWG cable with PFA sheath 500 mm length

Appliance class: class I


Over voltage categories: III as IEC 60664-1 standard


Rated voltage: 230 V a.c./d.c.
Rated voltage range: 110-250 V a.c./d.c.

Rated frequency: 50/60 Hz **Max voltage:** 265 V a.c./d.c.

Operating temperature: from -10°C to +60°C **Applicable standard:** EN 60335-1

Approvals: CE





Model	Dimensions		Heating Power*	Absorbed Current*	External Surface**	Internal Heat Sink**	Weight
	A [mm]	B [mm]	[W]	[mA]	[°C]	[°C]	[Kg]
RAC-45	102	34	45	200	70	90	0.28
RAC-60	102	34	60	260	85	105	0.28
RAC-80	152	58	80	390	90	110	0.40
RAC-100	152	58	100	475	105	130	0.40
RAC-150	227	95	150	770	125	145	0.59

- The above values of heating power, absorbed power and temperature, were obtained at 230 Va.c. 50Hz and at ambient temperature condition of 15±5°C after a working of 10 minutes. These values have an uncertainty of 10%.
- ** Temperatures have been obtained after a working of 10 minutes at ambient temperature condition of 23.5°C.

All specifications, data and drawing are subject to change without notice and are approximate. Please refer to our terms of sales including our warranty and limited liabilities clauses.