

# CSR1 & CSR2-B & E SERIES

## **POWER REGULATORS**

**CSR1/2-B/E** 

X10282

#### INTRODUCTION

The CSR Power Regulators are compact and robust units, which are capable of controlling single-phase mains driven loads of up to 15A. The CSR2 - series regulators come in two styles, open (type B) and enclosed (type E), with the enclosed version having its own integral heatsink. The regulator gives a fully adjustable output from zero to maximum voltage. The standard unit is rated for 110V and 230V ac, but other voltages are available on request.

# **APPLICATIONS**

Suitable for conventional resistive heating elements such as ovens, quartz lamps, moulders and dryers. Also suitable for some inductive loads such as transformers, fans and motors.

## **FEATURES**

RoHS Compliant
Directive
2002/95/EC


EXAMPLE - CSR2-15E


- Compact and easy to use
- Simple installation with or without heatsink

Available in 6, 10, and 15 ampere ratings

- Discrete component giving high reliability
- Cost effective







SPECIFICATIONS UNIT		CSR1 (110V) & CSR2 (230V)					
	TYPE	6B	6E	10B	10E	15B	15E
Maximum on-state current, Imax (tab @70°C	) A (RMS)	6	6	10	10	15	15
Peak one cycle surge currents	A	100	100	120	120	150	150
Off - leakage current (maximum)	mA			· ′;	2		
Minimum holding load current	mA			3	0		
RMS input voltage +/- 10% @ 50/60 Hz	V			110 o	r 230		
Repetitive peak voltage (tab @ 70°C)	V			40	0		
Hysteresis	%	5					
Total conduction phase angle (typical)	degrees	0 to 160°					
Controlled phase angle (typical)	degrees	30 to 160°					
Power transfer at Imax (efficiency)	%	99					
Tab surface operating range	°C	0 to + 75					
Storage temperature	°C	0 to + 75					
Insulation withstand capability (tab @ 70°C)		1500 for 1 min					
I <sup>2</sup> t limiting values for fusing	$A^2s$	18	18	50	50	100	100
Mounting hale diameter (minimum)	mm	10.3	10.3	10.3	10.3	10.3	10.3

#### **FUSING**

It is recommended to use semiconductor (fast acting) type fuses or circuit breakers (semiconductor- MCB) for unit protection. On initial 'switch on' some loads may need an increased Factor of Safety (F of S) for unit and/or device protection. See SRA Data sheet for further information.

## **CE MARKING**

This product family carries a "CE marking". These phase angle controllers need a suitable remote filter. For more information see recommendations section and contact our sales desk.

#### RECOMMENDATIONS

Other documents available on request, which may be appropriate for your applications:-

CODE	<b>IDENTITY</b>	DESCRIPTION
X10229	RFI	Filtering recommendation - addressing EMC Directive.
X10213	ITA	Interaction, uses for phase angle and for burst fire control.
X10255	SRA	Safety requirements - addressing the Low Voltage Directive (LVD) including :-
		Thermal data/cooling; "Live" parts warning & Earth requirements; Fusing
		recommendations.
AP02/4	COS	UAL Conditions of sale.

NOTE It is recommended that installation and maintenance of this equipment should be done with reference to the current edition of the I.E.E. wiring regulations (BS7671) by suitably qualified/trained personnel. The regulations contain important requirements regarding safety of electrical equipment.

(For International Standard refer to I.E.C. directive IEC 950).

**ORDER CODE:** State part number: CSR1 or 2 (Denotes supply voltage) + (current rating) + type 'B' or 'E'

Optional extras include: Knob, Dial, Heatsink compound, Filters.

Note: When ordering a filter, the current the CSR is to be used at will be required.



# UNITED AUTOMATION I

1Southport Business Park Southport, PR8 4HQ

Tel: 0044 (0) 1704 - 516500 Fax: 0044 (0) 1704 - 516501

e-mail: enquiry@united-automation.com **ENGLAND** 

Date 7/03/03 Page No. 2 of 2 Issue 3



This document was created with Win2PDF available at <a href="http://www.win2pdf.com">http://www.win2pdf.com</a>. The unregistered version of Win2PDF is for evaluation or non-commercial use only. This page will not be added after purchasing Win2PDF.