








POLARIZED, MONOSTABLE **SAFETY RELAY** WITH FORCIBLY GUIDED **DOUBLE CONTACTS**

SF2D



Features

- Relay complies with EN 50205, Type A
- Overvoltage category as per IEC 60664-1 III / 4kV
- Rated voltage as per IEC 60664-1 Polution degree basic insulation inside inside outside Coil-contact 400V 400V 250V Contact-contact 400V 400V 400V

SPECIFICATIONS

Weight approx. 47g

Contact

Contact configuration (a = normally open / NO, b = normally closed / NC)	2a2b	
Contact material	AgSnO ₂ , with Au flash	
Contact resistance (initial at 6V DC, 1A)	30mΩ	
Making and breaking capacities (breathing hole open)*1	6A 250V / 3A 24V	
Max. switching voltage	400V	
Min. switching voltage / min. switching current	10V / 10mA	
Pick-up / drop-out / bounce time (approx. values at U _{nominal})	17.5 / 7 / 2ms	
Mechanical life	10 ⁷ ops	

Coil

Operate / release voltage (% of U _{nominal} at 20°C)	75% / 10%	
Pick-up/nominal power consumption at 20°C	280 / 500mW	

Remarks

- *1 According to EN 60947-5-1: 1997, table 4 AC15 / DC13
- *2 Contact interruption <10µs
- *3 Breathing hole open

Characteristics

Max. switching frequency (without load)	10Hz	
Permissible ambient temperature at nominal power consumption	-40°C to +70°C	
Upper temperature limit	105°C	
Test voltage: open contact / contact-contact / contact-coil	2500 / 2500 / 2500V _{rms}	
Insulation resistance at 500V DC (initial)	$10^{9}\Omega$	
Shock resistance (11ms) NO/NC*2	30G	
Vibration resistance 10 – 200 Hz (10 – 55 Hz, amplitude 2 mm)*2	10G	
Degree of protection	IP67 / IP30*3	
Unit weight	37a	


Important: Relay characteristics may be influenced by:

- · strong external magnetic fields
- · magnetic conductive materials near the relay
- narrow top-to-top mounting (printed surface to printed surface)

Note:

Suitable for most common washing methods except ultrasonic cleaning.

ORDERING INFORMATION



Note: Standard packing; Carton: 20 pcs. Case 200 pcs.

Part number	Coil nominal voltage V DC	Operate voltage V DC	Release voltage V DC	Coil resistance Ω (±10%, 20°C)	Coil inductance (mH)	
SF2D-DC5V	5	3.75	0.5	50	47	
SF2D-DC9V	9	6.75	0.9	162	145	
SF2D-DC12V	F2D-DC12V 12 9.00 1.2		1.2	288	252	
SF2D-DC18V	18	13.50	1.8	648	551	
SF2D-DC21V	21	15.75	2.1	882	742	
SF2D-DC24V	24	18.00	2.4	1152	959	
SF2D-DC36V	36	27.00	3.6	2592	2097	
SF2D-DC48V	48	36.00	4.8	4608	3654	
SF2D-DC60V	60	45.00	6.0	7200	5612	


ELECTRICAL LIFE

Voltage	Current	Load type	Frequency	Duty cycle	No. of contacts	No. of ops.
230V AC	8A	AC 1	0.25Hz	25%	2 ^{*2}	85,000 ^{*5}
250V AC	6A	AC 1	0.33Hz	50%	4*2	100,000 ^{*5}
230V AC	6A	AC 1	0.33Hz	10%	2 ^{*3}	200,000*4,*5
230V AC	30 / 3A	AC 15*1	0.33Hz	10%	1 ^{*3}	150,000 ^{*4,*5}
24V DC	8A	DC 1	0.33Hz	10%	2 ^{*3}	200,000*4,*5
24V DC	3A	DC 13*1	0.33Hz	10%	1 ^{*3}	50,000*4,*5
24V DC	3A	L/R = 40ms	0.33Hz	10%	1 ^{*3}	100,000*4,*5

^{*1} EN 60947-5-1: 1997; table C.1


REFERENCE DATA

Load limit curve



Loads in the range under the curve can be switched safely. The arc will extinguish before the opposite contact makes.


Coil voltage characteristics




Permissable coil voltages and pick-up and drop-out characteristics at various ambient temperatures.

^{*2} Breathing hole closed
*3 Breathing hole open
*4 Ambient temperature +70°C
*5 Dielectric strength according to EN61810-1:2004.


Connection diagram and pcb bore hole data




The contacts are shown in the deenergized condition



Contact current characteristics



APPLICATION NOTES



If required a breathing hole can be made in the cover by removing the nipple. However be aware that the degree of protection will be reduced from IP67 to IP30!

For Cautions for Use, see Relay Technical Information.