FPA250 Thick Film Power Resistors



Due to a Non-Inductive design these elements are ideally suited for high frequency and pulse load applications. the FPA250 is available connected as 2 terminals or 4 terminals, in parallel or series.

- Non Inductive Performance for HF Applications
- Power Applications 100W to 600W
- Very Good Power/Volume Ratio
- RoHS Compliant



≤10pC / 5000Vac

0.05mm max

Characteristics

Power rating: 250W (heatsink at 100°C) Partial discharge: From 1R to 2M ohm E6 Series Self inductance: Resistance range: Tolerance (Code): Standard J (±5%) and K (±10%)

Also available F (±1%) on request Capacitance/Mass:

Heatsink flatness:

100ppm/°C Temperature coefficient: Max working voltage: 5000Vac -55°C to +155°C Working temperture range: Dielectric strength: 7000Vac

≥ 10Gohm at 500V Insulation resistance:

Creepage distance: 40mm Air gap distance: 14mm

40nH Parallel capacitance: 40pF ≤120pF Overload: 4Pn x 10 sec Thermal resistance: 0.15°C/W


Heatsink surface finish: 6.3 µm max Thermal grease: Required Max torque for contacts: 2Nm (static) Max torque for mounting: 1.8Nm (static)

Ordering Procedure

Standard (Version 1) Resistor Specify Series, Watts, Ohmic Value, Tolerance Code, e.g.: FPA250 10R J

Versions 2, 3, 4 or 5 Specify Series, Watts, Ohmic Value or Values, Tolerance Code and then Version Number,

e.g.: FPA250 10R 10R J version 4. Refer to versions available on page 2.



ARCOL UK Limited, Threemilestone Ind. Estate, Truro, Cornwall, TR4 9LG, UK. T +44 (0) 1872 277431

F +44 (0) 1872 222002

E sales@arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. Arcol operate a policy of continual product development, therefore, specifications may change.


It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask Arcol.


www.arcolresistors.com

6/08.05 Page 1 of 2

FPA250 Thick Film Power Resistors







Page 2 of 2 6 / 08.05