

Panasonic

ideas for life

LOW-PROFILE SURFACE-MOUNT RELAY

TQ SMD RELAYS

FEATURES

• Low-profile: 6 mm .236 inch

(Tape height: max. 6.5 mm .256 inch)

- Tape and reel package is available as standard packing style
- Surge withstand between contacts and coil: 2,500 V
- Breakdown voltage between contacts and coil: 1,500 V
- · Capacity: 2 A
- · High sensitivity:

2 Form C; 140 mW power consumption (Single side stable type)



mm inch

SPECIFICATIONS

Contact

Contact					
Arrangemen	t	2 Form C			
	t resistance, r drop 6 V DC 1	75 mΩ			
Contact mat	erial	Gold-clad silver alloy			
	Nominal swit (resistive load	tching capacity id)	2 A 30 V DC, 0.5 A 125 V AC		
Rating	Max. switchi (resistive loa		60 W, 62.5 VA		
Ü	Max. switchi	ng voltage	220 V DC, 125 V AC		
	Max. switchi	ng current	2 A		
	Min. switchin	ng capacity *1	10 μA 10 mV DC		
Nominal operating power	Single side s	stable	140 mW (1.5 to 12 V DC) 200 mW (24 V DC) 300 mW (48 V DC)		
	1 coil latchin	g	70 mW (1.5 to 12 V DC) 100 mW (24 V DC)		
	2 coil latchin	g	140 mW (1.5 to 12 V DC) 200 mW (24 V DC)		
	Mechanical ((at 180 cpm)	108		
Expected life (min. operations)	Electrical (at 20 cpm)	2 A 30 V DC resistive	10⁵		
		1 A 30 V DC resistive	2×10⁵		
		0.5 A 125 V AC resistive	10 ⁵		

Note

*1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load. (SX relays are available for low level load switching [10 μ A 1 mV DC – 10 mA 10 V DC])

Remarks

- * Specifications will vary with foreign standards certification ratings.
- *1 Measurement at same location as "Initial breakdown voltage" section.
- *2 By resistive method, nominal voltage applied to the coil; contact carrying current: 2 A.
- *3 Nominal voltage applied to the coil, excluding contact bounce time.
- *4 Nominal voltage applied to the coil, excluding contact bounce time without diode.
- \star_5 Half-wave pulse of sine wave: 6 ms; detection time: 10 μs
- *6 Half-wave pulse of sine wave: 6 ms
- *7 Detection time: 10 μs
- *8 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT (see catalog).

Characteristics

Initial insulat	ion resis	tance*1	Min. 1,000 MΩ (at 500 V DC)			
	Between open contacts		1,000 Vrms for 1 min. (Detection current: 10 mA)			
Initial breakdown voltage	Betwee	n contact sets	1,500 Vrms for 1 min. (Detection current: 10 mA)			
vollago	Between contact and coil		1,500 Vrms for 1 min. (Detection current: 10 mA)			
Initial surge	Between open contacts (10×160 µs)		1,500 V (FCC Part 68)			
voltage	Between contacts and coil (2×10 μs)		2,500 V (Telcordia)			
Temperature	rise*2 (a	t 20°C)	Max. 50°C			
Operate time	e [Set tim	e]*³ (at 20°C)	Max. 4 ms (Approx. 2 ms) [Max. 4 ms (Approx. 2 ms)]			
Release time (at 20°C)	e [Reset	time]*4	Max. 4 ms (Approx. 1 ms) [Max. 4 ms (Approx. 2 ms)]			
Chook regist	Shock resistance		Min. 750 m/s ² {75 G}			
SHOCK TESISE			Min. 1,000 m/s ² {100 G}			
Vibration rea	.		200 m/s ² {20G}, 10 to 55 Hz at double amplitude of 3.3 mm			
Vibration resistance		Destructive	294 m/s ² {30G}, 10 to 55 Hz at double amplitude of 5 mm			
Conditions for operation, transport and storage*8 (Not freezing and condensing at low temperature)		Ambient temperature	-40°C to +85°C*³ -40°F to +185°F			
		Humidity	5 to 85% R.H.			
Unit weight			Approx. 2 g .071 oz			

ORDERING INFORMATION

Ex. TQ 2 SA - L - 3V - Z								
Contact arrangement	Surface-mount availability	Operating function	Coil voltage (DC)	Packing style				
2: 2 Form C	2: 2 Form C SA: Standard surface-mount terminal type SL: High connection reliability surface-mount terminal type SS: Space saving surface-mount terminal type		1.5, 3, 4.5, 5, 6, 9, 12, 24, 48* V	Nil: Tube packing Z: Tape and reel packing (picked from the 6/7/8/9/10-pin side)				

*48 V coil type: Single side stable only
Notes: 1. Tape and reel (picked from 1/2/3/4/5-pin side) is also available by request. Part No. suffix "-X" is needed when ordering. (ex.) TQ2SA-3V-X
2. Tape and reel packing symbol "-Z" or "-X" are not marked on the relay.

TYPES

1. Single side stable

Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (max.)	Drop-out voltage, V DC (min.)	Nominal operating current, mA (±10%)	Coil resistance, Ω (±10%)	Nominal operating power, mW	Max. allowable voltage, V DC
TQ2SO-1.5 V	1.5	1.13	0.15	93.8	16	140	2.2
TQ2SO-3 V	3	2.25	0.3	46.7	64.3	140	4.5
TQ2SO-4.5 V	4.5	3.38	0.45	31	145	140	6.7
TQ2SO-5 V	5	3.75	0.5	28.1	178	140	7.5
TQ2SO-6 V	6	4.5	0.6	23.3	257	140	9
TQ2SO-9 V	9	6.75	0.9	15.5	579	140	13.5
TQ2SO-12 V	12	9	1.2	11.7	1,028	140	18
TQ2SO-24 V	24	18	2.4	8.3	2,880	200	36
TQ2SO-48 V	48	36	4.8	6.3	7,680	300	57.6

2. 1 coil latching

Part No.	Nominal voltage, V DC	Set voltage, V DC (max.)	Reset voltage, V DC (max.)	Nominal operating current, mA (±10%)	Coil resistance, Ω (±10%)	Nominal operating power, mW	Max. allowable voltage, V DC
TQ2SO-L-1.5 V	1.5	1.13	1.13	46.9	32	70	2.2
TQ2SO-L-3 V	3	2.25	2.25	23.3	128.6	70	4.5
TQ2SO-L-4.5 V	4.5	3.38	3.38	15.6	289.3	70	6.7
TQ2SO-L-5 V	5	3.75	3.75	14	357	70	7.5
TQ2SO-L-6 V	6	4.5	4.5	11.7	514	70	9
TQ2SO-L-9 V	9	6.75	6.75	7.8	1,157	70	13.5
TQ2SO-L-12 V	12	9	9	5.8	2,057	70	18
TQ2SO-L-24 V	24	18	18	4.2	5,760	100	36

3. 2 coil latching

Part No.	Nominal voltage, V DC	Set voltage, V DC (max.)	Reset voltage, V DC (max.)	Nominal operating current, mA (±10%)	Coil resistance, Ω (±10%)	Nominal operating power, mW	Max. allowable voltage, V DC
TQ2SO-L2-1.5 V	1.5	1.13	1.13	93.8	16	140	2.2
TQ2SO-L2-3 V	3	2.25	2.25	46.7	64.3	140	4.5
TQ2SO-L2-4.5 V	4.5	3.38	3.38	31	145	140	6.7
TQ2SO-L2-5 V	5	3.75	3.75	28.1	178	140	7.5
TQ2SO-L2-6 V	6	4.5	4.5	23.3	257	140	9
TQ2SO-L2-9 V	9	6.75	6.75	15.5	579	140	13.5
TQ2SO-L2-12 V	12	9	9	11.7	1,028	140	18
TQ2SO-L2-24 V	24	18	18	8.3	2,880	200	36

O: For each surface-mounted terminal variation, input the following letter.

SA type: \underline{A} , SL type: \underline{L} , SS type: \underline{S}


Notes: 1. Specified value of the pick-up, drop-out, set and reset voltage is with the condition of square wave coil pulse.

^{2.} Standard packing: Tube: 50 pcs.; Case; 1,000 pcs.; Tape and reel: 500 pcs./reel

^{3.} In case of 5 V transistor drive circuit, it is recommended to use 4.5 V type relay.

DIMENSIONS

SA type





SL type







SS type









General tolerance: $\pm 0.3 \pm .012$

Recommendable mounting pad


(Top view) SA type



SL type



SS type



Tolerance: ±0.1 ±.004

Schematic (Top view) Single side stable (Deenergized condition)


*Orientation stripe located on top of relay.

•1-coil latching (Reset condition)



*Orientation stripe located on top of relay.


•2-coil latching (Reset condition)




*Orientation stripe located on top of relay.

REFERENCE DATA


1. Maximum switching capacity



2. Life curve




3. Mechanical life (mounting by IRS method) Tested sample: TQ2SA-12V, 10 pcs.




4.-(1) Electrical life (2 A 30 V DC resistive load) Tested sample: TQ2SA-12V, 6 pcs. Operating frequency: 20 cpm

Change of pick-up and drop-out voltage (mounting by IRS method)




Change of contact resistance (mounting by IRS method)




4.-(2) Electrical life (0.5 A 125 V AC resistive load) Tested sample: TQ2SA-12V, 6 pcs


Operating frequency: 20 cpm Change of pick-up and drop-out voltage (mounting by IRS method)




Change of contact resistance (mounting by IRS method)




5. Coil temperature rise Tested sample: TQ2SA-12V, 6 pcs. Point measured: Inside the coil Ambient temperature: 25°C 77°F




6. Operate/release time Tested sample: TQ2SA-12V, 6 pcs.




7. Distribution of pick-up and drop out voltage Tested sample: TQ2SA-12V, 50 pcs.




8. Distribution of set and reset voltage Tested sample: TQ2SA-L-12V, 30 pcs.




9. Ambient temperature characteristics Tested sample: TQ2SA-12V, 5 pcs.




10. Distribution of contact resistance Tested sample: TQ2SA-5V, 30 pcs. (30 \times 4 contacts)




11.-(1) High-frequency characteristics Isolation characteristics




11.-(2) High-frequency characteristics Insertion loss characteristics




12.-(1) Malfunctional shock (single side stable) Tested sample: TQ2SA-12V, 6 pcs




12.-(2) Malfunctional shock (latching) Tested sample: TQ2SA-L2-12V, 6 pcs.




13.-(1) Influence of adjacent mounting Tested sample: TQ2SA-12V, 5 pcs.



13.-(2) Influence of adjacent mounting Tested sample: TQ2SA-12V, 6 pcs.




13.-(3) Influence of adjacent mounting Tested sample: TQ2SA-12V, 6 pcs.




14. Pulse dialing test
Tested sample: TQ2SA-12V, 6 pcs.


(35 mA 48 V DC wire spring relay load) Circuit



Change of pick-up and drop-out voltage (mounting by IRS method)




Change of contact resistance (mounting by IRS method)



NOTES


1. Packing style

1) The relay is packed in a tube with the relay orientation mark on the left side, as shown in the figure below.




2) Tape and reel packing (surface-mount terminal type)


- (1) Tape dimensions
- (i) SA type



(ii) SL, SS type



(2) Dimensions of plastic reel



For Cautions for Use, see Relay Technical Information (see catalog).