



Switch housing

For the installation of switches and other command devices Ø 22.5 mm.

Benefits:

- Temporary lid stay allows you to keep your hands free when wiring.
- Versatile attachment options: Screw fastening from the inside or outside, and via wall mounting brackets.
- Opening and closing the lid with quick-release fasteners (a three-quarter revolution is sufficient).

Material:

Stainless steel 1.4301 (AISI 304)
Enclosure: 1.25 mm
Cover: 1.25 mm

Surface finish:

Case and cover:
Brushed, grain 240

Protection category:

IP 66 to EN 60 529/10.91,
complies with NEMA 4x.

Supply includes:

Enclosure,
lid with foamed-in seal and 2 or
4 quick-release fasteners.

Detailed drawing,
see page 209.

No. of switch cut-outs	B mm	H mm	D mm	R mm	Packs of	Model No. SM
1	100	100	90	–	1	2384.010
2	160	100	90	60	1	2384.020
3	220	100	90	60	1	2384.030
4	280	100	90	60	1	2384.040

Accessories

Wall mounting bracket in stainless steel 1.4301 (AISI 304), Model No. KL 1594.000, see Cat. 31, page 905.

To order switch housing in stainless steel 1.4404 (AISI 316L), please add extension .5X0 to the Model No.
Delivery times available on request.



Cable glands

made from polyamide or brass.
Model No. see Cat. 31,
page 972.



Integrated temporary lid stay
allows you to keep your hands
free when wiring.



Baying system TS 8

Grain 400, the new, fine surface finish for

- Baying systems of stainless steel 1.4301 and 1.4404, see Cat. 31, page 151, 152 and 284
- Matching side panels, base/plinth and cover
- Customer-specific solutions with the same Model No.